


FB-EM-30346-000


SHT 1.1

RED CONTROLLED





TOP VIEW
W/WINDSHIELD SHOWN
SCALE 1:1

$\varnothing 19,0 \pm 0,3$
[.748 $\pm$.012]



PLASTIC HOUSING, BLACK




WIRES
2mm STRIPPED & TINNED ENDS

WIRE COLOR			WEIGHT GRAMS
+ve	OUTPUT	-ve	
RED	WHITE	BLACK	---

DIMENSIONS IN MILLIMETERS [INCHES]

KNOWLES ELECTRONICS
ITASCA, ILLINOIS U.S.A.



Revision	C.O. #	Implementation Date	RELEASE LEVEL	REVISION
			Active	D
D	C40101206	3-6-13		
SCALE: 1:1			DR. BY TT	DATE 6-26-08
DO NOT SCALE DRAWING			CK. BY GJP	DATE 7-15-08
TITLE: BOOM MICROPHONE FB-EM-30346-000			APP. BY GJP	DATE 7-15-08
OUTLINE DRAWING			SHT 1.1	



FREQUENCY	SENSITIVITY			DEVICE CONFORMITY RANGE OF DEVIATION FROM 1KHz	
	MIN.	NOM.	MAX.		
300	---	-48.0	---	-3.0	+3.0
1000	-51.0	-48.0	-45.0	0.0	0.0
4000	---	-47.0	---	-3.0	+5.0

NOTES:

- MICROPHONE TO BE FUNCTIONAL WITH 10 VDC SUPPLY.
- SENSITIVITY VALUES INDICATED ON THIS SPECIFICATION ARE VALID AT 50% HUMIDITY.
- TEST CONDITIONS:
HEAD OF BOOM EXPOSED TO 74 dBSPL SWEPT SOUND FIELD AT 6mm FROM VOICE APERTURE.
ARTIFICIAL VOICE:
B & k 4227 MOUTH SIMULATOR.
- FOR MICROPHONE CAPSULE SPEC. SEE DRAWING EK-23132-C36 SHEET 2.1.
- SURVIVES SUBMERSION IN 1m OF WATER FOR 30 MINUTES; SENSITIVITY WITHIN 3dB OF INITIAL SENSITIVITY AFTER DRIED FOR 30 MINUTES AT ROOM TEMPERATURE.



LEAD IDENTIFICATION
& TEST CIRCUIT


RED CONTROLLED

KNOWLES ELECTRONICS
ITASCA, ILLINOIS U.S.A.

Revision	C.O. #	Implementation Date	RELEASE LEVEL		REVISION
			Active		D
D	C40101206	3-6-13			
WHEN TEST LIMITS ARE USED TO ESTABLISH INCOMING INSPECTION ACCEPTANCE/REJECTION CRITERIA, CORRELATION OF TEST EQUIPMENT WITH KNOWLES IS ALSO REQUIRED FOR ELIMINATION OF EQUIPMENT AND TEST METHOD VARIATION				DR. BY	DATE
				TT	6-26-08
TITLE: BOOM MICROPHONE PERFORMANCE SPECIFICATION				CK. BY	DATE
				GJP	7-15-08
FB-EM-30346-000 SHT 2.1				APP. BY	DATE
				GJP	7-15-08




PROPRIETARY NOTE: THIS DOCUMENT CONTAINS INFORMATION WHICH IS THE PROPRIETARY PROPERTY OF KNOWLES ELECTRONICS, LLC. OR ITS AFFILIATED ENTITIES. IT IS ISSUED FOR THE EXCLUSIVE USE OF THE USER AND IS NOT TO BE REPRODUCED OR COPIED TO ANY THIRD PARTY PARTIALLY OR WHOLLY IN ANY MANNER WITHOUT PRIOR WRITTEN PERMISSION OF, AND MUST BE RETURNED UPON REQUEST BY, KNOWLES ELECTRONICS, LLC.

FB-EM-30346-000




SECTION A-A

BOTH SIDES
(4X)




TOP VIEW
W/WINDSHIELD SHOWN
SCALE 1:1

RED CONTROLLED



SECTION B-B
SCALE 4:1



DIMENSIONS IN MILLIMETERS [INCHES]

MATERIAL				SEE BILL OF MATERIALS		FINISH	
REF.	10-1747	A	C40107379	B	C40107748	UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES	THIRD ANGLE PROJECTION
		B	C40107748				
			RENAME IN PROVE FROM FB-30346-000 TO FB-EM-30346-000 11-8-12-08				
		C	C40100518				
			SEE SHEET 4.1 00 11-24-10				
		D	C40101206				
			UPDATE THE REVISION 00 3-4-13				

RELEASE LEVEL		REVISION	
Active		D	
SCALE: 2:1		DO NOT SCALE DRAWING	
KNOWLES ELECTRONICS		DR. BY	DATE
ITASCA, ILLINOIS U.S.A.		TT	6-26-08
		CH. BY	DATE
		GJP	7-15-08
		APP. BY	DATE
		GJP	7-15-08
TITLE		FB-EM-30346-000	
BOOM MICROPHONE ASSEMBLY		SHEET 3.1	

- NOTES:
- ITEM NUMBERS (SHOWN THUS **b**) ON DRAWING CORRESPOND WITH ITEM NUMBERS ON BILL OF MATERIAL.
 - ATTACH ITEM **4** TO ITEM **1** IN 4 PLACES MINIMUM ON EACH SIDE USING CEMENT.
 - SEAL BOOM END WITH ITEM **10**. BUILD UP TO BE 2mm MAX.
 - SEAL WHOLE HEAD CAVITY WITH ITEM **9**, WIRE HOLE MUST BE FILLED, ADHESIVE BUILD UP TO BE 2mm MAX.

D
C
C
C

FB-EM-30346-000			KNOWLES ELECTRONICS			FB-EM-30346-000				
Sheet 4.1			ITASCA, ILLINOIS U.S.A.			Sheet 4.1				
By TT Date 6-26-08			Subject: BOOM MICROPHONE ASSEMBLY			Revision				
Ch. GJP 7-15-08						D		Release Level		
App. GJP 7-15-08								Active		
COL. 1			2		3		4			
Part or Dwg. no.			Tot. Req.		Nomenclature:		Applicable Specs or Remarks		Item No. Line No.	
FB-218-500			1		HOUSING				1 1	
EK-23132-C36			1		MICROPHONE ASSEMBLY				2 2	
FB-189-167			1		FLEXIBLE BOOM 5.4 mm				3 3	
FB-223			1		SCREEN DISC				4 4	
FB-234			1		MEMBRANE				5 5	
FB-074-000			1		WIRE BLACK				6 6	
FB-074-001			1		WIRE RED				7 7	
FB-042			1		WINDSHIELD				8 8	
13-092-120101			A/R		CEMENT				9 9	
13-591			A/R		SILICONE SEALANT				10 10	
13-092-130102			A/R		CEMENT				11 11	
FB-219			1		COVER, BOTTOM				12 12	
FB-074-003			1		WIRE WHITE				13 13	

RED CONTROLLED

REVISION	A	c.o.	C10107379	FB-074-000 WAS FB-070-050 FB-074-001 WAS FB-070-049 ADD FB-074-003 00 11-24-10	C	c.o.	C40100518	FB-234 WAS FB-038 00 3-4-13	D	c.o.	C40101206	FB-EM-30346-000 Sheet 4.1
	B	c.o.	C10107748			c.o.	C40100518			c.o.	C40101206	
	RENAME IN PRO/E FROM FB-30346-000 TO FB-EM-30346-000 11 8-12-08											
PROPRIETARY NOTE: THIS DOCUMENT CONTAINS INFORMATION WHICH IS THE PROPRIETARY PROPERTY OF KNOWLES ELECTRONICS, LLC. OR ITS AFFILIATED ENTITIES. IT IS ISSUED IN STRICT CONFIDENCE AND SHALL NOT BE REPRODUCED, COPIED, USED, OR DISCLOSED TO ANY THIRD PARTY PARTIALLY OR WHOLLY IN ANY MANNER WITHOUT PRIOR WRITTEN PERMISSION OF, AND MUST BE RETURNED UPON REQUEST BY, KNOWLES ELECTRONICS, LLC.												

ITEM: 1004 PART: 000 PMW REF: 0

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Knowles:

[FB-EM-30346-000](#)