

5

4

3





2

1


SPECIFICATION

Mating Cycles	500
Filter type	C
Capacitance	3900pf±20%
Working Voltage	100v
Current Rating	7.5A
Insulation Resistance	>1GΩ

FREQUENCY (MHz)	ATTENUATION (dB)
5	6dB
10	11dB
50	25dB
100	35dB
500	35dB
1000	32dB

PCB Layout
Component side

	Dat.	Name
Detail.	8-JUL-02	CV
Insp.		
Stand.		



D-Sub, male, straight,
15 Poles, turned solder pins,
tin plated shell with dimples
and clinch nuts

Mo?Mstab/
Scale

1.5:1

09642227248	M3	33267	17/11/05	JMDR
09642227247	UNC 4-40	31058	8-JUL-02	CV
Part number	Nut thread	Mod.	Dat.	Name

HARTING EURL
F-95972 Paris

TB 0964222724x

Sub.

Blatt/ Page

3 / 3