

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [74062-1003](#)
Status: **Active**
Overview: [VHDM® Backplane Connector Systems](#)
Description: 2.00mm Pitch VHDM® Single-Ended Board-to-Board Backplane Header, Vertical, 8-Row, Guide Pin Signal Module, Shield End Version, 80 Circuits, Pin Length 4.25mm. Series:74075 Enables designers to create custom loaded connectors utilizing standard pin lengths 4.25, 4.75, 5.15 and 6.25mm

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-74031-999 \(PDF\)](#)

Agency Certification

UL E29179

General

Product Family Backplane Connectors
Series [74062](#)
Application Backplane
Application Tooling Documents TM-622010999
Comments No Keying Position
Component Type PCB Header
Overview [VHDM® Backplane Connector Systems](#)
Product Name VHDM®
Style N/A
UPC 800753259799

Physical

Circuits (Loaded) 80
Circuits (maximum) 80
Color - Resin Black
Durability (mating cycles max) 200
First Mate / Last Break No
Flammability 94V-0
Guide to Mating Part Yes
Keying to Mating Part None
Material - Metal Beryllium Copper, High Performance Alloy (HPA), Stainless Steel

Material - Plating Mating Gold
Material - Plating Termination Tin-Lead
Material - Resin High Temperature Thermoplastic
Net Weight 8.162/g
Number of Columns 10
Number of Pairs Open Pin Field
Number of Rows 8
Orientation Vertical
PC Tail Length 2.50mm
PCB Locator No
PCB Retention None
PCB Thickness - Recommended 1.80mm
Packaging Type Tube
Pitch - Mating Interface 2.00mm
Pitch - Termination Interface 1.00mm
Plating min - Mating 0.762µm
Plating min - Termination 0.762µm
Polarized to PCB Yes




image - Reference only

Series

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[74062Series](#)

Mates With
74040 VHDM® Board-to-Board Daughtercard Receptacle

Application Tooling FAQ	
<i>Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.</i>	
Global	
Description	Product #
Insertion Module for Standard Shield Signal Header, 8-Row by 10-Wide, 20.00mm	0622020209
8-Row Pin and Shield Repair Tool	0622015900
Signal Pin Inserter Repair Tool	0622015700

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[74062-1003](#)