




MATERIAL BASE-NYLON 6/6 W/15% GLASS FIBRE (BLACK)
AR-nylon 6/6 W/30% GLASS FIBRE (BLACK)
CONNECTOR: 94V-0 POLYESTER W/30% GLASS FIBRE (BLACK)

OPERATING PARAMETERS

- 1.) OFF POINT: LESS THAN 15° ROTATION FROM REST POSITION
2.) ON POINT: GREATER THAN 2° ROTATION FROM REST POSITION

CONTACT RATINGS

CONTACT CAPACITY= 10 WATTS MAX.
SWITCHING VOLTAGE= 200 Vdc MAX.
SWITCHING CURRENT= .500 Adc MAX.
CONTACT RESISTANCE= .200 OHM MAX.




CONNECTOR PINS .025 IN², GOLD PLATED PHOSPHOR BRONZE

* KEY DIMENSIONS

ALL DIMENSIONS IN mm

ACTUATION FORCE 4 GRAMS NOMINAL

TOLERANCES: ±0,25 UNLESS OTHERWISE SPECIFIED



4 DIGIT DATE CODE

SWITCH ASSEMBLY										H A M L I N, Inc.		DCR No. 4008
AC	REVISE PACKAGING, REFORMAT		A3903	JC	7/30/96	JC	7/30/96		Dwn.	DATE	D10-59220-020	
REV.	DESCRIPTION OF REVISION		DCR No.	BY	DATE	APP.	DATE		App'd	RLB	DATE 12/19/88	
										Page 1 of 1		