


TRENCH
GENFET®

P-Channel Enhancement-Mode MOSFET

$V_{DS} - 30V$ $R_{DS(ON)} 20m\Omega$ $I_D - 8.0A$



Mechanical Data

Case: SO-8 molded plastic body

Terminals: Leads solderable per MIL-STD-750, Method 2026

High temperature soldering guaranteed:
250°C/10 seconds at terminals

Mounting Position: Any **Weight:** 0.5g

Features

- Advanced Trench Process Technology
- High Density Cell Design for Ultra Low On-Resistance
- Specially Designed for Low Voltage DC/DC Converters
- Fast Switching for High Efficiency

Maximum Ratings and Thermal Characteristics ($T_A = 25^\circ C$ unless otherwise noted)

Parameter	Symbol	Limit	Unit
Drain-Source Voltage	V_{DS}	-30	V
Gate-Source Voltage	V_{GS}	± 20	
Continuous Drain Current	I_D	-8.0	A
Pulsed Drain Current	I_{DM}	-50	
Maximum Power Dissipation	P_D	2.5 1.6	W
	$T_A = 25^\circ C$ $T_A = 70^\circ C$		
Operating Junction and Storage Temperature Range	T_J, T_{stg}	-55 to 150	$^\circ C$
Maximum Junction-to-Ambient Thermal Resistance ⁽¹⁾	$R_{\theta JA}$	50	$^\circ C/W$

Note: (1) Surface Mounted on FR4 Board, $t \leq 10$ sec.



P-Channel Enhancement-Mode MOSFET

Electrical Characteristics (T_J = 25°C unless otherwise noted)

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Static						
Gate Threshold Voltage	V _{GS(th)}	V _{DS} = V _{GS} , I _D = −250μA	−1.0	−	−3.0	V
Gate-Body Leakage	I _{GSS}	V _{DS} = 0V, V _{GS} = ±20V	−	−	±100	nA
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} = −30V, V _{GS} = 0V	−	−	−1.0	μA
On-State Drain Current ⁽¹⁾	I _{D(on)}	V _{DS} ≥ −5V, V _{GS} = −10V	−40	−	−	A
Drain-Source Breakdown Voltage	BV _{DSS}	V _{GS} = 0V, I _D = −250μA	−30	−	−	V
Drain-Source On-State Resistance ⁽¹⁾	R _{DS(on)}	V _{GS} = −10V, I _D = −8.0A	−	15.3	20	mΩ
		V _{GS} = −4.5V, I _D = −5.0A	−	25.3	35	
Forward Transconductance ⁽¹⁾	g _{fs}	V _{DS} = −15V, I _D = −8.0A	−	22	−	S
Dynamic						
Total Gate Charge	Q _g	V _{DS} = −15V, V _{GS} = −10V I _D = −4.6A	−	54	60	nC
Gate-Source Charge	Q _{gs}		−	8.5	−	
Gate-Drain Charge	Q _{gd}		−	10.3	−	
Turn-On Delay Time	t _{d(on)}	V _{DD} = −15V, R _L = 15Ω I _D ≈ −1A, V _{GEN} = −10V R _G = 6Ω	−	24	30	ns
Rise Time	t _r		−	12	30	
Turn-Off Delay Time	t _{d(off)}		−	78	120	
Fall Time	t _f		−	37	80	
Input Capacitance	C _{iSS}	V _{GS} = 0V	−	2520	−	pF
Output Capacitance	C _{oSS}	V _{DS} = −15V	−	490	−	
Reverse Transfer Capacitance	C _{rSS}	f = 1.0MHz	−	335	−	
Source-Drain Diode						
Maximum Diode Forward Current	I _S		−	−	−2.1	A
Diode Forward Voltage	V _{SD}	I _S = −2.1A, V _{GS} = 0V	−	−0.75	−1.2	V

Note:

(1) Pulse test; pulse width ≤ 300 μs,
duty cycle ≤ 2%



P-Channel Enhancement-Mode MOSFET

Ratings and Characteristic Curves ($T_A = 25^\circ\text{C}$ unless otherwise noted)

Fig. 1 – Output Characteristics




Fig. 2 – Transfer Characteristics




Fig. 3 – Threshold Voltage
vs. Temperature




Fig. 4 – On-Resistance
vs. Drain Current





Fig. 5 – On-Resistance
vs. Junction Temperature



P-Channel Enhancement-Mode MOSFET

Ratings and Characteristic Curves ($T_A = 25^\circ\text{C}$ unless otherwise noted)

**Fig. 6 – On-Resistance
vs. Gate-to-Source Voltage**




Fig. 7 – Gate Charge






Fig. 8 – Capacitance




**Fig. 9 – Source-Drain Diode
Forward Voltage**



P-Channel Enhancement-Mode MOSFET

Ratings and Characteristic Curves ($T_A = 25^\circ\text{C}$ unless otherwise noted)

**Fig. 10 – Breakdown Voltage
vs. Junction Temperature**



**Fig. 11 – Transient Thermal
Impedance**




Fig. 12 – Power vs. Pulse Duration




Fig. 13 – Maximum Safe Operating Area

