

1


2

3


4

PRODUCT NUMBER
XXXXX-YYYHTLF


- LEAD FREE OPTION
SEE NOTE 1,10
- TUBE PACKAGING OPTION
SEE NOTE 1
- HIGH TEMPERATURE PLASTIC
SEE NOTE 1
- NO. OF
POSITIONS
SEE NOTE 1
- PIN PLATING
SEE SHEET 2
- BASE PART NO.




TOP VIEW



RECOMMENDED HOLE PATTERN




SIDE VIEW



END VIEW

⊕ ∅ .020/.51 (M) U (M) V (S)

NOTE 4



DETAIL P
TYP BOTH ENDS

ELX-N-16105

rev	ecn no	dr	date
AP	ELX-N-16105	ZK	2013-10-22
AJ	M05-0072	MHT	5/03/05
AK	M06-0269	MHT	7/17/06
AL	M06-0346	MHT	9/04/06
AM	M08-0291	MHT	10/06/08
AN	N11-0118	J.Z	2011-04-12

www.fciconnect.com			surface 6.4 ISO 1302	tolerance std ISO 406 ISO 1101	projection size A4	INCH/MM Scale 1.000
Dr	T. BREWBAKER	7/29/94	TOLERANCES UNLESS OTHERWISE SPECIFIED		size	ECN
Eng	T.HANNA	7/29/94	ANGULAR	LINEAR	0.X ±.03	0.XX ±.015
Chr	J. MURPHY	7/29/94	0° ±2°	0.XXX ±.05	ECN	Spec ref
Appr	T.HANNA	7/29/94	Product family		BERGSTIK	69192
FCI			title		BERGSTIK® II HEADER .100/2.54 DR SELF-RET	Rev. AP
			catalog no		CUSTOMER	sheet 1 of 4

1

2

3

4

PIN PLATING CODES:

XXXX-1YY	30u"/0.76u MIN (SEE NOTE 11) OVER 50u"/1.27u MIN Ni
XXXX-2YY	15u"/0.38u MIN (SEE NOTE 11) OVER 50u"/1.27u MIN Ni
XXXX-3YY	50u"/1.27u MIN (SEE NOTE 11) OVER 50u"/1.27u MIN Ni
XXXX-4YY	100u"/2.54u MIN Sn OVER 50u"/1.27u MIN Ni (SEE NOTE 12)
XXXX-4YYHLF	
XXXX-5YY	15u"/0.38u MIN (SEE NOTE 11) OVER 50u"/1.27u MIN Ni
XXXX-6YY	30u"/0.76u MIN (SEE NOTE 11) OVER 50u"/1.27u MIN Ni
XXXX-7YY	30u"/0.76u MIN (SEE NOTE 11) OVER 50u"/1.27u MIN Ni
XXXX-8YY	15u"/0.38u MIN (SEE NOTE 11) OVER 50u"/1.27u MIN Ni
XXXX-9YY	15u"/0.38u MIN (SEE NOTE 11) OVER 50u"/1.27u MIN Ni
XXXX-0YY	30u"/0.76u MIN (SEE NOTE 11) OVER 50u"/1.27u MIN Ni

NOTES

(1) PART NUMBER OPTIONS:

PIN PLATING CODES (SEE ABOVE)

HIGH TEMP. MATERIAL:

FOR HIGH-TEMPERATURE APPLICATIONS, SPECIFY AN "H" AT THE END OF THE PART NUMBER, AND PCT WILL BE SUPPLIED.

NUMBER OF POSITION:

ANY NUMBER OF POSITIONS FROM 2 (2X1) THRU 72 (2X36).

PACKAGING:

PACKAGED IN POLY BAGS.

EIGHT DIGIT PART NUMBERS FOLLOWED BY A "T" ARE PACKAGED IN TUBES. SEE SPECIFIC PART NUMBERS FOR AVAILABILITY.

LEAD FREE:

ADD "HLF" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION, NOT AVAILABLE FOR -5YY,-5YYH,-6YY & -6YYH.

(2) BODY MATERIAL:

MANUFACTURER'S OPTION OF NYLON OR PCT, GLASS FIBER REINFORCED, FLAME RETARDANT PER UL-94V-0.

COLOR: BLACK. OR

MINERAL FILLED LCP, COLOR BLACK

FLAME RETARDANT PER UL-94V-0

PART NUMBERS WITH "H" SUFFIX WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 20 SECONDS IN WAVE SOLDER, INFRA-RED OR VAPOR PHASE SOLDER PROCESS.

PART NUMBERS WITHOUT "H" SUFFIX WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR WAVE SOLDER PROCESS.

(3) PIN MATERIAL: PHOS-BRONZE.

(4) MEASURED WITH PART IN RESTRAINED CONDITION.

5. TWO SIDES OF PIN TIPS NOT PLATED. TYPICAL BOTH ENDS.

(6) 2LBS/0.9KG MIN PIN RETENTION IN EITHER DIRECTION.

(7) ±0.10/0.25 TOL. APPLIES TO ALL "G" TAILS EXCEPT INDICATED PARTS ON TABLE WHERE +0.10/0.25,-.000/0.00 APPLIES.

(8) SECTION R-R DIMENSIONS APPLY TO RETENTION PIN POSITIONS ONLY LOCATED AT MANUFACTURES OPTION.

9. 5LB/2.3KG MAX INSERTION FORCE AND .25LB/.1KG MIN RETENTION FORCE PER RETENTIVE PIN USING .062/1.57 THICK CIRCUIT BOARDS AND RECOMMENDED HOLE PATTERN.

(10) THESE PRODUCTS MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.

(11) PLATING OPTIONS:




PERFORMANCE PLATING WILL BE EITHER GOLD OR GXT ON POST OR TAIL, OPTIONALLY (78~295u"/2~7.5u) TIN ON TAIL.

(12) "THIS PRODUCT HAS 100% TIN PLATING IN THE INTERFACE AND HAS NOT BEEN TESTED FOR WHISKER GROWTH IN ALL INTERCONNECT ENVIRONMENTS."

www.fciconnect.com			surface ISO 1302 ✓		tolerance std ISO 406 ISO 1101		projection 		INCH/MM 	
			TOLERANCES UNLESS		OTHERWISE SPECIFIED					
Dr	T. BREWBAKER	7/29/94	ANGULAR	LINEAR	0.X ±0.3		size A4	Scale 1.000		
Eng	T.HANNA	7/29/94			0.XX ±0.15					
Chr	J. MURPHY	7/29/94			0.XXX ±0.05					
Appr	T.HANNA	7/29/94	Product family		BERGSTIK		Spec ref			
	title				BERGSTIK® II HEADER .100/2.54 DR SELF-RET		dwg no 69192		Rev AP	
	catalog no						CUSTOMER		sheet 2 of 4	



Copyright FCI.



www.fciconnect.com			surface ISO 1302 ✓		tolerance std ISO 406 ISO 1101		projection 		INCH/MM 	
			TOLERANCES UNLESS		OTHERWISE SPECIFIED					
Dr	T. BREWBAKER	7/29/94	ANGULAR	LINEAR	0.X	±0.3	size A4	Scale 1.000		
Eng	T.HANNA	7/29/94			0.XX	±0.15				
Chr	J. MURPHY	7/29/94	0°	±2°	0.XXX	±0.05	ECN			
Appr	T.HANNA	7/29/94	Product family				BERGSTIK		Spec ref	
	title BERGSTIK® II HEADER .100/2.54 DR SELF-RET				dwg no 69192				Rev. AP	
	catalog no				CUSTOMER				sheet 3 of 4	

A

B

C

Copyright FCI.

D

PRODUCT NUMBER	TOTAL PIN LENGTH		TAIL LENGTH		MATING LENGTH			
	DIM F	DIM F	DIM G	DIM G	DIM H	DIM H		
	ENGLISH	METRIC	ENGLISH	METRIC	ENGLISH	METRIC	PACKAGING	NOTES
69192-YYY	0.450	11.43	0.120	3.05	0.230	5.84	POLY BAGS/TUBES	
78252-YYY	U N A V A I L A B L E							
78548-YYY	0.538	13.67	0.120	3.05	0.318	8.08	POLY BAGS	
78577-YYY	0.650	16.51	0.120	3.05	0.430	10.92	POLY BAGS	
79214-YYY	0.620	15.75	0.120	3.05	0.400	10.16	POLY BAGS	
79979-YYY	0.450	11.43	0.120	3.05	0.230	5.84	POLY BAGS/TUBES	7
86380-YYY	0.470	11.94	0.120	3.05	0.250	6.35	POLY BAGS	
86584-YYY	0.760	19.30	0.120	3.05	0.540	13.72	POLY BAGS	
87444-YYY	1.090	27.69	0.125	3.18	0.865	21.97	POLY BAGS	
87456-YYY	0.840	21.34	0.120	3.05	0.620	15.75	POLY BAGS	
87457-YYY	0.990	25.15	0.120	3.05	0.770	19.56	POLY BAGS	
87837-YYY	0.585	14.86	0.120	3.05	0.365	9.27	POLY BAGS	
87920-YYY	0.830	21.08	0.120	3.05	0.610	15.49	POLY BAGS	
88526-YYY	1.340	34.04	0.120	3.05	1.120	28.45	POLY BAGS	
88714-YYY	0.640	16.26	0.120	3.05	0.420	10.67	POLY BAGS	
89580-YYY	0.930	23.62	0.120	3.05	0.710	18.03	POLY BAGS	
90824-YYY	0.420	10.67	0.120	3.05	0.200	5.08	POLY BAGS	
94654-XXYH	0.415	10.54	0.085	2.16	0.230	5.84	POLY BAGS	
95066-XXYH	1.240	31.50	0.120	3.05	1.020	25.91	POLY BAGS	
95654-XXYH	0.880	22.35	0.120	3.05	0.660	16.76	POLY BAGS	
98845-XXYH	0.572	14.54	0.120	3.00	0.354	9.00	POLY BAGS/TUBES	
10002463-XXYH	0.503	12.78	0.085	2.16	0.318	8.08	POLY BAGS	

LF

OPTION

NOTE 1,10

OB

OB

OB

OB

OB

OB

OB

OB

OB

OB

OB

OB

NOTE 1,10

OB

OB

OB

A

B

C

D

www.fciconnect.com			surface ISO 1302 ✓		tolerance std ISO 406 ISO 1101		projection 		INCH/MM ←————→				
			TOLERANCES UNLESS		OTHERWISE SPECIFIED								
Dr	T. BREWBAKER	7/29/94	ANGULAR	LINEAR	0.X	±0.3	size	A4	Scale 1.000				
Eng	T.HANNA	7/29/94			0.XX	±0.15							
Chr	J. MURPHY	7/29/94			0.XXX	±0.05	ECN						
Appr	T.HANNA	7/29/94	Product family			BERGSTIK		Spec ref					
	title					BERGSTIK® II HEADER					dwg no	69192	Rev AP
						.100/2.54 DR SELF-RET							
	catalog no												
					CUSTOMER					sheet 4 of 4			