



## AAP Gen 7 (TO-240AA) Power Modules Standard Diodes, 80 A

**AAP Gen 7 (TO-240AA)****RoHS**  
COMPLIANT**FEATURES**

- High voltage
- Industrial standard package
- Low thermal resistance
- UL approved file E78996 
- Designed and qualified for industrial level
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)

**BENEFITS**

- Excellent thermal performances obtained by the usage of exposed direct bonded copper substrate
- Up to 1600 V
- High surge capability
- Easy mounting on heatsink

**ELECTRICAL DESCRIPTION**

These modules are intended for general purpose high voltage applications such as high voltage regulated power supplies, lighting circuits, temperature and motor speed control circuits, UPS and battery charger.

**PRIMARY CHARACTERISTICS**

|                       |                                                                                              |
|-----------------------|----------------------------------------------------------------------------------------------|
| $I_{F(AV)}$           | 80 A                                                                                         |
| Type                  | Modules - Diode, High Voltage                                                                |
| Package               | AAP Gen 7 (TO-240AA)                                                                         |
| Circuit configuration | Two diodes doubler circuit, two diodes common cathode, two diodes common anode, single diode |

**MECHANICAL DESCRIPTION**

The AAP Gen 7 (TO-240AA), new generation of AAP module, combines the excellent thermal performances obtained by the usage of exposed direct bonded copper substrate, with advanced compact simple package solution and simplified internal structure with minimized number of interfaces.

**MAJOR RATINGS AND CHARACTERISTICS**

| SYMBOL         | CHARACTERISTICS | VALUES      | UNITS              |
|----------------|-----------------|-------------|--------------------|
| $I_{F(AV)}$    |                 | 80          | A                  |
|                | $T_C$           | 110         | °C                 |
| $I_{F(RMS)}$   |                 | 126         | A                  |
| $I_{FSM}$      | 50 Hz           | 1500        |                    |
|                | 60 Hz           | 1570        |                    |
| $I^2t$         | 50 Hz           | 11.25       | kA <sup>2</sup> s  |
|                | 60 Hz           | 10.26       |                    |
| $I^2\sqrt{t}$  |                 | 112.5       | kA <sup>2</sup> √s |
| $V_{RRM}$      | Range           | 400 to 1600 | V                  |
| $T_{Stg}, T_J$ |                 | -40 to +150 | °C                 |


**ELECTRICAL SPECIFICATIONS**

| <b>VOLTAGE RATINGS</b> |              |                                                          |                                                              |                                                                |
|------------------------|--------------|----------------------------------------------------------|--------------------------------------------------------------|----------------------------------------------------------------|
| TYPE NUMBER            | VOLTAGE CODE | $V_{RRM}$ , MAXIMUM REPETITIVE PEAK REVERSE VOLTAGE<br>V | $V_{RSM}$ , MAXIMUM NON-REPETITIVE PEAK REVERSE VOLTAGE<br>V | $I_{RRM}$ MAXIMUM AT $T_J = 150\text{ }^{\circ}\text{C}$<br>mA |
| VS-VSK.71              | 04           | 400                                                      | 500                                                          | 10                                                             |
|                        | 06           | 600                                                      | 700                                                          |                                                                |
|                        | 08           | 800                                                      | 900                                                          |                                                                |
|                        | 10           | 1000                                                     | 1100                                                         |                                                                |
|                        | 12           | 1200                                                     | 1300                                                         |                                                                |
|                        | 14           | 1400                                                     | 1500                                                         |                                                                |
|                        | 16           | 1600                                                     | 1700                                                         |                                                                |

| FORWARD CONDUCTION                                            |                     |                                                                                                           |                        |                                                                       |        |                    |
|---------------------------------------------------------------|---------------------|-----------------------------------------------------------------------------------------------------------|------------------------|-----------------------------------------------------------------------|--------|--------------------|
| PARAMETER                                                     | SYMBOL              | TEST CONDITIONS                                                                                           |                        |                                                                       | VALUES | UNITS              |
| Maximum average forward current at case temperature           | I <sub>F(AV)</sub>  | 180° conduction, half sine wave                                                                           |                        |                                                                       | 80     | A                  |
|                                                               |                     |                                                                                                           |                        |                                                                       | 110    | °C                 |
| Maximum RMS forward current                                   | I <sub>F(RMS)</sub> |                                                                                                           |                        |                                                                       | 126    |                    |
| Maximum peak, one-cycle forward, non-repetitive surge current | I <sub>FSM</sub>    | t = 10 ms                                                                                                 | No voltage reappplied  | Sinusoidal half wave, initial T <sub>J</sub> = T <sub>J</sub> maximum | 1500   | A                  |
|                                                               |                     | t = 8.3 ms                                                                                                |                        |                                                                       | 1570   |                    |
|                                                               |                     | t = 10 ms                                                                                                 | 100 % V <sub>RRM</sub> |                                                                       | 1260   |                    |
|                                                               |                     | t = 8.3 ms                                                                                                | reappplied             |                                                                       | 1320   |                    |
| Maximum I <sup>2</sup> t for fusing                           | I <sup>2</sup> t    | t = 10 ms                                                                                                 | No voltage reappplied  |                                                                       | 11.25  | kA <sup>2</sup> s  |
|                                                               |                     | t = 8.3 ms                                                                                                |                        |                                                                       | 10.26  |                    |
|                                                               |                     | t = 10 ms                                                                                                 | 100 % V <sub>RRM</sub> |                                                                       | 7.95   |                    |
|                                                               |                     | t = 8.3 ms                                                                                                | reappplied             |                                                                       | 7.23   |                    |
| Maximum I <sup>2</sup> √t for fusing                          | I <sup>2</sup> √t   | t = 0.1 ms to 10 ms, no voltage reappplied                                                                |                        |                                                                       | 112.5  | kA <sup>2</sup> √s |
| Low level value of threshold voltage                          | V <sub>F(TO)1</sub> | (16.7 % × π × I <sub>F(AV)</sub> ) < I < π × I <sub>F(AV)</sub> , T <sub>J</sub> = T <sub>J</sub> maximum |                        |                                                                       | 0.73   | V                  |
| High level value of threshold voltage                         | V <sub>F(TO)2</sub> | (I > π × I <sub>F(AV)</sub> ), T <sub>J</sub> = T <sub>J</sub> maximum                                    |                        |                                                                       | 0.83   |                    |
| Low level value of forward slope resistance                   | r <sub>f1</sub>     | (16.7 % × π × I <sub>F(AV)</sub> ) < I < π × I <sub>F(AV)</sub> , T <sub>J</sub> = T <sub>J</sub> maximum |                        |                                                                       | 3.22   | mΩ                 |
| High level value of forward slope resistance                  | r <sub>f2</sub>     | (I > π × I <sub>F(AV)</sub> ), T <sub>J</sub> = T <sub>J</sub> maximum                                    |                        |                                                                       | 2.89   |                    |
| Maximum forward voltage drop                                  | V <sub>FM</sub>     | I <sub>FM</sub> = π × I <sub>F(AV)</sub> , T <sub>J</sub> = 25 °C, t <sub>p</sub> = 400 μs square wave    |                        |                                                                       | 1.6    | V                  |

| BLOCKING                             |                  |                         |                            |       |
|--------------------------------------|------------------|-------------------------|----------------------------|-------|
| PARAMETER                            | SYMBOL           | TEST CONDITIONS         | VALUES                     | UNITS |
| Maximum peak reverse leakage current | I <sub>RRM</sub> | T <sub>J</sub> = 150 °C | 10                         | mA    |
| Maximum RMS insulation voltage       | V <sub>INS</sub> | 50 Hz                   | 3000 (1 min)<br>3600 (1 s) | V     |



| THERMAL AND MECHANICAL SPECIFICATIONS                         |                |                                                                                                                                          |                      |       |
|---------------------------------------------------------------|----------------|------------------------------------------------------------------------------------------------------------------------------------------|----------------------|-------|
| PARAMETER                                                     | SYMBOL         | TEST CONDITIONS                                                                                                                          | VALUES               | UNITS |
| Junction and storage temperature range                        | $T_J, T_{Stg}$ |                                                                                                                                          | -40 to +150          | °C    |
| Maximum internal thermal resistance, junction to case per leg | $R_{thJC}$     | DC operation                                                                                                                             | 0.28                 | °C/W  |
| Typical thermal resistance, case to heatsink per module       | $R_{thCS}$     | Mounting surface flat, smooth and greased                                                                                                | 0.1                  |       |
| Mounting torque $\pm 10\%$ to heatsink<br>busbar              |                | A mounting compound is recommended and the torque should be rechecked after a period of 3 hours to allow for the spread of the compound. | 4                    | Nm    |
|                                                               |                |                                                                                                                                          | 3                    |       |
| Approximate weight                                            |                |                                                                                                                                          | 75                   | g     |
|                                                               |                |                                                                                                                                          | 2.7                  | oz.   |
| Case style                                                    |                | JEDEC®                                                                                                                                   | AAP Gen 7 (TO-240AA) |       |

| $\Delta R$ CONDUCTION PER JUNCTION |                           |       |       |       |       |                             |       |      |       |      |       |
|------------------------------------|---------------------------|-------|-------|-------|-------|-----------------------------|-------|------|-------|------|-------|
| DEVICES                            | SINE HALF WAVE CONDUCTION |       |       |       |       | RECTANGULAR WAVE CONDUCTION |       |      |       |      | UNITS |
|                                    | 180°                      | 120°  | 90°   | 60°   | 30°   | 180°                        | 120°  | 90°  | 60°   | 30°  |       |
| VSK.71                             | 0.075                     | 0.088 | 0.113 | 0.155 | 0.228 | 0.06                        | 0.094 | 0.12 | 0.158 | 0.23 | °C/W  |

## Note

- Table shows the increment of thermal resistance  $R_{thJC}$  when devices operate at different conduction angles than DC




Fig. 1 - Current Ratings Characteristics




Fig. 4 - Forward Power Loss Characteristics




Fig. 2 - Current Ratings Characteristics




Fig. 5 - Maximum Non-Repetitive Surge Current




Fig. 3 - Forward Power Loss Characteristics




Fig. 6 - Maximum Non-Repetitive Surge Current




Fig. 7 - Forward Power Loss Characteristics




Fig. 8 - Forward Power Loss Characteristics




Fig. 9 - Forward Power Loss Characteristics




Fig. 10 - Forward Voltage Characteristics




Fig. 11 - Thermal Impedance  $Z_{thJC}$  Characteristics





## ORDERING INFORMATION TABLE

| Device code | VS-VS                                                   | K | D | 71 | / | 16 |
|-------------|---------------------------------------------------------|---|---|----|---|----|
|             | 1                                                       | 2 | 3 | 4  |   | 5  |
| 1           | Vishay Semiconductors product                           |   |   |    |   |    |
| 2           | Module type                                             |   |   |    |   |    |
| 3           | Circuit configuration (see Circuit Configuration table) |   |   |    |   |    |
| 4           | Current code (80 A)                                     |   |   |    |   |    |
| 5           | Voltage code (see Voltage Ratings table)                |   |   |    |   |    |

### Note

- To order the optional hardware go to [www.vishay.com/doc?95172](http://www.vishay.com/doc?95172)



| CIRCUIT CONFIGURATION      |                            |                                                                                                            |
|----------------------------|----------------------------|------------------------------------------------------------------------------------------------------------|
| CIRCUIT DESCRIPTION        | CIRCUIT CONFIGURATION CODE | CIRCUIT DRAWING                                                                                            |
| Two diodes doubler circuit | D                          | <p><b>VSKD...</b></p>    |
| Two diodes common cathode  | C                          | <p><b>VSKC...</b></p>    |
| Two diodes common anode    | J                          | <p><b>VSKJ...</b></p>   |
| Single diode               | E                          | <p><b>VSKE...</b></p>  |

| LINKS TO RELATED DOCUMENTS |                                                                        |
|----------------------------|------------------------------------------------------------------------|
| Dimensions                 | <a href="http://www.vishay.com/doc?95369">www.vishay.com/doc?95369</a> |

## ADD-A-PAK Generation VII - Diode

**DIMENSIONS** in millimeters (inches)





## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.