


# Type FCN Surface Mount Film Capacitors

## Stable Stacked Metallized Film (PEN) Chips for Reflow Soldering



Type FCN capacitors are designed for applications requiring a general purpose SMT capacitor with stable temperature and frequency characteristics similar to polyester film capacitors. They are ideal for applications such as EMI noise filtering, power supply input/output filters, audio or signal coupling, and IC power bus bypassing or decoupling. FCN SMT capacitors have a non-inductive stacked metallized PEN film construction which results in a low ESR and excellent high frequency performance.

### Highlights

- Designed for reflow soldering
- Withstands 150% of rated voltage for 60 seconds
- Stacked metallized polyethylene naphthalate (PEN) film
- Performs like polyester capacitors
- Nonmagnetic and lead-free

Type FCN SMT capacitors are the general purpose line of CDE's surface mount product offerings. They range in capacitance from .001  $\mu\text{F}$  to 1.0  $\mu\text{F}$ , and they are available in voltage ratings up to 400 Vdc.

### Specifications


|                                    |                                                                                                                                                                                                                                                                                                                               |
|------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Capacitance Range                  | 1000 pF to 1.0 $\mu\text{F}$ (1kHz at $\leq 5 \text{ Vrms}$ )                                                                                                                                                                                                                                                                 |
| Capacitance Tolerance              | $\pm 5\%$ (J), $\pm 10\%$ (K) (See Ratings)                                                                                                                                                                                                                                                                                   |
| Rated Voltage                      | 16, 50, 100, 250 & 400 Vdc                                                                                                                                                                                                                                                                                                    |
| Dissipation Factor (Tan $\delta$ ) | 1.0% Max. (1 kHz at 5 Vrms)                                                                                                                                                                                                                                                                                                   |
| Operating Temperature Range        | 16, 50, 100Vdc ( $< 0.012 \mu\text{F}$ ); $-55^\circ\text{C}$ to $+105^\circ\text{C}$<br>100 Vdc ( $\geq 0.012 \mu\text{F}$ ), 250, 400 Vdc; $-40^\circ\text{C}$ to $+85^\circ\text{C}$                                                                                                                                       |
| Surface Temperature                | 16 V & 50 V & 100 V $\leq 0.01 \mu\text{F}$ : 240 $^\circ\text{C}$ max<br>100 V $\geq 0.012 \mu\text{F}$ , 250 V & 400 V: 230 $^\circ\text{C}$ max                                                                                                                                                                            |
| Insulation Resistance              | C $> 0.33 \mu\text{F}$ : IR = 1000 $\text{M}\Omega \cdot \mu\text{F}$ Min.<br>C $\leq 0.33 \mu\text{F}$ : IR $\geq 3000 \text{ M}\Omega$                                                                                                                                                                                      |
| Construction                       | Stacked metallized polyphenylene sulfide (PPS) film. Terminations are lead free with a Sn-Ag-Cu solder finish.                                                                                                                                                                                                                |
| Withstand Voltage                  | 16 V & 50 V, 100 V $\leq 0.01 \mu\text{F}$ : 175% rated voltage, 5 s<br>100 V $\geq 0.012 \mu\text{F}$ , 250 V and 400 V: 150% rated voltage, 5 s                                                                                                                                                                             |
| Life Test                          | 1000 h at rated temp. & 125% rated voltage<br>$\Delta$ Capacitance: +1%, -6% max<br>Dissipation Factor: 1.1% max<br>IR: 1000 $\text{M}\Omega \cdot \text{min}$ (C $> 0.33 \mu\text{F}$ , 300 $\text{M}\Omega \cdot \mu\text{F}$ min)<br>No significant visual damage                                                          |
| Resistance to Soldering Heat       | 5 s at max capacitor surface temperature<br>$\Delta$ Capacitance: $\pm 5\%$ max<br>Dissipation Factor: 1.1% max<br>IR: 1000 $\text{M}\Omega \cdot \text{min}$ (C $> 0.33 \mu\text{F}$ , 300 $\text{M}\Omega \cdot \mu\text{F}$ min)<br>Voltage withstanding: 1.5 times rated voltage, 1 min.<br>No significant visual damage. |
| Moisture Resistance                | 500 h at 85 $^\circ\text{C}$ and 85% RH<br>$\Delta$ Capacitance: $\pm 10\%$ max<br>Dissipation Factor: 2% max<br>IR: 10 $\text{M}\Omega \cdot \text{min}$ (C $> 0.33 \mu\text{F}$ , 3 $\text{M}\Omega \cdot \mu\text{F}$ min)<br>Voltage withstanding: 1.3 times rated voltage, 1 min.<br>No significant damage               |
| RoHS Compliant                     |                                                                                                                                                                                                                                                                                                                               |

# Type FCN Surface Mount Film Capacitors

## Part Numbering System

| FCN  | 1206      | A           | 102                 | J             | H2         |   | Tape          | Tape                   | Reel     |
|------|-----------|-------------|---------------------|---------------|------------|---|---------------|------------------------|----------|
| Type | Case Size | Voltage     | Capacitance         | Tolerance     | Packaging  |   | Width<br>(mm) | Diameter<br>[in. (mm)] | Quantity |
| FCN  | 1206      | C = 16 Vdc  | 102 = 0.001 $\mu$ F | J = $\pm$ 5%  | K1         | = | 8             | 7 (178)                | 4000     |
|      | 1913      | H = 50 Vdc  | 223 = 0.022 $\mu$ F | K = $\pm$ 10% | J1, J2     | = | 8             | 7 (178)                | 3000     |
|      | 2416      | A = 100 Vdc | 474 = 0.47 $\mu$ F  |               | H1, H2     | = | 8             | 7 (178)                | 3000     |
|      | 2420      | E = 250 Vdc |                     |               | H3         | = | 8             | 7 (178)                | 2000     |
|      | 2820      | G = 400 Vdc |                     |               | G1, G2, G3 | = | 8             | 7 (178)                | 2000     |
|      | 3022      |             |                     |               | E1, E2     | = | 12            | 13 (330)               | 3000     |
|      | 3925      |             |                     |               | E3, E4     | = | 12            | 13 (330)               | 2000     |
|      | 3931      |             |                     |               | D1, D2     | = | 12            | 13 (330)               | 3000     |
|      | 6031      |             |                     |               | D3, D4, D5 | = | 12            | 13 (330)               | 2000     |
|      | 6040      |             |                     |               | B, Z       | = | 12            | 13 (330)               | 1500     |
|      |           |             |                     |               | U, V, X, Y | = | 16            | 13 (330)               | 1000     |
|      |           |             |                     |               | S, T       | = | 24            | 13 (330)               | 750      |

## Outline Drawing



t = 0.014  $\pm$  0.008 in. (0.35  $\pm$  0.2 mm)

For 0.001  $\mu$ F – 0.01  $\mu$ F, 100 V, t = 0.026  $\pm$  0.012 in. (0.62  $\pm$  0.3 mm)

## Ratings

| Rated Voltage: 16 Vdc (12 Vac)           |                 | Operating Temperature Range: -55 to +105°C                                                                                      |                             |                             |
|------------------------------------------|-----------------|---------------------------------------------------------------------------------------------------------------------------------|-----------------------------|-----------------------------|
| Capacitance Range: 0.12 to 0.47 μF       |                 | Dielectric Withstand Voltage: 28 Vdc for 5 seconds                                                                              |                             |                             |
| Capacitance Tolerance: ± 5% (J)          |                 | Insulation Resistance (20°C, 10 Vdc, 60 Seconds);<br>For ≤ 0.39 μF, I.R. ≥ 3000 MegΩ<br>For > 0.39 μF, I.R. = 1000 MegΩ•μF Min. |                             |                             |
| D.F. (20°C, 1 kHz): ≤ 1%                 |                 |                                                                                                                                 |                             |                             |
| Max. capacitor surface temperature: 40°C |                 |                                                                                                                                 |                             |                             |
| Capacitance (μF)                         | CDE P.N.        | L ±.008 (±0.2)<br>[in.(mm)]                                                                                                     | W ±.012 (±0.3)<br>[in.(mm)] | T ±.008 (±0.2)<br>[in.(mm)] |
| 0.12                                     | FCN1913C124J-E1 | 0.189 (4.8)                                                                                                                     | 0.130 (3.3)                 | 0.055 (1.4)                 |
| 0.15                                     | FCN1913C154J-E2 | 0.189 (4.8)                                                                                                                     | 0.130 (3.3)                 | 0.079 (2.0)                 |
| 0.18                                     | FCN1913C184J-E2 | 0.189 (4.8)                                                                                                                     | 0.130 (3.3)                 | 0.079 (2.0)                 |
| 0.22                                     | FCN1913C224J-E4 | 0.189 (4.8)                                                                                                                     | 0.130 (3.3)                 | 0.094 (2.4)                 |
| 0.27                                     | FCN2416C274J-D1 | 0.236 (6.0)                                                                                                                     | 0.161 (4.1)                 | 0.071 (1.8)                 |
| 0.33                                     | FCN2416C334J-D2 | 0.236 (6.0)                                                                                                                     | 0.161 (4.1)                 | 0.079 (2.0)                 |
| 0.39                                     | FCN2416C394J-D3 | 0.236 (6.0)                                                                                                                     | 0.161 (4.1)                 | 0.094 (2.4)                 |
| 0.47                                     | FCN2416C474J-D4 | 0.236 (6.0)                                                                                                                     | 0.161 (4.1)                 | 0.110 (2.8)                 |

# Type FCN Surface Mount Film Capacitors

| <b>Rated Voltage:</b> 50 Vdc (40 Vac)            |                 | <b>Operating Temperature Range:</b> -55 to +105°C                                   |                                     |                                     |
|--------------------------------------------------|-----------------|-------------------------------------------------------------------------------------|-------------------------------------|-------------------------------------|
| <b>Capacitance Range:</b> 0.056 to 0.22 µF       |                 | <b>Dielectric Withstand Voltage:</b> 87.5 Vdc for 5 seconds                         |                                     |                                     |
| <b>Capacitance Tolerance:</b> ± 5% (J)           |                 | <b>Insulation Resistance (20°C, 50 Vdc, 60 Seconds);</b><br><b>I.R. ≥ 3000 MegΩ</b> |                                     |                                     |
| <b>D.F. (20°C, 1 kHz):</b> ≤ 1%                  |                 |                                                                                     |                                     |                                     |
| <b>Max. capacitor surface temperature:</b> 210°C |                 |                                                                                     |                                     |                                     |
| <b>Capacitance (µF)</b>                          | <b>CDE P.N.</b> | <b>L ±.008 (±0.2)<br/>[in.(mm)]</b>                                                 | <b>W ±.012 (±0.3)<br/>[in.(mm)]</b> | <b>T ±.008 (±0.2)<br/>[in.(mm)]</b> |
| <b>0.056</b>                                     | FCN1913H563J-E2 | 0.189 (4.8)                                                                         | 0.130 (3.3)                         | 0.079 (2.0)                         |
| <b>0.068</b>                                     | FCN1913H683J-E2 | 0.189 (4.8)                                                                         | 0.130 (3.3)                         | 0.079 (2.0)                         |
| <b>0.082</b>                                     | FCN1913H823J-E4 | 0.189 (4.8)                                                                         | 0.130 (3.3)                         | 0.094 (2.4)                         |
| <b>0.10</b>                                      | FCN1913H104J-E3 | 0.189 (4.8)                                                                         | 0.130 (3.3)                         | 0.110 (2.8)                         |
| <b>0.12</b>                                      | FCN2416H124J-D1 | 0.236 (6.0)                                                                         | 0.161 (4.1)                         | 0.071 (1.8)                         |
| <b>0.15</b>                                      | FCN2416H154J-D2 | 0.236 (6.0)                                                                         | 0.161 (4.1)                         | 0.079 (2.0)                         |
| <b>0.18</b>                                      | FCN2416H184J-D3 | 0.236 (6.0)                                                                         | 0.161 (4.1)                         | 0.094 (2.4)                         |
| <b>0.22</b>                                      | FCN2416H224J-D4 | 0.236 (6.0)                                                                         | 0.161 (4.1)                         | 0.110 (2.8)                         |

|                                                  |                 |                                                                                          |                                     |                                     |
|--------------------------------------------------|-----------------|------------------------------------------------------------------------------------------|-------------------------------------|-------------------------------------|
| <b>Rated Voltage:</b> 100 Vdc (63 Vac)           |                 | <b>Operating Temperature Range:</b> -55 to +105°C                                        |                                     |                                     |
| <b>Capacitance Range:</b> 0.001 to 0.010 μF      |                 | <b>Dielectric Withstand Voltage:</b> 175 Vdc for 5 seconds                               |                                     |                                     |
| <b>Capacitance Tolerance:</b> ± 5% (J)           |                 | <b>Insulation Resistance (20°C, 100 Vdc, 60 Seconds);</b><br><br><b>I.R. ≥ 3000 MegΩ</b> |                                     |                                     |
| <b>D.F. (20°C, 1 kHz):</b> ≤ 1%                  |                 |                                                                                          |                                     |                                     |
| <b>Max. capacitor surface temperature: 240°C</b> |                 |                                                                                          |                                     |                                     |
| <b>Capacitance (μF)</b>                          | <b>CDE P.N.</b> | <b>L ±.008 (±0.2)<br/>[in.(mm)]</b>                                                      | <b>W ±.008 (±0.2)<br/>[in.(mm)]</b> | <b>T ±.008 (±0.2)<br/>[in.(mm)]</b> |
| 0.001                                            | FCN1206A102J-H2 | 0.126 (3.2)                                                                              | 0.063 (1.6)                         | 0.043 (1.1)                         |
| 0.0012                                           | FCN1206A122J-H2 | 0.126 (3.2)                                                                              | 0.063 (1.6)                         | 0.043 (1.1)                         |
| 0.0015                                           | FCN1206A152J-H2 | 0.126 (3.2)                                                                              | 0.063 (1.6)                         | 0.043 (1.1)                         |
| 0.0018                                           | FCN1206A182J-H2 | 0.126 (3.2)                                                                              | 0.063 (1.6)                         | 0.043 (1.1)                         |
| 0.0022                                           | FCN1206A222J-H2 | 0.126 (3.2)                                                                              | 0.063 (1.6)                         | 0.043 (1.1)                         |
| 0.0027                                           | FCN1206A272J-H2 | 0.126 (3.2)                                                                              | 0.063 (1.6)                         | 0.043 (1.1)                         |
| 0.0033                                           | FCN1206A332J-H3 | 0.126 (3.2)                                                                              | 0.063 (1.6)                         | 0.059 (1.5)                         |
| 0.0039                                           | FCN1206A392J-H3 | 0.126 (3.2)                                                                              | 0.063 (1.6)                         | 0.059 (1.5)                         |
| 0.0047                                           | FCN1206A472J-H3 | 0.126 (3.2)                                                                              | 0.063 (1.6)                         | 0.059 (1.5)                         |
| 0.0056                                           | FCN1210A562J-G2 | 0.126 (3.2)                                                                              | 0.098 (2.5)                         | 0.059 (1.5)                         |
| 0.0068                                           | FCN1210A682J-G2 | 0.126 (3.2)                                                                              | 0.098 (2.5)                         | 0.059 (1.5)                         |
| 0.0082                                           | FCN1210A822J-G3 | 0.126 (3.2)                                                                              | 0.098 (2.5)                         | 0.083 (2.1)                         |
| 0.01                                             | FCN1210A103J-G3 | 0.126 (3.2)                                                                              | 0.098 (2.5)                         | 0.083 (2.1)                         |

# Type FCN Surface Mount Film Capacitors

|                                                  |                 |                                                                                                                                                                    |                                     |                                     |
|--------------------------------------------------|-----------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------|-------------------------------------|
| <b>Rated Voltage:</b> 100 Vdc (63 Vac)           |                 | <b>Operating Temperature Range:</b> -40 to +85°C                                                                                                                   |                                     |                                     |
| <b>Capacitance Range:</b> 0.012 to 1.0 µF        |                 | <b>Dielectric Withstand Voltage:</b> 150 Vdc for 60 seconds                                                                                                        |                                     |                                     |
| <b>Capacitance Tolerance:</b> ± 10% (K)          |                 | <b>Insulation Resistance (20°C, 100 Vdc, 60 Seconds);</b><br><br><b>For C ≤ 0.33 µF:I.R. ≥ 3000 MegΩ</b><br><br><b>For C &gt; 0.33 µF:I.R. = 1000 MegW•µF Min.</b> |                                     |                                     |
| <b>D.F. (20°C, 1 kHz):</b> ≤ 1%                  |                 |                                                                                                                                                                    |                                     |                                     |
| <b>Max. capacitor surface temperature: 230°C</b> |                 |                                                                                                                                                                    |                                     |                                     |
| <b>Capacitance (µF)</b>                          | <b>CDE P.N.</b> | <b>L ±.008 (±0.2)<br/>[in.(mm)]</b>                                                                                                                                | <b>W ±.012 (±0.3)<br/>[in.(mm)]</b> | <b>T ±.008 (±0.2)<br/>[in.(mm)]</b> |
| 0.012                                            | FCN1913A123K-E1 | 0.189 (4.8)                                                                                                                                                        | 0.130 (3.3)                         | 0.055 (1.4)                         |
| 0.015                                            | FCN1913A153K-E1 | 0.189 (4.8)                                                                                                                                                        | 0.130 (3.3)                         | 0.055 (1.4)                         |
| 0.018                                            | FCN1913A183K-E1 | 0.189 (4.8)                                                                                                                                                        | 0.130 (3.3)                         | 0.055 (1.4)                         |
| 0.022                                            | FCN1913A223K-E1 | 0.189 (4.8)                                                                                                                                                        | 0.130 (3.3)                         | 0.055 (1.4)                         |
| 0.027                                            | FCN1913A273K-E1 | 0.189 (4.8)                                                                                                                                                        | 0.130 (3.3)                         | 0.055 (1.4)                         |
| 0.033                                            | FCN1913A333K-E1 | 0.189 (4.8)                                                                                                                                                        | 0.130 (3.3)                         | 0.055 (1.4)                         |
| 0.039                                            | FCN1913A393K-E1 | 0.189 (4.8)                                                                                                                                                        | 0.130 (3.3)                         | 0.055 (1.4)                         |
| 0.047                                            | FCN1913A473K-E2 | 0.189 (4.8)                                                                                                                                                        | 0.130 (3.3)                         | 0.079 (2.0)                         |
| 0.056                                            | FCN1913A563K-E2 | 0.189 (4.8)                                                                                                                                                        | 0.130 (3.3)                         | 0.079 (2.0)                         |
| 0.068                                            | FCN1913A683K-E4 | 0.189 (4.8)                                                                                                                                                        | 0.130 (3.3)                         | 0.094 (2.4)                         |
| 0.082                                            | FCN1913A823K-E3 | 0.189 (4.8)                                                                                                                                                        | 0.130 (3.3)                         | 0.110 (2.8)                         |
| 0.10                                             | FCN2416A104K-D1 | 0.236 (6.0)                                                                                                                                                        | 0.161 (4.1)                         | 0.071 (1.8)                         |
| 0.12                                             | FCN2416A124K-D3 | 0.236 (6.0)                                                                                                                                                        | 0.161 (4.1)                         | 0.094 (2.4)                         |
| 0.15                                             | FCN2416A154K-D4 | 0.236 (6.0)                                                                                                                                                        | 0.161 (4.1)                         | 0.110 (2.8)                         |

| Capacitance (µF) | CDE P.N.       | L ±.016 (±0.4) <sup>2</sup><br>[in.(mm)] | W ±.016 (±0.4)<br>[in.(mm)] | T ±.012 (±0.3)<br>[in.(mm)] |
|------------------|----------------|------------------------------------------|-----------------------------|-----------------------------|
| 0.18             | FCN2820A184K-Z | 0.280 (7.1)                              | 0.197 (5.0)                 | 0.079 (2.0)                 |
| 0.22             | FCN2820A224K-Z | 0.280 (7.1)                              | 0.197 (5.0)                 | 0.094 (2.4)                 |
| 0.27             | FCN2820A274K-Z | 0.280 (7.1)                              | 0.197 (5.0)                 | 0.114 (2.9)                 |
| 0.33             | FCN2820A334K-Z | 0.280 (7.1)                              | 0.197 (5.0)                 | 0.138 (3.5)                 |
| 0.39             | FCN3022A394K-X | 0.303 (7.7)                              | 0.217 (5.5)                 | 0.134 (3.4)                 |
| 0.47             | FCN3022A474K-X | 0.303 (7.7)                              | 0.217 (5.5)                 | 0.157 (4.0)                 |
| 0.56             | FCN3925A564K-V | 0.386 (9.8)                              | 0.248 (6.3)                 | 0.118 (3.0)                 |
| 0.68             | FCN3925A684K-V | 0.386 (9.8)                              | 0.248 (6.3)                 | 0.142 (3.6)                 |
| 0.82             | FCN3925A824K-V | 0.386 (9.8)                              | 0.248 (6.3)                 | 0.169 (4.3)                 |
| 1.0              | FCN3925A105K-V | 0.386 (9.8)                              | 0.248 (6.3)                 | 0.201 (5.1)                 |




# Type FCN Surface Mount Film Capacitors

| Cap<br>( $\mu$ F) | Catalog<br>Part Number | L<br>in (mm)     |                  | W<br>in (mm)     |                 | T<br>in (mm)     |                 |
|-------------------|------------------------|------------------|------------------|------------------|-----------------|------------------|-----------------|
| 250 Vdc           |                        |                  |                  |                  |                 |                  |                 |
| 0.12              | FCN2420E124K-B *       | 0.236 $\pm$ .008 | (6.0 $\pm$ 0.2)  | 0.197            | (5.0)           | 0.177            | (4.5)           |
| 0.15              | FCN2825E154K-Y         | 0.280 $\pm$ .016 | (7.1 $\pm$ 0.4)  | 0.248            | (6.3)           | 0.138            | (3.5)           |
| 0.18              | FCN2825E184K-Y         | 0.280 $\pm$ .016 | (7.1 $\pm$ 0.4)  | 0.248            | (6.3)           | 0.161            | (4.1)           |
| 0.22              | FCN2825E224K-Y         | 0.280 $\pm$ .016 | (7.1 $\pm$ 0.4)  | 0.248            | (6.3)           | 0.201            | (5.1)           |
| 0.27              | FCN3925E274K-V         | 0.386 $\pm$ .020 | (9.8 $\pm$ 0.5)  | 0.248            | (6.3)           | 0.154            | (3.9)           |
| 0.33              | FCN3925E334K-V         | 0.386 $\pm$ .020 | (9.8 $\pm$ 0.5)  | 0.248            | (6.3)           | 0.189            | (4.8)           |
| 0.39              | FCN3931E394K-U         | 0.386 $\pm$ .020 | (9.8 $\pm$ 0.5)  | 0.315            | (8.0)           | 0.173            | (4.4)           |
| 0.47              | FCN3931E474K-U         | 0.386 $\pm$ .020 | (9.8 $\pm$ 0.5)  | 0.315            | (8.0)           | 0.209            | (5.3)           |
| 0.56              | FCN6031E564K-T         | 0.598 $\pm$ .020 | (15.2 $\pm$ 0.5) | 0.315            | (8.0)           | 0.146            | (3.7)           |
| 0.68              | FCN6031E684K-T         | 0.598 $\pm$ .020 | (15.2 $\pm$ 0.5) | 0.315            | (8.0)           | 0.173            | (4.4)           |
| 0.82              | FCN6040E824K-S         | 0.598 $\pm$ .020 | (15.2 $\pm$ 0.5) | 0.394            | (10.0)          | 0.165            | (4.2)           |
| 1.0               | FCN6040E105K-S         | 0.598 $\pm$ .020 | (15.2 $\pm$ 0.5) | 0.394            | (10.0)          | 0.201            | (5.1)           |
| 400 Vdc           |                        |                  |                  |                  |                 |                  |                 |
| 0.001             | FCN1913G102J-E1        | 0.189 $\pm$ .008 | (4.8 $\pm$ 0.2)  | 0.130 $\pm$ .012 | (3.3 $\pm$ 0.3) | 0.055 $\pm$ .008 | (1.4 $\pm$ 0.2) |
| 0.0012            | FCN1913G122J-E1        | 0.189 $\pm$ .008 | (4.8 $\pm$ 0.2)  | 0.130 $\pm$ .012 | (3.3 $\pm$ 0.3) | 0.055 $\pm$ .008 | (1.4 $\pm$ 0.2) |
| 0.0015            | FCN1913G152J-E1        | 0.189 $\pm$ .008 | (4.8 $\pm$ 0.2)  | 0.130 $\pm$ .012 | (3.3 $\pm$ 0.3) | 0.055 $\pm$ .008 | (1.4 $\pm$ 0.2) |
| 0.0018            | FCN1913G182J-E1        | 0.189 $\pm$ .008 | (4.8 $\pm$ 0.2)  | 0.130 $\pm$ .012 | (3.3 $\pm$ 0.3) | 0.055 $\pm$ .008 | (1.4 $\pm$ 0.2) |
| 0.0022            | FCN1913G222J-E1        | 0.189 $\pm$ .008 | (4.8 $\pm$ 0.2)  | 0.130 $\pm$ .012 | (3.3 $\pm$ 0.3) | 0.055 $\pm$ .008 | (1.4 $\pm$ 0.2) |
| 0.0027            | FCN1913G272J-E1        | 0.189 $\pm$ .008 | (4.8 $\pm$ 0.2)  | 0.130 $\pm$ .012 | (3.3 $\pm$ 0.3) | 0.055 $\pm$ .008 | (1.4 $\pm$ 0.2) |
| 0.0033            | FCN1913G332J-E1        | 0.189 $\pm$ .008 | (4.8 $\pm$ 0.2)  | 0.130 $\pm$ .012 | (3.3 $\pm$ 0.3) | 0.055 $\pm$ .008 | (1.4 $\pm$ 0.2) |
| 0.0039            | FCN1913G392J-E1        | 0.189 $\pm$ .008 | (4.8 $\pm$ 0.2)  | 0.130 $\pm$ .012 | (3.3 $\pm$ 0.3) | 0.055 $\pm$ .008 | (1.4 $\pm$ 0.2) |
| 0.0047            | FCN1913G472J-E1        | 0.189 $\pm$ .008 | (4.8 $\pm$ 0.2)  | 0.130 $\pm$ .012 | (3.3 $\pm$ 0.3) | 0.055 $\pm$ .008 | (1.4 $\pm$ 0.2) |
| 0.0056            | FCN1913G562J-E2        | 0.189 $\pm$ .008 | (4.8 $\pm$ 0.2)  | 0.130 $\pm$ .012 | (3.3 $\pm$ 0.3) | 0.079 $\pm$ .008 | (2.0 $\pm$ 0.2) |
| 0.0068            | FCN1913G682J-E2        | 0.189 $\pm$ .008 | (4.8 $\pm$ 0.2)  | 0.130 $\pm$ .012 | (3.3 $\pm$ 0.3) | 0.079 $\pm$ .008 | (2.0 $\pm$ 0.2) |
| 0.0082            | FCN1913G822J-E4        | 0.189 $\pm$ .008 | (4.8 $\pm$ 0.2)  | 0.130 $\pm$ .012 | (3.3 $\pm$ 0.3) | 0.094 $\pm$ .008 | (2.4 $\pm$ 0.2) |
| 0.01              | FCN1913G103J-E3        | 0.189 $\pm$ .008 | (4.8 $\pm$ 0.2)  | 0.130 $\pm$ .012 | (3.3 $\pm$ 0.3) | 0.110 $\pm$ .008 | (2.8 $\pm$ 0.2) |
| 0.012             | FCN2416G123J-D2        | 0.236 $\pm$ .008 | (6.0 $\pm$ 0.2)  | 0.161 $\pm$ .012 | (4.1 $\pm$ 0.3) | 0.079 $\pm$ .008 | (2.0 $\pm$ 0.2) |
| 0.015             | FCN2416G153J-D3        | 0.236 $\pm$ .008 | (6.0 $\pm$ 0.2)  | 0.161 $\pm$ .012 | (4.1 $\pm$ 0.3) | 0.094 $\pm$ .008 | (2.4 $\pm$ 0.2) |
| 0.018             | FCN2416G183J-D4        | 0.236 $\pm$ .008 | (6.0 $\pm$ 0.2)  | 0.161 $\pm$ .012 | (4.1 $\pm$ 0.3) | 0.110 $\pm$ .008 | (2.8 $\pm$ 0.2) |
| 0.022             | FCN2416G223J-D5        | 0.236 $\pm$ .008 | (6.0 $\pm$ 0.2)  | 0.161 $\pm$ .012 | (4.1 $\pm$ 0.3) | 0.126 $\pm$ .012 | (3.2 $\pm$ 0.3) |
| 0.027             | FCN2420G273J-B         | 0.236 $\pm$ .008 | (6.0 $\pm$ 0.2)  | 0.197 $\pm$ .016 | (5.0 $\pm$ 0.4) | 0.118 $\pm$ .012 | (3.0 $\pm$ 0.3) |
| 0.033             | FCN2420G333J-B         | 0.236 $\pm$ .008 | (6.0 $\pm$ 0.2)  | 0.197 $\pm$ .016 | (5.0 $\pm$ 0.4) | 0.142 $\pm$ .012 | (3.6 $\pm$ 0.3) |
| 0.039             | FCN2820G393J-Z         | 0.280 $\pm$ .016 | (7.1 $\pm$ 0.4)  | 0.197 $\pm$ .016 | (5.0 $\pm$ 0.4) | 0.126 $\pm$ .012 | (3.2 $\pm$ 0.3) |
| 0.047             | FCN2820G473J-Z         | 0.280 $\pm$ .016 | (7.1 $\pm$ 0.4)  | 0.197 $\pm$ .016 | (5.0 $\pm$ 0.4) | 0.150 $\pm$ .012 | (3.8 $\pm$ 0.3) |
| 0.056             | FCN2825G563J-Y         | 0.280 $\pm$ .016 | (7.1 $\pm$ 0.4)  | 0.248 $\pm$ .016 | (6.3 $\pm$ 0.4) | 0.142 $\pm$ .012 | (3.6 $\pm$ 0.3) |
| 0.068             | FCN2825G683J-Y         | 0.280 $\pm$ .016 | (7.1 $\pm$ 0.4)  | 0.248 $\pm$ .016 | (6.3 $\pm$ 0.4) | 0.173 $\pm$ .012 | (4.4 $\pm$ 0.3) |
| 0.082             | FCN3925G823J-V         | 0.386 $\pm$ .016 | (9.8 $\pm$ 0.4)  | 0.248 $\pm$ .016 | (6.3 $\pm$ 0.4) | 0.134 $\pm$ .012 | (3.4 $\pm$ 0.3) |
| 0.1               | FCN3925G104J-V         | 0.386 $\pm$ .016 | (9.8 $\pm$ 0.4)  | 0.248 $\pm$ .016 | (6.3 $\pm$ 0.4) | 0.157 $\pm$ .012 | (4.0 $\pm$ 0.3) |
| 0.12              | FCN3931G124J-U         | 0.386 $\pm$ .016 | (9.8 $\pm$ 0.4)  | 0.315 $\pm$ .016 | (8.0 $\pm$ 0.4) | 0.150 $\pm$ .012 | (3.8 $\pm$ 0.3) |
| 0.15              | FCN3931G154J-U         | 0.386 $\pm$ .016 | (9.8 $\pm$ 0.4)  | 0.315 $\pm$ .016 | (8.0 $\pm$ 0.4) | 0.181 $\pm$ .012 | (4.6 $\pm$ 0.3) |




\* also available in 5% (J) tolerance

# Type FCN Surface Mount Film Capacitors

## Typical Temperature Characteristics









## Typical Frequency Characteristics



# Type FCN Surface Mount Film Capacitors

## Vrms vs. Frequency Characteristics




# Type FCN Surface Mount Film Capacitors

## Pulse Handling Capability


| Capacitance<br>( $\mu\text{F}$ ) | Voltage<br>(Vdc) | dV/dt<br>(volts/ $\mu\text{sec}$ ) | Capacitance<br>( $\mu\text{F}$ ) | Voltage<br>(Vdc) | dV/dt<br>(volts/ $\mu\text{sec}$ ) | Capacitance<br>( $\mu\text{F}$ ) | Voltage<br>(Vdc) | dV/dt<br>(volts/ $\mu\text{sec}$ ) |
|----------------------------------|------------------|------------------------------------|----------------------------------|------------------|------------------------------------|----------------------------------|------------------|------------------------------------|
| .12 - .22                        | 16               | 60                                 | .0039                            | 100              | 530                                | .001 - .0039                     | 250              | 615                                |
| .27 - .47                        | 16               | 40                                 | .0047                            | 100              | 480                                | .0047 - .033                     | 250              | 360                                |
| .056 - .10                       | 50               | 190                                | .0056                            | 100              | 450                                | .039 - .12                       | 250              | 240                                |
| .12 - .22                        | 50               | 130                                | .0068                            | 100              | 410                                | .15 - .22                        | 250              | 190                                |
| .001                             | 100              | 1000                               | .0082                            | 100              | 370                                | .27 - .47                        | 250              | 115                                |
| .0012                            | 100              | 920                                | .01                              | 100              | 340                                | .56 - 1.0                        | 250              | 65                                 |
| .0015                            | 100              | 830                                | .012 - .082                      | 100              | 320                                | .001 - .0039                     | 400              | 615                                |
| .0018                            | 100              | 760                                | .10 - .15                        | 100              | 210                                | .0047 - .01                      | 400              | 360                                |
| .0022                            | 100              | 690                                | .18 - .33                        | 100              | 120                                | .012 - .033                      | 400              | 240                                |
| .0027                            | 100              | 630                                | .39 - .47                        | 100              | 100                                | .039 - .068                      | 400              | 190                                |
| .0033                            | 100              | 570                                | .056 - 1.0                       | 100              | 70                                 | .082 - .15                       | 400              | 115                                |

## Typical Applications

DC Blocking for xDSL



Integration for Electroluminescent (EL) Driver



With no piezoelectric effects to deal with, the SMT film capacitor will not create electrical noise in signal circuits or buzzing in power circuits.

## Type FCN Surface Mount Film Capacitors

---

**Notice and Disclaimer:** All product drawings, descriptions, specifications, statements, information and data (collectively, the "Information") in this datasheet or other publication are subject to change. The customer is responsible for checking, confirming and verifying the extent to which the Information contained in this datasheet or other publication is applicable to an order at the time the order is placed. All Information given herein is believed to be accurate and reliable, but it is presented without any guarantee, warranty, representation or responsibility of any kind, expressed or implied. Statements of suitability for certain applications are based on the knowledge that the Cornell Dubilier company providing such statements ("Cornell Dubilier") has of operating conditions that such Cornell Dubilier company regards as typical for such applications, but are not intended to constitute any guarantee, warranty or representation regarding any such matter – and Cornell Dubilier specifically and expressly disclaims any guarantee, warranty or representation concerning the suitability for a specific customer application, use, storage, transportation, or operating environment. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by Cornell Dubilier with reference to the use of any Cornell Dubilier products is given gratis (unless otherwise specified by Cornell Dubilier), and Cornell Dubilier assumes no obligation or liability for the advice given or results obtained. Although Cornell Dubilier strives to apply the most stringent quality and safety standards regarding the design and manufacturing of its products, in light of the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies or other appropriate protective measures) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage. Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicated in such warnings, cautions and notes, or that other safety measures may not be required.