








2 POS



3 POS



NOTES:

1. SPECIFICATIONS

Current Rating: 1A AC,DC

Voltage Rating: 125V AC,DC

Temperature Range: -40°C ~ +105°C

Contact Resistance: 20mΩ Max.

Insulation Resistance: 100MΩ Min.

Withstanding Voltage: 500V AC/minute

2. Material & finish:

Housing: Natural Thermoplastic, UL94V-0

Contact and metal hold-down: Phosphor Bronze

Plating of contact: Matte Tin or gold plating over Nickel

3. Crimping application hand tool P/N: 10118656-1000

4. Ordering Information & Dimensions:

10114831- X X X XX LF

Material

1: LCP

LF: See note A

pin counts from 02~15

Plating

0: Matte Tin

1: Gold Flash

Packaging

1: Tape & Reel

Part No.	Dimensions			
	POS	A	B	C
10114831-xxx02LF	2	1.25±0.10	4.25	3.05
10114831-xxx03LF	3	2.50±0.10	5.50	4.30
10114831-xxx04LF	4	3.75±0.10	6.75	5.55
10114831-xxx05LF	5	5.00±0.10	8.00	6.80
10114831-xxx06LF	6	6.25±0.15	9.25	8.05
10114831-xxx07LF	7	7.50±0.15	10.50	9.30
10114831-xxx08LF	8	8.75±0.15	11.75	10.55
10114831-xxx09LF	9	10.00±0.15	13.00	11.80
10114831-xxx10LF	10	11.25±0.20	14.25	13.05
10114831-xxx11LF	11	12.50±0.20	15.50	14.30
10114831-xxx12LF	12	13.75±0.20	16.75	15.55
10114831-xxx13LF	13	15.00±0.20	18.00	16.80
10114831-xxx14LF	14	16.25±0.20	19.25	18.05
10114831-xxx15LF	15	17.50±0.20	20.50	19.30

Note A: The LF means RoHS compliance, the housing will withstand exposure to peak temperature 260 degree C for 5 sec in the IR re-flow process.

www.fciconnect.com

surface 6.4
ISO 1302tolerance std
ISO 406 ISO 1101projection
MM

MM

TOLERANCES UNLESS OTHERWISE SPECIFIED

ANGULAR LINEAR

0.X ±0.25

0.XX ±0.15

0.XXX -

Product family WTB

Spec ref

title WT 1.25MM WAFER 90° DIP

catalog no

CUSTOMER

sheet 1 of 1

rev	ecn no	dr	date
A	T10-0145	J H	12/1/10
B	ELX-N-011323	J.Z	2012-04-17



title

WT 1.25MM WAFER 90° DIP

catalog no

dwg no

10114831

Rev.
B