




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		J1	REVISED PER ECO-11-005033	23MAR11	RK	HMR



- 1 SHELL DIAMETER IN THIS AREA TO BE .529±.005 MEASURED ANYWHERE EXCEPT OVER KEY.
- 2 SHELL DIAMETER IN THIS AREA TO BE .531±.003.
- 3 SHELL DIAMETER IN KEY TRANSITION AREA MAY NOT EXCEED .535 AT ANY MEASUREMENT POINT.
- 4 TIN-LEAD.
- 5 TIN.

	5	CIRCULAR DIN SUB-ASSEMBLY, 8 POSITION	9-212437-2
	5	CIRCULAR DIN SUB-ASSEMBLY, 6 POSITION	9-212437-1
	5	CIRCULAR DIN SUB-ASSEMBLY, 5 POSITION	9-212437-0
	5	CIRCULAR DIN SUB-ASSEMBLY, 4 POSITION	212437-7
OBSOLETE	4	CIRCULAR DIN SUB-ASSEMBLY, 8 POSITION	212437-6
OBSOLETE	4	CIRCULAR DIN SUB-ASSEMBLY, 7 POSITION	212437-5
OBSOLETE	4	CIRCULAR DIN SUB-ASSEMBLY, 6 POSITION	212437-4
OBSOLETE	4	CIRCULAR DIN SUB-ASSEMBLY, 5 POSITION	212437-3
OBSOLETE	4	CIRCULAR DIN SUB-ASSEMBLY, 4 POSITION	212437-2
OBSOLETE	4	CIRCULAR DIN SUB-ASSEMBLY, 3 POSITION	212437-1

SHIELD FINISH		DESCRIPTION			PART NUMBER				
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 11-10-05 L. Varela - Dock5	 TE Connectivity						
		CHK 11-10-05 C. ROHDE							
DIMENSIONS: INCHES		APVD 11-10-05 M. WALMSLEY	NAME	CIRCULAR DIN PLUG, SUB-ASSEMBLY					
		TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC	—					
		0 PLC ± —	APPLICATION SPEC	—					
		1 PLC ± —	—	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
MATERIAL		FINISH	WEIGHT	A2	00779	C-212437	—		
SEE TABLE		SEE TABLE	CUSTOMER DRAWING	SCALE	1:1	SHEET	1 of 1	REV	J1