

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART #	STUD SIZE		DIMENSIONS in. [mm]					CA9 SERIES CRIMP DIE	CA-800(EZ) SERIES CRIMP DIE
	ENGLISH	METRIC	L ± [0,8]	W ± [0,3]	C ± [0,5]	M ± [0,8]	H ± [0,3]		
PMV1-3FB-3K	--	M3	.78 [19,8]	.23 [5,8]	.20 [5,1]	.64 [16,3]	.13 [3,3]	CD9-1A	CD-800-1
PV18-6FB-3K	#6	M3,5	.78 [19,8]	.30 [7,6]	.20 [5,1]	.64 [16,3]	.15 [3,8]		
PV18-6FNB-3K	#6	M3,5	.78 [19,8]	.25 [6,4]	.20 [5,1]	.64 [16,3]	.15 [3,8]		
PV18-8FB-3K	#8	M4	.84 [21,3]	.32 [8,1]	.23 [5,8]	.68 [17,2]	.17 [4,3]		
PV18-10FB-3K	#10	--	.86 [21,8]	.35 [8,9]	.25 [6,4]	.70 [17,8]	.20 [5,1]		
PV18-10FNB-3K	#10	--	.86 [21,8]	.31 [7,9]	.25 [6,4]	.70 [17,8]	.20 [5,1]		
PMV1-5FB-3K	--	M5	.86 [21,8]	.35 [8,9]	.25 [6,4]	.70 [17,8]	.20 [5,1]		
PV18-14FB-3K	1/4"	M6	1.03 [26,2]	.44 [11,2]	.33 [8,4]	.78 [19,9]	.27 [6,9]		

PRESS/APPLICATOR COMPATIBILITY CHART

PRESS	CP-871	CP-861
APPLICATOR	CA9 CA-800EZ	CA-800

NOTES:

- UL LISTED AND CSA CERTIFIED FOR:
A. #22-18 AWG [0,5-1,0 mm²] SOLID OR STRANDED COPPER WIRE
B. 221°F [105°C] MAX. OPERATING TEMPERATURE
C. 600 V. MAX. VOLTAGE RATING

- SEE www.panduit.com FOR PACKAGE QUANTITIES



- MATERIAL:
A. STAMPING: .03" [0,8] THK COPPER, TIN PLATED
B. HOUSING: VINYL, RED

- DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT

- WIRE STRIP LENGTH: 1/4" ^{+1/32}₋₀ [6,4mm ^{+0,8}₋₀]

CARRIER STRIP
(CONFIGURATION
MAY VARY)

.15 [3,8]
MAX. WIRE
INSUL. DIA.



TITLE		FORK TERMINALS, 2 PC. VINYL INSULATED, #22-18, CONTINUOUS REEL	
ITEM REVISION NAME		CUSTOMER DRAWING	
N41081BA/08		PANDUIT	
DATASET FILE NAME		N41081BA-DC/08A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL: SEE NOTES	
.X ± .XX ±		.XXX ± ANGLES ±	
THIRD ANGLE PROJECTION		DRAWING NUMBER: A41081	
DRAWN BY DSM	DATE -	CHK FS	SCALE N.T.S.
SHT 1 OF 1		SIZE A	