








FCIconnect.com

Copyright FCI



PC card drilling dimensions(after plating)
(thickness 1.60 $\pm$ 0.20mm)



PART NUMBER

SHELL	A ± 0.38	B ± 0.12	C ± 0.10	D $\begin{smallmatrix} +0.25 \\ 0 \end{smallmatrix}$	E ± 0.07	200 Mating cycles	500 Mating cycles
09	30.81	24.99	16.96	16.21	10.96	D09S33E4GX00**	D09S33E6GX00**
15	39.14	33.32	25.18	24.54	19.18	D15S33E4GX00**	D15S33E6GX00**
25	53.03	47.04	39.12	38.25	33.12	D25S33E4GX00**	D25S33E6GX00**
37	69.32	63.50	55.68	54.71	49.68	D37S33E4GX00**	D37S33E6GX00**

LF FOR LEAD FREE

GENERAL CHARACTERISTICS : SEE DRAWING C01-8646-0000

mat'l. code				surface	tolerance	projection	product family			
-				ISO 1302	ISO 406 ISO 1101		D-SUB			
ltr	ecn no	dr	date	tolerances unless otherwise specified			title			
D	ELX-I-19243	AB	2014-10-29	angles	linear					
				0 $\pm$ 2'						
				dr	JOHN SLEEBA	1994-10-14	dwg no		sheet 1 of 1	
				enr	ALIAS BABU	2014-10-29				
				chr	MITHUN PAUL	2014-10-29				
				app	BIJU K PAUL	2014-10-29				
sheet index		revision	D				C01-8646-0823		A3	
index		sheet	1							
							type		Product Customer Drawing	