





REVISION					
ZONE	LTR	ECN	DESCRIPTION	DATE	APPROVED
	C	39399	GENERAL DWG UPDATE	8/22/99	REL



NOTES: UNLESS OTHERWISE SPECIFIED

1. MARK PER TIS.
2. POTTING COMPOUND USED IS 194-8102-6215/6225.
3. CRIMP LEADS INTO CONTACTS PER MEP 302-05.
4. EPOXY WICKING FROM THE REAR OF INSULATOR ON INSULATED LEADS MUST NOT EXCEED .125 MAX ON #25 AWG AND SMALLER LEADS AND .200 MAX ON #24 AWG AND LARGER LEADS.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCE ARE:

FRACTIONS	DECIMALS	ANGLES
$\pm 1/8$	.XX $\pm .01$.XXX $\pm .005$	$\pm 2^\circ$

MATERIALS:

FINISH:

APPROVALS

SIGNATURE	DATE
DRAWN BY MEL F. CAMPOS	09/16/99
P.E. <i>[Signature]</i>	9/16/99
M.E.	
D.A.	

THIS DOCUMENT IS THE PROPERTY OF MICRODOT CONNECTORS, A DIVISION OF UNI-STAR INDUSTRIES INC. USE OF THIS DOCUMENT OR ANY PART THEREOF IS STRICTLY FORBIDDEN WITHOUT THE EXPRESS WRITTEN PERMISSION OF MICRODOT CONNECTORS, A DIVISION OF UNI-STAR INDUSTRIES INC.



MICRODOT CONNECTORS
A DIVISION OF UNI-STAR INDUSTRIES INC.
386 PASADENA AVE., SO. PASADENA, CA 91030

METAL SHELL 'D' CONNECTOR
MCDMI-B-15P

PROD
CODE
842

CODE
M

SIZE	CODE IDENT NO.	DRAWING NO.
A	98278	095-0000-0075
SCALE: NONE		SHEET 1 OF 1