

MICRO SWITCHFREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929**SWITCH - BASIC**

CATALOG LISTING

V3L-607**CQ-H0480****V3L-607**

PAGE 1 OF 1

MDRAWING
NUMBERISSUE
10

REPLACES

RELEASE NO. PR-6350

CHECK

04 JUN 04

AK

CHECK

23 FEB 77

CEB

04 JUN 04

REVISIONS

A NEW DWG
PR-6350K P
22 FEB 77


B CO-38993

T M M
5 AUG 77C CO
59921SMA
29 SEPT 86D CO-
69205BAB
3 JAN 91E CO
76444DCS
8 FEB 94F CO
77116DCS
22 APR 94

G CO-93311

TSM
16 OCT 98


H 0005782

RJ
04 JUN 04**NOTES**

- 1 - TERMINALS ARE PLATED FOR SOLDERING
- 2 - IN INSPECTION, DO NOT BURN OUT - GOLD CONTACTS
- 3 - IN INSPECTION, DO NOT EXCEED 10 VDC, .1A RESISTIVE LOAD
- 4 - INSPECT SWITCH RESISTANCE PER CONTROL PLAN

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION

**CHARACTERISTICS**

OPERATING FORCE ----- 4 OZ MAX

RELEASE FORCE ----- 1/2 OZ MIN

RELEASE TRAVEL ----- .010 MIN

DIFFERENTIAL TRAVEL ----- .032 MAX

OVERTRAVEL ----- .080 MIN

ELECTRICAL DATACONTACT ARRANGEMENT
S P D T

L22 1A-125 VAC



SCALE FULL

DO NOT SCALE PRINT

TOLERANCES
APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR
REFERENCE. UNLESS NOTED, TOLERANCES ARE ±

DIM.	TOL.	DIM.	TOL.
mm	mm/in	in	mm/in
NO PLACES	X	1/04	
ONE PLACE	X,X	0.4/016	X X 0.8/03
TWO PLACES	X,X,X	0.15/006	X X X 0.38/015
THREE PLACES	X,X,X,X		X X X X 0.13/005

DESIGN UNITS ☐ SI METRICUS CUSTOMARY ☒

WEIGHT

FORMTEK

DRAWN

K P K22 FEB 77 CHECK CEB