



DESCRIPTION: **HIGH DENSITY MALE RIGHT ANGLE**



POS.	A	B	C	D	E	F
15	1.213	0.984	0.666	0.090	0.329	0.496
	30.80	24.99	16.92	2.29	8.36	12.60
26	1.543	1.312	0.994	0.090	0.329	0.496
	39.19	33.32	25.25	2.29	8.36	12.60
44	2.087	1.852	1.534	0.090	0.329	0.496
	53.00	47.04	38.96	2.29	8.36	12.60
62	2.740	2.500	2.181	0.095	0.329	0.496
	69.60	63.50	55.42	2.41	8.36	12.60

181-XXX-112-XX1

SERIES _____
POSITIONS _____
015
026
044
062
GENDER _____
1 = MALE
TERMINATION _____
1 = DIP SOLDER
SHELL PLATING _____
2 = TIN
HARDWARE OPTIONS _____
00 = NO HARDWARE
16 = .120"Ø/INSIDE GRND STRAPS
17 = 4-40 INSERTS/INSIDE GRND STRAPS
18 = 4-40 SCREWLOCKS/INSIDE GRND STRAPS
43 = .120"Ø/METAL SHELL
45 = 4-40 INSERTS/METAL SHELL
48 = 4-40 SCREWLOCKS/METAL SHELL
53 = 4-40 INSERT/BOARD LOCKS
56 = 4-40 SCREWLOCKS/BOARDLOCKS
PLATING OPTIONS _____
1 = GOLD FLASH ENTIRE CONTACT


ELECTRICALS:
CURRENT RATING: 2 AMPS
CONTACT RESISTANCE: 15 mOHMS MAX.
INSULATOR RESISTANCE: 1000MOHMS MIN.
VOLTAGE: 500V FOR 1 MINUTE
TEMPERATURE: -50° TO +100°

MATERIALS:
SHELL: STEEL, TIN PLATED
INSULATOR: PBT - BLACK (UL-94-VO)
CONTACTS:BRASS - GOLD FLASH ENTIRE CONTACT


	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.		DRAWN: PAM JENKINS		DATE: 8-19-99	
			CHECKED:		DATE:	
		SCALE:		SHEET OF		REV 6
		DWG NO. 181-XXX-112-XX1				

DESCRIPTION: HIGH DENSITY RIGHT ANGLE MALE FOOTPRINT


78 POSITION MALE




26 POSITION MALE




62 POSITION MALE



15 POSITION MALE



44 POSITION MALE



THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF NorComp AND
SHALL NOT BE REPRODUCED, COPIED
OR USED AS THE BASIS FOR THE
MANUFACTURE OF SALE OF APPARATUS
WITHOUT WRITTEN PERMISSION.

DRAWN:
PAM JENKINS

DATE:	10-29-01
-------	----------

CHECKED:

DATE:

SHEET	OF
1	1

REV
3

DWG NO.

HIGH DENSITY RIGHT ANGLE MALE FOOTPRINT

NorComp