


37 4101, 37 4102,  
37 4103  
and 37 4104



37 5101



37 5102



37 5104



37 6101, 37 6102,  
37 6103  
and 37 6104



37 8101, 37 8102  
and 37 8103



37 9101, 37 9102, 37 9103 and 37 9104



## Features:

- Offers a grey 'non-marking' rubber tyre on a black nylon centre including thread guards which is available with plain bore.

## The wheels can be fitted in the following castor housings:

- Top plate swivel, fixed and swivel with foot brake.
- Threaded stem swivel and threaded stem with foot brake.

## Recommended Uses:


This wheel type is recommended for light duty applications.

## Specifications:


In accordance with ISO 2175. Defines castor and/or wheel application appropriate with environmental conditions-load, speed of use, temperature, floor condition and cycle time.

Type : Plain bearing bore.


37 4101, 37 4102, 37 4103  
and 37 4104



37 5101, 37 5102  
and 37 5104




37 6101, 37 6102, 37 6103  
and 37 6104




Dimensions : Millimetres

37 8101, 37 81032  
and 37 8103



37 9101, 37 9102, 37 9103  
and 37 9104



Dimensions : Millimetres

## Specification Table

| Description                   | Wheel Diameter (D) | Thread Width (b) | Overall Height (H) | Plate Dimensions (A x B) | Hole Spacing (a x b) | Hole Width (e) | Offset (E) | Carrying Capacity (kg) | Part Number |
|-------------------------------|--------------------|------------------|--------------------|--------------------------|----------------------|----------------|------------|------------------------|-------------|
| Castor, Apparatus, Swivel Top | 50                 | 20               | 68                 | 55 x 55                  | 40 x 40              | 6              | 25         | 35                     | 37 4101     |
| Castor, Apparatus, Swivel Top | 60                 | 24               | 85                 | 60 x 60                  | 45 x 45              |                | 21         | 50                     | 37 4102     |
| Castor, Apparatus, Swivel Top | 80                 |                  | 106                |                          |                      |                | 25         | 55                     | 37 4103     |
| Castor, Apparatus, Swivel Top | 100                |                  | 121                |                          |                      |                | 32         |                        | 37 4104     |

Dimensions : Millimetres

## Specification Table

| Description                  | Wheel Diameter (D) | Thread Width (b) | Overall Height (H) | Plate Dimensions (A x B) | Hole Spacing (a x b) | Hole Width (e) | Offset (E) | Carrying Capacity (kg) | Part Number |
|------------------------------|--------------------|------------------|--------------------|--------------------------|----------------------|----------------|------------|------------------------|-------------|
| Castor, Apparatus, Fixed Top | 50                 | 20               | 68                 | 55 x 55                  | 40 x 40              | 6              | -          | 35                     | 37 5101     |
| Castor, Apparatus, Fixed Top | 60                 | 24               | 85                 | 60 x 60                  | 45 x 45              |                |            | 50                     | 37 5102     |
| Castor, Apparatus, Fixed Top | 100                | 24               | 121                |                          |                      |                |            | 55                     | 37 5104     |

Dimensions : Millimetres

## Specification Table

| Description                | Wheel Diameter (D) | Thread Width (b) | Overall Height (H) | Stem Diameter (C) | Stem Length (F) | Plate Diameter (C) | Offset (E) | Carrying Capacity (kg) | Part Number |
|----------------------------|--------------------|------------------|--------------------|-------------------|-----------------|--------------------|------------|------------------------|-------------|
| Castor, Apparatus, Swivel* | 50                 | 20               | 66                 | 8M                | 15              | 35                 | 25         | 35                     | 37 6101     |
| Castor, Apparatus, Swivel* | 60                 | 24               | 83                 | 12M               | 25              | 41                 | 21         | 50                     | 37 6102     |
| Castor, Apparatus, Swivel* | 80                 |                  | 104                |                   |                 |                    | 25         | 55                     | 37 6103     |
| Castor, Apparatus, Swivel* | 100                |                  | 121                |                   |                 |                    | 32         |                        | 37 6104     |

\*Threaded stem swivel castor

Dimensions : Millimetres

## Specification Table

| Description                     | Wheel Diameter (D) | Thread Width (b) | Overall Height (H) | Plate Dimensions (A x B) | Hole Spacing (a x b) | Hole Width (e) | Offset (E) | Pedal Length | Carrying Capacity (kg) | Part Number |
|---------------------------------|--------------------|------------------|--------------------|--------------------------|----------------------|----------------|------------|--------------|------------------------|-------------|
| Castor, Apparatus, Swivel Top** | 50                 | 20               | 68                 | 55 x 55                  | 40 x 40              | 6              | 25         | 76           | 35                     | 37 8101     |
| Castor, Apparatus, Swivel Top** | 60                 | 24               | 85                 | 60 x 60                  | 45 x 45              |                | 21         | 84           | 50                     | 37 8102     |
| Castor, Apparatus, Swivel Top** | 80                 |                  | 106                |                          |                      |                | 25         | 91           | 55                     | 37 8103     |

\*\*Swivel castor with foot brake

Dimensions : Millimetres

## Specification Table

| Description                  | Wheel Diameter (D) | Thread Width (b) | Overall Height (H) | Stem Diameter (C) | Stem Length (F) | Plate Diameter (C) | Offset (E) | Pedal Length | Carrying Capacity (kg) | Part Number |
|------------------------------|--------------------|------------------|--------------------|-------------------|-----------------|--------------------|------------|--------------|------------------------|-------------|
| Castor, Apparatus, Swivel*** | 50                 | 20               | 66                 | 8M                | 15              | 35                 | 25         | 76           | 35                     | 37 9101     |
| Castor, Apparatus, Swivel*** | 60                 | 24               | 83                 | 12M               | 25              | 41                 | 21         | 84           | 50                     | 37 9102     |
| Castor, Apparatus, Swivel*** | 80                 |                  | 104                |                   |                 |                    | 25         | 91           | 55                     | 37 9103     |
| Castor, Apparatus, Swivel*** | 100                |                  | 124                |                   |                 |                    | 32         | 95           |                        | 37 9104     |

\*\*\*Threaded stem castor with foot brake

Dimensions : Millimetres

**Disclaimer** This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. DURATOOL is the registered trademark of the Group. © Premier Farnell plc 2009.