





LOC		DIST		REVISIONS			
AD	00	P	LYR	DESCRIPTION	DATE	DWN	APVD
		B		REVISED PER ECO-11-025276	26DEC11	KH	DY

- 1 MATERIAL:
HOUSING: LCP, GLASS FILLED, UL94V-0.
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.
- 2 FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN
ON PCB TAILS, NICKEL OVERALL.
- 3 FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN-LEAD
ON PCB TAILS, NICKEL OVERALL.
4. SCREWS PACKAGED IN END OF PACKAGING TUBE.
- 5 FOR GROUNDED GUIDE PIN USE Ø3.56±0.08 PTH,
Ø3.66 DRILL, AND Ø6.5 PAD.
6. KEYING PIN SHOWN IN POSITION A. SEE KEYING CHART
ON SHEET 2 FOR OTHER POSITIONS.




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. K. SHOBER 13JAN2011	TE Connectivity	
DIMENSIONS:		CHK J. EABY 13JAN2011		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD J. EABY 13JAN2011	NAME	
	9 PLC ±.01	PRODUCT SPEC	IMPACT, 4 PAIR, 16 COLUMN, HEADER	
Ø	1 PLC ±0.25	APPLICATION SPEC	RIGHT GUIDED, OPEN END WALL	
	2 PLC ±0.13		SIGNAL MODULE, 0.39 PTH	
MATERIAL	3 PLC ±.01	WEIGHT	SIZE CAGE CODE DRAWING NO	
	4 PLC ±.01		A100779C=2007829	
FINISH		CUSTOMER DRAWING	SCALE 6:1	SHEET 1 OF 2 REV B

LOC		DIST		REVISIONS						
AD		00		REV	LYR	DESCRIPTION	DATE	DWN	APVD	
				-	-	SEE SHEET 1	-	-	-	


	H	5.5	8-2007829-6
	H	4.9	8-2007829-5
	H	4.5	8-2007829-4
	H	5.5	8-2007829-3
	H	4.9	8-2007829-2
	H	4.5	8-2007829-1
	G	5.5	7-2007829-6
	G	4.9	7-2007829-5
	G	4.5	7-2007829-4
	G	5.5	7-2007829-3
	G	4.9	7-2007829-2
	G	4.5	7-2007829-1
	F	5.5	6-2007829-6
	F	4.9	6-2007829-5
	F	4.5	6-2007829-4
	F	5.5	6-2007829-3
	F	4.9	6-2007829-2
	F	4.5	6-2007829-1
	E	5.5	5-2007829-6
	E	4.9	5-2007829-5
	E	4.5	5-2007829-4
	E	5.5	5-2007829-3
	E	4.9	5-2007829-2
	E	4.5	5-2007829-1
	D	5.5	4-2007829-6
	D	4.9	4-2007829-5
	D	4.5	4-2007829-4
	D	5.5	4-2007829-3
	D	4.9	4-2007829-2
	D	4.5	4-2007829-1
	C	5.5	3-2007829-6
	C	4.9	3-2007829-5
	C	4.5	3-2007829-4
	C	5.5	3-2007829-3
	C	4.9	3-2007829-2
	C	4.5	3-2007829-1
	B	5.5	2-2007829-6
	B	4.9	2-2007829-5
	B	4.5	2-2007829-4
	B	5.5	2-2007829-3
	B	4.9	2-2007829-2
	B	4.5	2-2007829-1
	A	5.5	1-2007829-6
	A	4.9	1-2007829-5
	A	4.5	1-2007829-4
	A	5.5	1-2007829-3
	A	4.9	1-2007829-2
	A	4.5	1-2007829-1
	-	5.5	2007829-6
	-	4.9	2007829-5
	-	4.5	2007829-4
	-	5.5	2007829-3
	-	4.9	2007829-2
	-	4.5	2007829-1
FINISH	KEY POSITION	DIM M	PART NUMBER

REFER TO WWW.TE.COM
FOR PRODUCT AVAILABILITY


KEY POSITION
CHART




NONE



A



E




B




F




C




G



D



H

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN	J. K. SHOBER	13JAN2011	 TE Connectivity		
			CHKD	J. EABY	13JAN2011			
DIMENSIONS:			TOLERANCES UNLESS OTHERWISE SPECIFIED:			NAME	IMPACT, 4 PAIR, 16 COLUMN, HEADER RIGHT GUIDED, OPEN END WALL SIGNAL MODULE, 0.39 PTH	
mm						PRODUCT SPEC		
			9 PLC			APVD	J. EABY 13JAN2011	
			1 PLC			APPLICATION SPEC		
			3 PLC			SIZE	CAGE CODE	DRAWING NO
			5 PLC			WEIGHT	A100779C=2007829	
			4 PLC			CUSTOMER DRAWING	SCALE	5:1
MATERIAL			FINISH			SHEET 2 OF 2		REV B
-			SEE TABLE					
-								