

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [34250-0001](#)
Status: **Active**
Overview: [MX150™ Sealed and Unsealed Connector System](#)
Description: MX150™ Cable Sealed Female Connector, Single Row, 3 Circuits, Polarization A, with Connector Position Assurance, Black

Documents:
[Drawing \(PDF\)](#)
[Product Specification PS-34250-000 \(PDF\)](#)
[Product Specification PS-34646-001 \(PDF\)](#)
[Application Specification AS-34250-100 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Crimp Housings
Series [34250](#)
Application Power
Comments with Connector Position Assurance (CPA), Dual Key
More Detailed Tech Information <http://ewcap.uscarteams.org>
Overview [MX150™ Sealed and Unsealed Connector System](#)
Product Name MX150™
UPC 756054705056

Physical
Circuits (maximum) 3
Circuits Detail 3
Color - Resin Black
Gender Female
Glow-Wire Compliant No
Keying to Mating Part Yes
Lock to Mating Part Yes
Material - Resin Polyester, Polyphenylene Ether Alloy
Net Weight 7.327/g
Number of Rows 1
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 4.50mm
Pitch - Termination Interface 4.50mm
Polarized to Mating Part Yes
Stackable No
Temperature Range - Operating -40°C to +125°C

Electrical
Current - Maximum per Contact 15A

Material Info

Reference - Drawing Numbers
[Application Specification](#) AS-34250-100
[Product Specification](#) PS-34250-000, PS-34646-001
[Sales Drawing](#) SD-34250-002



image - Reference only

Series

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?
Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)
Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[34250Series](#)

Mates With
Direct Connect only

Use With
[34083](#) Tin (Sn) Cable Seal Female Terminal,
[34081](#) Gold (Au) Cable Seal Female Terminal