

SURFACE MOUNT AUDIO JACKS

- Mates with 2.5mm and 3.5mm plugs
- Designed for reliable interface with audio equipment including computer speakers, headphones, sound cards, cell phones, etc.
- Models available for mono and stereo applications
- Low profile, surface mount design



FOR 2.5 mm PLUGS

SUPPLIED ON TAPE AND REEL

SPECIFICATIONS



Housing: Polyamide, UL Rated 94V-0

Ground Terminal: .012 (.30) Brass, Gold Flash ①

Spring Contacts: .008 (.20) Phosphor Bronze, Gold Flash ② ⑤

Shunt Terminals: .012 (.30) Brass, Gold flash ③ ④



FOR 3.5 mm PLUGS



STEREO SCHEMATIC



MONO SCHEMATIC



CAT. NO. 980TR (Stereo)

CAT. NO. 982TR (Mono)

Tape Spec's: 24mm wide; 16mm pitch

Reel Spec's: 15 inch reel (1,000 pieces per reel)

CAT. NO. 981TR (Stereo)

CAT. NO. 983TR (Mono)

Tape Spec's: 24mm wide; 16mm pitch

Reel Spec's: 15 inch reel (800 pieces per reel)


BINDING POSTS

All Keystone binding posts are designed to prevent accidental contact with current carrying parts. They feature a "limited opening" captivated head to insure safety. Ideal for audio circuitry, R.F. circuitry, oscilloscopes, power supplies and various other applications.


These multi-purpose binding posts feature high current rating, captivated heads and anti-rotation stud mounting.

Note: Binding Posts accept .175" (4.5) Banana Plugs, .080" (2.08) Tip Plugs, Spade Lugs, Alligator Clips, Wires and EZ hooks.

STANDARD BINDING POST



Mounting Detail



For panels up to .281 (7.1) thick

CAT. NO.	COLOR
7004	RED
7005	BLACK

MATERIAL:

Stud: Brass per QQ-B-626


Plating: Silver Plate

Insulation: Nylon

Current Rating: 15 Amps

Stud to Panel Capacitance: 3.3 pF Nominal

UNINSULATED BINDING POST



For panels up to .313 (8.0) thick

CAT. NO.	COLOR
7006	RED
7007	BLACK

MATERIAL:


Stud: Brass per QQ-B-626

Plating: Nickel Plate


Insulation: Nylon

Current Rating: 15 Amps, 1000V AC Working

STANDARD DUAL HEX HEAD



Mounting Detail



GOLD PLATE		NICKEL PLATE	
CAT. NO.	THREAD	CAT. NO.	THREAD
4108	8-32	7018	8-32
4109	10-32	7019	10-32


MATERIAL:

Stud: Brass per ASTM B-16.


Insulation: Nylon

Current Rating: 30 Amps, 1000V AC Working

STANDARD HEX HEAD



Mounting Detail



GOLD PLATE			NICKEL PLATE		
CAT. NO.	THREAD	COLOR	CAT. NO.	THREAD	COLOR
4096	8-32	RED	4091	8-32	RED
4097	8-32	BLACK	4092	8-32	BLACK
7016	10-32	RED	4093	10-32	RED
7017	10-32	BLACK	4094	10-32	BLACK
7023	10-32	WHITE	4198	10-32	WHITE
7024	10-32	YELLOW	4199	10-32	YELLOW

MATERIAL:

Stud: Brass per ASTM B-16.

Insulation: Nylon

Current Rating: 30 Amps, 1000V AC Working