








DESCRIPTION		
REV.	DATE	
NC	09/14/95	INITIAL RELEASE
A	05/10/05	UPDATE DRAWING FORMAT
B	07/25/05	EXPLODE TO SHOW ALL PARTS/ MODIFY DESCRIPTION



RECOMMENDED
CABLE STRIPPING DIM'S



NOTE:
1. CRIMPED CONTACT PIN
HEX CRIMP SIZE .068"



8											
7	CONTACT PIN	BRASS	GOLD	1	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020"	DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex		
6	HEX NUT	BRASS	NICKEL	1							
5	WASHER	BRASS	NICKEL	1							
4	GASKET	SILICONE	RED	1							
3	TOP HAT	BRASS	NICKEL	1							
2	INSULATOR	DELTRIN	NATURAL	1	PART DESCRIPTION BNC CLAMP PLUG (FOR RG-58C/U, 58/U, 142A/U, 223/U)	PART NO. 112348	DWG. NO. 112348.DWG	REV. B	SIZE A	SCALE NA	
1	BODY	BRASS	NICKEL	1							
DESCRIPTION				MATERIAL	FINISH	QTY					