





OPTION CODE -1*






SECTION A-A

NOTES:

1. MATERIAL: GLASS FILLED POLYESTER 94V-0 COLER WHITE.
2. PLATINGS:
P909 - HOT TIN DIP: .000100/(0.00254) MIN.
* THE PRIMARY SHIPPING CARTON WILL BE LABELED "COMPLIANT TO RoHS DIRECTIVE 2002/95/EC AND ELV ANNEX II OF DIRECTIVE 2000/53/EC".
CARTONS WITHOUT THIS LABEL MAY CONTAIN PRODUCT WITH TIN/LEAD PLATING.
3. PRODUCT SPECIFICATION: NONE
4. PACKAGING: BULK
5. TERMINAL TO HOUSING RETENTION FORCE: 3 LBS. MIN.
6. CONNECTORS ARE NOT STACKABLE ON .100/(2.54) CENTERS.
7. TERMINALS CONFORM TO SOLDERABILITY SPECIFICATION SMES-152.
8. .085/(2.16) DIM. WILL VARY DEPENDING ON LEAD THICKNESS.



OPTION CODE -2*



SECTION A-A

4038-N *
ASSEMBLY OPTION CODE
1= STRAIGHT
2= RIGHT ANGLE
TERMINAL SEE CHART

ADD DIMENSION EC NO: UCP2007-0731 DRAWN: PRI DER CHKD: ADERR APPR: FSM TH DATE: 2006/09/29 DATE: 2006/10/03 DATE: 2006/10/17	DESCRIPTION QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 1:1	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION	SHEET NO. 1 OF 2		
			mm	INCH	DRAWN BY SAMIEC	DATE 1992/01/10	TITLE TRANSISTOR SOCKET ASSY 4038 SERIES DWG.			DOCUMENT NO. SDA-4038	
		4 PLACES	± .010	± .010	CHECKED BY	DATE					
		3 PLACES	± .010	± .010	PATEL	1992/01/10					
		2 PLACES	± 0.25	± .014	APPROVED BY	DATE					
		1 PLACE	± 0.36	± .014	LENZ	1992/01/10					
		ANGULAR ± 1/2°		MATERIAL NO.		DOCUMENT NO.					
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART							
				SIZE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

[illegible]