



HiQ™



Dimensions (In.)



Specifications:

- Primary voltage: 115VAC 60Hz
- Primary exciting current: 35mA (max.)
- Secondary voltage (no load): 20.4CT VAC $\pm 0.8V$
- Secondary voltage (full load): 18.0CT VAC $\pm 0.8V$
- Rated secondary current: 0.2 amperes (AC) 60Hz
- Voltage regulation: less than 15% $(V_{NL} - V_{FL}) / (V_{FL}) \times 100$
- Temperature rise (@ room temperature 25°C): less than 50°C
- Breakdown voltage (HIPOT): 2000VAC 50Hz 1 minute
- Coil to coil insulation: 200M Ω (min.) 500VDC
- Strain relief: 10 lbs
- Channel frame material & thickness: iron 0.6mm
- Crossover insulation: 0.05mm polyester tape
- Core size: EI-41
- Core material: hilite core H-23 0.5mm
- Inner insulation: 3 layers of 0.05mm polyester tape
- Outer wrap insulation: 3 layer of 0.05mm polyester tape w/1 pc of fibre board (yellow)
- Bobbin: nylon, normal type 13mm x 16.5mm
- Impregnation: varnish
- Lead wire: PRI UL-1015 AWG22, SEC UL-1007 AWG22

Your source for quality electronics. Toll-free full service

(800) 346-6873

<http://www.mouser.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Xicon:](#)

[41FJ200](#)