



**CONNECTOR  
DESIGNATORS**  
**A-B\*-C-D-E-F**  
**G-H-J-K-L-S**







\* Conn. Desig. B See Note 5  
**DIRECT COUPLING**



Length ± .060 (1.52)  
 Min. Order Length 2.0 Inch  
 (See Note 4)



**STYLE 2**  
**(STRAIGHT)**  
 See Note 1)



**400-002**  
**TAG® Ring Backshell**  
 with Strain Relief  
 Direct Coupling - Low Profile



40

**TABLE III: FRONT ADAPTER**

| Shell<br>Size | J Max - Conn. Designator |              |              |
|---------------|--------------------------|--------------|--------------|
|               | A-D-E-F<br>J-H-L-S       | B-G-K        | C            |
| 08/09         | 1.000 (25.4)             | 1.250 (31.8) |              |
| 10/11         | 1.000 (25.4)             | 1.250 (31.8) |              |
| 12/13         | 1.000 (25.4)             | 1.250 (31.8) | 1.735 (44.1) |
| 14/15         | 1.000 (25.4)             | 1.250 (31.8) | 1.915 (48.6) |
| 16/17         | 1.000 (25.4)             | 1.416 (36.0) | 1.915 (48.6) |
| 18/19         | 1.000 (25.4)             | 1.416 (36.0) | 1.915 (48.6) |
| 20/21         | 1.000 (25.4)             | 1.416 (36.0) | 1.915 (48.6) |
| 22/23         | 1.000 (25.4)             | 1.416 (36.0) | 1.915 (48.6) |
| 24/25         | 1.000 (25.4)             | 1.416 (36.0) | 1.915 (48.6) |
| 28/29         | 1.000 (25.4)             | 1.416 (36.0) | 1.915 (48.6) |
| 32/33         | 1.000 (25.4)             | 1.416 (36.0) | 1.915 (48.6) |
| 36            | 1.000 (25.4)             | 1.416 (36.0) | 1.915 (48.6) |
| 40            | 1.000 (25.4)             | 1.687 (42.9) | 1.915 (48.6) |

See inside back cover  
 fold-out or pages 13 and  
 14 for Tables I and II.

1. When maximum cable entry (page 22) is exceeded, Style 2 will be supplied. (Function S only).
2. Metric dimensions (mm) are indicated in parentheses.
3. Cable range is defined as the accommodations range for the wire bundle or cable. Dimensions shown are not intended for inspection criteria.
4. Consult factory for shorter lengths on straight backshells.
5. When using Connector Designator B refer to pages 18 and 19 for part number development.

**TABLE IV: ELBOW DIMENSIONS**

| Elbow<br>Size | E<br>Max     | F<br>Max     | G<br>Max     | H<br>Max     |
|---------------|--------------|--------------|--------------|--------------|
| 02            | .630 (16.0)  | 1.720 (43.7) | .636 (16.2)  | 1.670 (42.4) |
| 03            | .630 (16.0)  | 1.720 (43.7) | .709 (18.0)  | 1.790 (45.5) |
| 04            | .692 (17.6)  | 1.780 (45.2) | .734 (18.6)  | 1.810 (46.0) |
| 05            | .755 (19.2)  | 1.870 (47.5) | .829 (21.1)  | 1.880 (47.8) |
| 06            | .848 (21.5)  | 1.970 (50.0) | .990 (25.1)  | 1.970 (50.0) |
| 07            | 1.036 (26.3) | 2.170 (55.1) | 1.000 (25.4) | 2.140 (54.4) |
| 08            | 1.130 (28.7) | 2.310 (58.7) | 1.325 (33.7) | 2.250 (57.2) |
| 09            | 1.130 (28.7) | 2.310 (58.7) | 1.325 (33.7) | 2.250 (57.2) |
| 10            | 1.130 (28.7) | 2.310 (58.7) | 1.325 (33.7) | 2.250 (57.2) |

**TABLE V: CABLE ENTRY**

| Dash<br>No. | K<br>Max     | Cable Entry<br>Max |
|-------------|--------------|--------------------|
| 02          | .545 (13.8)  | .250 (6.4)         |
| 03          | .670 (17.0)  | .375 (9.5)         |
| 04          | .795 (20.2)  | .500 (12.7)        |
| 05          | .920 (23.4)  | .625 (15.9)        |
| 06          | 1.045 (26.5) | .750 (19.1)        |
| 07          | 1.170 (29.7) | .875 (22.2)        |
| 08          | 1.295 (32.9) | 1.000 (25.4)       |
| 09          | 1.420 (36.1) | 1.125 (28.6)       |
| 10          | 1.670 (42.4) | 1.250 (31.8)       |

**TABLE VI: CABLE ENTRY**

| Dash<br>No. | L<br>Max     | Cable Range |              |
|-------------|--------------|-------------|--------------|
|             |              | Min         | Max          |
| 02          | .968 (24.6)  | .125 (3.2)  | .250 (6.4)   |
| 03          | 1.046 (26.6) | .250 (6.4)  | .375 (9.5)   |
| 04          | 1.156 (29.4) | .250 (6.4)  | .500 (12.7)  |
| 05          | 1.218 (30.9) | .375 (9.5)  | .625 (15.9)  |
| 06          | 1.343 (34.1) | .500 (12.7) | .750 (19.1)  |
| 07          | 1.468 (37.3) | .625 (15.9) | .875 (22.2)  |
| 08          | 1.593 (40.5) | .625 (15.9) | 1.000 (25.4) |
| 09          | 1.718 (43.6) | .750 (19.1) | 1.125 (28.6) |
| 10          | 1.843 (46.8) | .875 (22.2) | 1.250 (31.8) |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Glenair:

[400HA001NF1909L](#) [400HS002M1506L3](#) [400AA002M1404L](#) [400AS002M1003G3](#) [400AS002M1203G3](#)  
[400AS002M1404G3](#) [400AS002M1605G3](#) [400AS002M1807G3](#) [400AS002M2003G3](#) [400AS002M2004G3](#)  
[400AS002M2004L3](#) [400AS002M2005G3](#) [400AS002M2006G3](#) [400AS002M2007G3](#) [400AS002M2206G3](#)  
[400AS002M2208G3](#) [400AS002M2804L3](#) [400AS002M2805L3](#) [400AS002M2806G3](#) [400AS002M2808L3](#)  
[400AS002M3605L3](#) [400AS002M3606G3](#) [400AS002M3606L3](#) [400AS002T1405L3](#) [400AS002T1605L3](#)  
[400DS002B0802L3](#) [400DS002B1406L3](#) [400DS002N2006F3](#) [400HS001NF2509G3](#) [400HS002NF1506L3](#)  
[400AA001N2005L3](#) [400AC015NF1604L](#) [400FS001M2008L4](#) [400HC015NF1705L](#) [400HD001NF1104L](#)  
[400HD015NF1705L](#) [400HF015NF1705L](#) [400HS001NF1505L4](#) [400HS001NF1905L4](#) [400HS015NF1103L3](#)  
[400AD011NF1202L](#) [400AS011NF2410L](#) [400FC011NF1404F](#) [400FS011NF0802L](#) [400HD011NF1302L](#)  
[400HD011NF2306L](#) [400HS002NF2306L3](#) [400HS011NF2510FD](#) [400JS002NF1803L4](#) [400HS001NF1910G3](#)  
[400AS002M3608G3](#) [400DS002M2002L4](#) [400AD011NF1405FD](#) [400DA002M1406F](#) [400FS004N1006A03B3](#)  
[400AD011NF1003L](#) [400AS011M2007F](#) [400FS001M2405L3](#) [400FS011NF2208F](#) [400HS001N1102L4](#)  
[400HS001NF1904L4](#) [400HS015NF1906L4](#) [400FS011NF1003L](#) [400HS004NF1310A04B4](#) [400HS004NF1512A04B4](#)  
[400HS011NF1504L](#) [400HS011NF1705L](#) [400AC011NF2005L](#) [400AD011NF1002L](#) [400AD011NF2410L](#)  
[400AS007NF2020H08C6A](#) [400AS007NF2816H08C6A](#) [400AS011NF1003L](#) [400AS011NF1202L](#) [400AS011NF1405L](#)  
[400AS011NF2007L](#) [400AS011NF2408L](#) [400AS021M1405S](#) [400FC011NF2206L](#) [400FD011NF0802L](#)  
[400FD011NF1204L](#) [400FD011NF1606L](#) [400FD011NF1807L](#) [400FS011NF1405L](#) [400FS011NF2008L](#)  
[400HC003M2306L](#) [400HC011M1905L](#) [400HC011NF0902L](#) [400HC011NF1504L](#) [400HC011NF1705L](#)  
[400HC011NF1905L](#) [400HC011NF2306L](#) [400HC011NF2506L](#) [400HD011NF0902L](#) [400HD011NF1103L](#)  
[400HD011NF1504L](#) [400HD011NF1904L](#) [400HD011NF1905L](#) [400HD011NF2108L](#) [400HD011NF2508L](#)