

HF92F

MINIATURE INTERMEDIATE POWER RELAY

cUL US

File No.:E134517



File No.:40016109



File No.:CQC09002037814 (DC type)



Features

- 30A switching capability
- Creepage distance: 8mm
- 4kV dielectric strength (between coil and contacts)
- UL insulation system: Class F
- Plastic sealed and dust protected types available
- PCB & QC layouts available
- Environmental friendly product (RoHS compliant)
- Outline Dimensions: (52.0 x 33.7 x 26.7) mm

CONTACT DATA

Contact arrangement	2A, 2C
Contact resistance	50mΩ max.(at 1A 24VDC)
Contact material	AgSnO ₂ , AgCdO
Contact rating (Res. load)	NO: 30A 250VAC; 30A 277VAC NC: 3A 250VAC; 3A 277VAC
Max. switching voltage	277VAC
Max. switching current	30A
Max. switching power	8310VA
Mechanical endurance	5 x 10 ⁶ OPS
Electrical endurance	1 x 10 ⁵ OPS (NO: 30A 277VAC, Resistive load, Room temp., 1s on 9s off) 1 x 10 ⁵ OPS (NC: 3A 277VAC, Resistive load, Room temp., 1s on 9s off)

CHARACTERISTICS

Insulation resistance		1000MΩ (at 500VDC)
Dielectric strength	Between coil & contacts	4000VAC 1min
	Between open contacts	1500VAC 1min
	Between contact poles	2000VAC 1min
Surge voltage (between coil & contacts)		10kV (1.2/50μs)
Operate time (at nomi. volt.)		DC type: 25ms max.
Release time (at nomi. volt.)		DC type: 25ms max.
Temperature rise (at nomi. volt.)		AC type:90K max. DC type:70K max.
Shock resistance	Functional	98m/s²
	Destructive	980m/s²
Vibration resistance		10Hz to 55Hz 1.65mm DA
Humidity		5% to 85% RH
Ambient temperature		AC: -40°C to 65°C DC: -40°C to 85°C
Termination		PCB, QC
Unit weight		Approx. 86g
Construction		Plastic sealed, Flux proofed

Notes: The data shown above are initial values.

COIL

Coil power	DC type: Approx. 1.7W; AC type: Approx. 4.0VA
------------	--

COIL DATA

at 23°C

DC type

Coil Code	Nominal Voltage VDC	Pick-up Voltage VDC max.	Drop-out Voltage VDC min.	Max. Voltage VDC *	Coil Resistance Ω
005D	5	3.8	0.5	8.0	15.3x (1±10%)
006D	6	4.5	0.6	9.6	22x (1±10%)
012D	12	9	1.2	19.2	86x (1±10%)
024D	24	18	2.4	38.4	350x (1±10%)
048D	48	36	4.8	76.8	1390x (1±10%)
110D	110	82.5	11	176	7255x (1±10%)

AC type (at 50Hz)

Coil Code	Nominal Voltage VDC	Pick-up Voltage VDC max.	Drop-out Voltage VDC min.	Max. Voltage VDC *	Coil Resistance Ω
024A5	24	19.2	4.8	26.4	45x (1±10%)
120A5	120	96	24	132	1125x (1±10%)
208A5	208	166.4	41.6	229	3278x (1±10%)
220A5	220	176	44	242	3800x (1±10%)
240A5	240	192	48	264	4500x (1±10%)
277A5	277	221.6	55.4	305	5960x (1±10%)

AC type (at 60Hz)

Coil Code	Nominal Voltage VDC	Pick-up Voltage VDC max.	Drop-out Voltage VDC min.	Max. Allowable Voltage VDC *	Coil Resistance Ω
024A6	24	19.2	4.8	26.4	35.7x (1±10%)
120A6	120	96	24	132	830x (1±10%)
208A6	208	166.4	41.6	229	2600x (1±10%)
220A6	220	176	44	242	2870x (1±10%)
240A6	240	192	48	264	3800x (1±10%)
277A6	277	221.6	55.4	305	4700x (1±10%)



HONGFA RELAY

ISO9001, ISO/TS16949, ISO14001, OHSAS18001, IECQ QC 080000 CERTIFIED

2014 Rev. 1.01

COIL DATA

at 23°C

AC type (at 50Hz/60Hz)

Coil Code	Nominal Voltage VAC	Pick-up Voltage VAC max.		Drop-out Voltage VAC min.		Max. Allowable Voltage VDC *	Coil Resistance Ω
		50Hz	60Hz	50Hz	60Hz		
120A	120	88	96	22	24	132	950 x (1±10%)
208A	208	160	166.4	40	41.6	229	2841 x (1±10%)
240A	240	176	192	44	48	264	3800 x (1±10%)
277A	277	200	221.6	50	55.4	305	5485 x (1±10%)

Notes: * Maximum voltage refers to the maximum voltage which relay coil could endure in a short period of time.

SAFETY APPROVAL RATINGS

UL/CUL ¹⁾	NO	30A 277VAC 1HP 120VAC 2.5HP 240VAC 110 LRA/25.3 FLA 240VAC (DC type)
	NC	3A 277VAC
VDE ¹⁾ (AgSnO ₂)	NO	30A 250VAC 20A 250VAC
	NC	3A 250VAC

Notes: 1) UL certified loads are tested at 40°C. VDE certified loads are tested at 85°C (DC products) or 50°C (AC products).

2) Only typical loads are listed above. Other load specifications can be available upon request.

ORDERING INFORMATION

Type	HF92F	-012D	-2C	2	2	F	(XXX)
Coil Code	XXX D: DC type(5,6,12,24,48,110VDC) XXX A5: AC type 50Hz(24,120,208,220,240,277VAC) XXX A6: AC type 60Hz(24,120,208,220,240,277VAC) XXX A: AC type 50Hz/60Hz(120,208,240,277VAC)						
Contact arrangement	2A: 2 Form A 2C: 2 Form C						
Termination	1: PCB 2, 3: QC						
Contact material	1: AgSnO ₂ 2: AgCdO						
Construction ^{1) 2)}	S: Plastic sealed F: Flux proofed						
Customer special code							


Notes: 1) We recommend dust protected types for a clean environment (free from contaminations like H₂S, SO₂, NO₂, dust, etc.).

We suggest to choose plastic sealed types and validate it in real application for an unclean environment (with contaminations like H₂S, SO₂, NO₂, dust, etc.).


2) Contact is recommended for suitable condition and specifications if water cleaning or surface process is involved in assembling relays on PCB.

Outline Dimensions


1 Type (PCB)




2 Type (QC)



3 Type (QC)




PCB Layout (Bottom view)




Wiring Diagram (Bottom view)

2 Form A




2 Form C



- Remark: 1) In case of no tolerance shown in outline dimension: outline dimension $\leq 1\text{mm}$, tolerance should be $\pm 0.2\text{mm}$; outline dimension $> 1\text{mm}$ and $\leq 5\text{mm}$, tolerance should be $\pm 0.3\text{mm}$; outline dimension $> 5\text{mm}$, tolerance should be $\pm 0.4\text{mm}$.
2) The tolerance without indicating for PCB layout is always $\pm 0.1\text{mm}$.

CHARACTERISTIC CURVES



Disclaimer

The specification is for reference only. See to "Terminology and Guidelines" for more information. Specifications subject to change without notice. We could not evaluate all the performance and all the parameters for every possible application. Thus the user should be in a right position to choose the suitable product for their own application. If there is any query, please contact Hongfa for the technical service. However, it is the user's responsibility to determine which product should be used only.

© Xiamen Hongfa Electroacoustic Co., Ltd. All rights of Hongfa are reserved.