



WELCOME TO
ACCURATE SCREW MACHINE
A Division of MW Industries

[Login / Register](#)
[ENTER](#)

[HOME](#)
[ABOUT ASM](#)
[QUALITY](#)
[TECH TIPS](#)
[CREDIT](#)
[CHAT](#)
[E-SERVICES](#)
[RFQ](#)
[CALL US TOLL-FREE: 1.877.285.2181](#)

[CONTACT ASM](#)


Product Search

By Part No.:

By Keyword:

[ENTER](#)

View Products




- » Bushings
- » Captive Screws & Assemblies
- » Handles / Ferrules
- » Locking Fasteners
- » Nuts
- » Panel Screw Retainers
- » Screws - Standard, Set, Stud
- » Spacers
- » Springs
- » Standoffs / Adapters
- » Thumb Screws
- » Tools
- » Washers
- » **Custom Parts**
- » Optional Product Features



CAPTIVE SOCKET HEAD CAP SCREWS

(1960 Series)



Complete ASM Part No.: 114121 1.00 SS 1

[Material Specifications](#)
[Thread Length Info](#)
[Metric Size Info](#)
[Help](#)
[Back to Product Index](#)

Printed catalog page(s): 129

Tolerance(s): K: ± 0.010 B: ± 0.005

Step 3 of 3: Click here to add part & download CAD Drawings or
Edit values below and click [Up-date](#) **again**

Length	Material	Finish	Options	Point Full Thrd. Self-Seal Opt 'Prefix'
1.00	Steel Stainless Steel	No finish Anodized (Dk. Gray) Anodized (Clear) Anodized (Blue) Anodized (Red) Anodized (YellowGreen) Anodized (Dichromate) Anodized (Dyed Gold) Anodized (Black) Cadmium Clear Plate	Full thread Unselect	Lead Point Self Sealing Self Seal, Lead Pt. Unselect