

Features

Regulated Converters

- Universal input 85-305VAC
- 3W PCB mount package
- <75mW no load power consumption
- Ultra low profile, compact size
- -40°C to +85°C Operating temperature
- Continuous SCP, OCP, OVP
- EN60335, IEC/EN/UL60950 & CE certified

RECOM
AC/DC Converter

Description

The RAC03-GA series are low cost AC/DC power supplies, ideal for PCB mounted, compact, board level industrial applications. They feature universal AC input voltage range, regulated and short-circuit -proof isolated DC outputs, low standby power consumption and -40°C to +85°C operating temperature range. The RAC03-GA have a built-in Class A / FCC Part 15 EMC filter, are certified to IEC/EN/UL60950-1 and EN60335 and are pending to IEC/EN/UL62368 and EN61558 safety standards and come with a three year warranty.

Selection Guide

Part Number	Input Voltage Range [VAC]	Output Voltage [VDC]	Output Current [mA]	Efficiency typ. ⁽¹⁾ [%]	Max. Capacitive Load ⁽²⁾ [μF]
RAC03-3.3SGA	85-305	3.3	910	70	2000
RAC03-05SGA	85-305	5	600	72	1500
RAC03-12SGA	85-305	12	250	78	500
RAC03-15SGA	85-305	15	200	78	200
RAC03-24SGA	85-305	24	130	80	150

On Request


RAC03-09SGA	85-305	9	330	77	1000
-------------	--------	---	-----	----	------

Notes:

Note1: Efficiency is tested at nominal input and full load at +25°C ambient

Note2: Max. Cap. Load is tested at nominal input and full resistive load

Model Numbering



Ordering Example

RAC03-12SGA = 3W Output Power, 12V Output Voltage, Single Output, EMC Class A

Specifications (measured @ ta=25°C, nom. Vin, full load unless otherwise noted)

BASIC CHARACTERISTICS

Parameter	Condition		Min.	Typ.	Max.
Internal Input Filter					Pi-Type
Input Voltage Range	refer to line derating graph on page PA-4		85VAC 120VDC		305VAC 430VDC
Input Current	115VAC 230VAC			70mA 45mA	
Inrush Current	cold start at 25°C	115VAC 230VAC			10A 20A
No Load Power Consumption					75mW
Input Frequency Range	AC Input		45Hz		65Hz
Minimum Load			0%		
Power Factor	115VAC 230VAC			0.53 0.41	
Start-up Time	115VAC, 230VAC			30ms	1s
Hold-up Time	115VAC 230VAC			5ms 40ms	
Internal Operating Frequency	100% load at nominal Vin			65kHz	

continued on next page

RAC03-GA

3 Watt
Single
Output
EMC Class A



FCC **IC** **CE** **E196683**

UL60950-1 certified
IEC/EN60950-1 certified
UL62368-1 pending
IEC/EN62368-1 pending
EN61558-1 pending
EN61558-2-16 pending

Specifications (measured @ $ta=25^\circ\text{C}$, nom. Vin, full load unless otherwise noted)

Output Ripple and Noise ⁽⁴⁾	20MHz BW	0°C to 85°C	3.3, 5 Vout 12Vout 15Vout 24Vout			100mVp-p 150mVp-p 200mVp-p 240mVp-p
		-30°C to 0°C	3.3, 5Vout 12Vout 15, 24Vout			200mVp-p 250mVp-p 300mVp-p


Notes:

Note3: The products were submitted for safety files at AC-Input Operation


Note4: Measurements are made with a 12" twisted pair-wire with a 0.1 μF and 10 μF parallel capacitor across output (low ESR)

Efficiency vs. Load

RAC03-05SGA



RAC03-12SGA




REGULATIONS

Parameter	Condition	Value
Output Accuracy		$\pm 2.5\%$ max.
Line Regulation	low line to high line	$\pm 0.5\%$ max.
Load Regulation	10% to 100% load	$\pm 0.5\%$ max.


Accuracy vs. Load

(@nom. Vin: 115/230VAC)

RAC03-05SGA



RAC03-12SGA




Specifications (measured @ $ta=25^{\circ}\text{C}$, nom. V_{in} , full load unless otherwise noted)

PROTECTIONS		
Parameter	Type	Value
Input Fuse	internal	T1A, 300V
Short Circuit Protection (SCP)	below $100\text{m}\Omega$	long-term mode, auto recovery
Over Voltage Protection (OVP)	3.3Vout	3.8V - 4.9V, hiccup mode auto recovery
	5Vout	5.3V - 6.8V, hiccup mode auto recovery
	12Vout	12.6V - 16.2V, hiccup mode auto recovery
	15Vout	15.75V - 20.3V, hiccup mode auto recovery
	24Vout	25.2V - 32.4V, hiccup mode auto recovery
Over Current Protection (OCP)	3.3Vout	1.41A - 3A, hiccup mode auto recovery
	5Vout	0.91A - 2.2A, hiccup mode auto recovery
	12Vout	0.37A - 0.95A, hiccup mode auto recovery
	15Vout	0.29A - 0.72A, hiccup mode auto recovery
	24Vout	0.19A - 0.45A, hiccup mode auto recovery
Class of Equipment		Class II
Over Voltage Category (OVC)		OVC II
Isolation Voltage ⁽⁵⁾	I/P to O/P	rated for 1 minute
Isolation Resistance		$10\text{M}\Omega$ min.
Insulation Grade		Reinforced
Leakage Current	277VAC, 50Hz	0.1mA max.

Notes:

Note5: For repeat Hi-Pot testing, reduce the time and/or the test voltage

Note6: For operation at 230VAC, an external MOV is recommended. The Varistor should comply with IEC61051-2. eg. EPCOS S14 series




ENVIRONMENTAL			
Parameter	Condition		Value
Operating Temperature Range	@ natural convection 1m/s see graph	without derating	-40°C to +70°C
Maximum Case Temperature			+100°C
Temperature Coefficient			$\pm 0.03^{\circ}/\text{C}$
Operating Altitude			3000m
Operating Humidity	non-condensing		5% - 95% RH
Pollution Degree			PD2
Shock			20G/11ms pulse, 3 times at each x, y, z axes
Vibration			10-150Hz, 2G 10min./1cycle, period 60min. along x,y,z axes for 6 cycles
MTBF	according to MIL-HDBK-217F, G.B.	+25°C +70°C	100 x 10^3 hours 17 x 10^3 hours

continued on next page


Specifications (measured @ $ta=25^{\circ}\text{C}$, nom. V_{in} , full load unless otherwise noted)

Derating Graph

(@ Chamber and natural convection 0.1m/s)



Line Derating Graph



SAFETY AND CERTIFICATION


Certificate Type (Safety)	Report / File Number	Standard
Information Technology Equipment, General Requirements for Safety (LVD)	SA17031845 001	IEC60950-1, 2nd Edition: 2005 + A2, 2013 EN60950-1: 2006 +A2, 2013
Information Technology Equipment, General Requirements for Safety	E196683-A3-UL	UL60950-1, 2nd Edition: 2014 CAN/CSA C22.2 No. 60950-1-07, 2nd Edition: 2014
Audio/video, information and communication technology equipment. Safety requirements	pending	UL62368-1, 2nd Edition CAN/CSA C22.2 No 62368-1
Audio/video, information and communication technology equipment. Safety requirements	pending	IEC62368-1, 2nd Edition: 2014 EN62368-1: 2014
Household and similar electrical appliances - Safety. General requirements	SA1703184L 01001	EN60335: 2012 + A11, 2014
Measurement methods for electromagnetic fields of household appliances and similar apparatus with regard to human exposure	SA1703184L 01001	EN62233: 2008
Safety of power transformers, power supplies, reactors and similar products for supply voltages up to 1100 V Part 2: Particular requirements	pending	EN61558-1: 2005 + A1, 2009 EN61558-2-16: 2009 + A1, 2013
RoHS 2+		RoHS 2011/65/EU + AM2015/863

EMC Compliance	Condition	Standard / Criterion
Information technology equipment - Radio disturbance characteristics - Limits and methods of measurement	EA1703184E 01001 with external components	EN55032: 2015, Class A
Limitations on the amount of electromagnetic interference allowed from digital and electronic devices	EA1703184E 01001	47 CFR FCC Part 15 Subpart B: 2016
ESD Electrostatic discharge immunity test	Air $\pm 8\text{kV}$, Contact $\pm 4\text{kV}$	EN61000-4-2: 2009, Criteria A
Radiated, radio-frequency, electromagnetic field immunity test	3V/m	EN61000-4-3: 2006 + A2, 2010, Criteria A
Fast Transient and Burst Immunity	AC Power Port $\pm 1\text{kV}$	EN61000-4-4: 2012, Criteria A
Surge Immunity	AC Power Port L-N $\pm 1\text{kV}$	EN61000-4-5: 2014, Criteria B
Immunity to conducted disturbances, induced by radio-frequency fields	AC Power Port 3V	EN61000-4-6: 2014, Criteria A
Voltage Dips and Interruption	Voltage Dips >95% Voltage Dips 30% Voltage Interruptions >95%	EN61000-4-11: 2004, Criteria A EN61000-4-11, 2004, Criteria A EN61000-4-11, 2004, Criteria C

continued on next page

Specifications (measured @ $ta=25^\circ C$, nom. V_{in} , full load unless otherwise noted)


EMI Filtering according to EN60335-1 / EN55032 Class B Compliance



DIMENSION and PHYSICAL CHARACTERISTICS

Parameter	Type	Value
Material	Case	black plastic, (UL94 V-0)
	PCB	FR4, (UL94 V-0)
Package Dimension (LxWxH)		37.0 x 24.0 x 15.0mm
Package Weight		20g typ.

Dimension Drawing (mm)



PACKAGING INFORMATION

Parameter	Type	Value
Packaging Dimension (LxWxH)	tube	505.0 x 39.7 x 23.2mm
Packaging Quantity		20pcs
Storage Temperature Range		-40°C to +100°C
Storage Humidity	non-condensing	5% - 95% RH max.

The product information and specifications may be subject to changes even without prior written notice. The product has been designed for various applications; its suitability lies in the responsibility of each customer. The products are not authorized for use in safety-critical applications without RECOM's explicit written consent. A safety-critical application is an application where a failure may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The applicant shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.