



FCIconnect.com


Copyright FCI

PRODUCT NUMBER
XXXXX-YYYHPLF


- LEAD FREE OPTION
SEE NOTE 1,13
- SPECIAL OPTIONS
SEE NOTE 1 OR 10
- HIGH TEMPERATURE PLASTIC
SEE NOTE 1
- NO OF
POSITIONS
SEE NOTE 1
- PIN PLATING
SEE SHEET 2
- BASE PART NO.

67996-X XX-XXX XXX LF

- TAIL LENGTH (EXAMPLE BELOW)
3.0mm=030 12.8mm=128
(SEE NOTE 16 & 17)
- MATING LENGTH (EXAMPLE BELOW)
5.0mm=050 25.5mm=255
(SEE NOTE 16 & 17)
- TOTAL NUMBER OF POSITIONS
FROM 2 (2X1) THRU 72 (2X36) POS.
- PIN PLATING (SEE NOTE 14)
1=0.76µm Au
4= PURE TIN
8=0.36µm Au
- BASE PART NO.
DOUBLE ROW




TOP VIEW




SIDE VIEW

END VIEW



RECOMMENDED HOLE PATTERN



DETAIL P
SCALE 5:1
TYP BOTH ENDS

mat'l. code				surface		tolerance	projection	product family		
NOTE 2 & 3				ISO 1302 ✓		ISO 406 ISO 1101		BERGSTIK		
ltr	ecn no	dr	date	tolerances unless otherwise specified				title		
DF	N11-0180	J.Z	2011-05-31	angles	linear	XX±01/XX±3	INCH/MM	BERGSTIK II HEADER D/R		
DG	ELX-N-13471	J.Z	2011-11-16			XXX±0.005/XXX±13		.100/2.54cc STRAIGHT		
DH	ELX-N-16105	ZK	2013-10-22	0°±2'		XXXX±0020/XXX±05	scale 2:1	dwg no		
				dr	T.BREWBAKER	12/21/94		sheet 1 of 8		
				enrg	T.HANNA	12/21/94		67996		
				chr	J.MURPHY	12/21/94		A3		
				appd	T.HANNA	12/21/94		type Product Customer Drawing		
sheet index	revision	DH	...	DH						
	sheet	1	...	8						

PIN PLATING CODES:	
XXXX-1YY	30u"/0.76u MIN (SEE NOTE 14) OVER 50u"/1.27u MIN Ni
XXXX-2YY	15u"/0.38u MIN (SEE NOTE 14) OVER 50u"/1.27u MIN Ni
XXXX-3YY	50u"/1.27u MIN (SEE NOTE 14) OVER 50u"/1.27u MIN Ni
XXXX-4YY	100u"/2.54u MIN Sn OVER 50u"/1.27u MIN Ni (SEE NOTE 15)
XXXX-4YYHLF	
XXXX-5YY	15u"/0.38u MIN (SEE NOTE 14) OVER 50u"/1.27u MIN Ni
XXXX-6YY	30u"/0.76u MIN (SEE NOTE 14) OVER 50u"/1.27u MIN Ni
XXXX-7YY	30u"/0.76u MIN (SEE NOTE 14) OVER 50u"/1.27u MIN Ni
XXXX-8YY	15u"/0.38u MIN (SEE NOTE 14) OVER 50u"/1.27u MIN Ni
XXXX-9YY	15u"/0.38u MIN (SEE NOTE 14) OVER 50u"/1.27u MIN Ni
XXXX-0YY	30u"/0.76u MIN (SEE NOTE 14) OVER 50u"/1.27u MIN Ni

NOTES

1. PART NUMBER OPTIONS:
PIN PLATING CODES (SEE ABOVE)

HIGH TEMPERATURE MATERIAL:

PART NUMBERS WITH AND WITHOUT "H" WILL BE SUPPLIED WITH HIGH TEMPERATURE PLASTIC.

NUMBER OF POSITIONS :

EVEN NUMBER OF POSITIONS FROM 2 (2X1) THROUGH 72 (2X36).
-X00H INDICATES BERGSTRIIP PRODUCT. SEE PAGE 3
FOR SPECIAL GEOMETRY OF THIS CONTINUOUS STRIP PRODUCT.
AUTOMATED REELS WILL CONTAIN 45,000 PINS.
SEE SPECIFIC PART NUMBERS FOR AVAILABILITY.

PACKAGING:

PACKAGED IN POLY BAGS.
EIGHT DIGIT PART NUMBERS FOLLOWED BY A "T" ARE PACKAGED
IN TUBES. SEE SPECIFIC PART NUMBERS FOR AVAILABILITY.
EIGHT DIGIT PART NUMBERS FOLLOWED BY A "G" ARE PACKAGED
IN GPAX FOR IBM ONLY. SEE SPECIFIC PART NUMBERS FOR AVAILABILITY.
PART NUMBERS FOLLOWED BY A "C" ARE PACKAGED IN TUBES
WITH A PICKUP CAP APPLIED.
EIGHT DIGIT PART NUMBERS FOLLOWED BY A "A" ARE PACKAGED 
IN TAPE/REEL WITH PICKUP CAP P/N 95730-003 APPLIED, PER BUS-14-345.

LEAD FREE:

ADD "HLF" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE
OPTION, NOT AVAILABLE FOR -5YY,-5YYH, -6YY & -6YYH

2. BODY MATERIAL:




BODY MATERIAL : MANUFACTURER'S OPTION OF NYLON, PCT GLASS FIBER
REINFORCED OR MINERAL FILLED LCP FLAME RETARDENT PER UL-94V-0.
COLOR: BLACK
BERGSTRIIP™ PRODUCED WITH HIGH TEMPERATURE LCP
THERMOPLASTIC, FLAME RETARDENT PER UL-94V-0.
COLOR: BLACK

PART NUMBERS WITH "H" AND WITHOUT SUFFIX WILL WITHSTAND EXPOSURE
TO 260° C PEAK TEMPERATURE FOR 20 SECONDS IN
WAVE SOLDER, INFRA-RED OR VAPOR PHASE SOLDER PROCESS.


3. PIN MATERIAL: PHOS BRONZE.
4. MEASURED WITH PART IN RESTRAINED CONDITION.
5. TWO SIDES OF PIN TIPS NOT PLATED. TYPICAL BOTH ENDS.
6. 2LBS/0.9KG MIN PIN RETENTION IN EITHER DIRECTION.
7. MILITARY BERGSTIK HEADER
P/N XXXXX-XY-MIL
NOT AVAILABLE.
8. ±.010/0.25 TOL APPLIES TO ALL "G" TAILS EXCEPT
INDICATED PARTS ON TABLE WHERE +.010/0.25 -.000/0.00
APPLIES.
9. NOTCH CONFIGURATION WILL VARY PER VENDOR'S DISCRETION.
10. BERGSTRIIP™ PART NUMBERS FOLLOWED BY
BY A "B" ARE BULK PRICED.
11. TAIL LENGTH (DIM. G) TO BE ±.008/.020.
12. POSITIONS PER ROW 37 TO 50 CAN BE PRODUCED,
BUT FLATNESS AND CURVATURE MAY NOT BE
HELD AS CLOSE AS 36 POSITIONS.
13. THESE PRODUCTS MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
14. PLATING OPTIONS:
PERFORMANCE PLATING WILL BE EITHER GOLD OR GXT ON POST OR TAIL,
OPTIONALLY (78~295u"/2~7.5u) TIN ON TAIL.
15. "THIS PRODUCT HAS 100% TIN PLATING IN THE INTERFACE AND
HAS NOT BEEN TESTED FOR WHISKER GROWTH IN ALL INTERCONNECT
ENVIRONMENTS."
16. THE OAL DON'T EXCEED 34.5mm
17. INCREMENTS BY 0.1mm IN LENGTHS ONLY
18. FOR SPECIAL PACKAGING REQUEST PLEASE CONTACT PRODUCT MANAGER FOR AVAILABILITY
19. TO DETERMINE DIMENSIONS:
N=NUMBER OF POSITION PER ROW
EXAMPLE: 10 POS. N X .100/2.54

mat'l. code NOTE 2 & 3				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection 	product family BERGSTIK
ltr	ecn	no	dr	date	tolerances unless otherwise specified	INCH/MM scale 2:1 	title
DG					angles linear XX±01/XX±3 XXX±0.005/XXX±.13 XXXX±0020/XXX±.05		BERGSTIK II HEADER D/R .100/2.54cc STRAIGHT
					0°±2'		
				dr	T.BREWBAKER	12/21/94	dwg no
				enr	T.HANNA	12/21/94	sheet 2 of 8
				chr	J.MURPHY	12/21/94	size
				appd	T.HANNA	12/21/94	A3
sheet	revision						type
index	sheet						Product Customer Drawing

BERGSTRIPTM HEADER



REEL PACKING DIMENSIONS



mat'l. code NOTE 2 & 3				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family BERGSTIK			
itr ecn no dr date				tolerances unless otherwise specified						 INCH/MM scale 2:1		title BERGSTIK II HEADER D/R .100/2.54cc STRAIGHT	
DH				angles		linear		$XXX \pm 0.1 / X \pm .3$ $XXX \pm 0.005 / XXX \pm .13$ $XXX \pm 0.020 / XXX \pm .051$					
				0° ± 2'						dwg no		sheet 3 of 8	size
				dr		T.BREWBAKER		12/21/94		67996		A3	
				enr		T.HANNA		12/21/94					
				chr		J.MURPHY		12/21/94					
				app		T.HANNA		12/21/94		type		Product Customer Drawing	
sheet index		revision sheet											

1				2		3				4		5		6		
PRODUCT NUMBER	TOT. PIN LGTH.		TAIL LENGTH		MATING LENGTH				BERGSTRIPTM		LF OPTION					
	DIM F	DIM F	DIM G	DIM G	DIM H	DIM H	PACKAGING	NOTES	AVAILABLE							
	ENGLISH	METRIC	ENGLISH	METRIC	ENGLISH	METRIC										
69132-XYX	0.760	19.30	0.120	3.05	0.540	13.72	POLY BAGS/TUBES	---	---	NO	OB NOTE 1,13					
69133-XYX	0.615	15.62	0.285	7.24	0.230	5.84	POLY BAGS	-	NO							
69157-XYX	0.410	10.41	0.110	2.79	0.200	5.08	POLY BAGS	-	NO							
71217-XYXH	1.000	25.40	0.450	11.43	0.450	11.43	POLY BAGS	---	---	NO						OB
71222-XYXH	0.850	21.59	0.250	6.35	0.500	12.70	POLY BAGS	---	---	NO						OB
72273-XYXH	0.725	18.42	0.110	2.79	0.515	13.08	POLY BAGS	---	---	NO						OB
72448-XYXH	0.658	16.71	0.172	4.37	0.386	9.80	POLY BAGS	---	---	NO						OB
72455-XYXH	0.598	15.19	0.180	4.57	0.318	8.08	POLY BAGS	---	---	NO						OB
72455-632HG	0.598	15.19	0.180	4.57	0.318	8.08	GPAX	NOTE 1	NO	OB						
73503-XYXH	0.420	10.67	0.120	3.05	0.200	5.08	POLY BAGS	---	---	NO						OB
73596-XYXH	0.795	20.19	0.110	2.79	0.585	14.86	POLY BAGS	---	---	NO	OB					
74317-XYXH	0.532	13.51	0.309	7.85	0.123	3.12	POLY BAGS	NOTE 11	---	NO	OB					
74318-XYXH	0.592	15.04	0.369	9.37	0.123	3.12	POLY BAGS	NOTE 11	---	NO	OB					
74999-XYXH	0.508	12.90	0.090	2.29	0.318	8.08	POLY BAGS	---	---	NO	OB					
78212-XYX	0.710	18.03	0.350	8.89	0.260	6.60	POLY BAGS	---	---	NO	OB					
78233-XYX	0.568	14.43	0.150	3.81	0.318	8.08	POLY BAGS	-	NO							
78269-XYX	0.385	9.78	0.095	2.41	0.190	4.83	POLY BAGS	---	---	NO	OB					
78286-XYX	0.500	12.70	0.160	4.06	0.240	6.10	POLY BAGS/TUBES	---	---	NO	OB					
78932-XYX	UNAVAILABLE		UNAVAILABLE		UNAVAILABLE			-	-							
78933-XYX	0.695	17.65	0.285	7.24	0.310	7.87	POLY BAGS	---	---	NO	OB					
78988-XYX	0.540	13.72	0.135	3.43	0.305	7.75	POLY BAGS	---	---	NO	OB					
78989-XYX	UNAVAILABLE		UNAVAILABLE		UNAVAILABLE			-	-							
78990-XYX	UNAVAILABLE		UNAVAILABLE		UNAVAILABLE			-	-							
78991-XYX	UNAVAILABLE		UNAVAILABLE		UNAVAILABLE			-	-							
78992-XYX	UNAVAILABLE		UNAVAILABLE		UNAVAILABLE			-	-							
78993-XYX	UNAVAILABLE		UNAVAILABLE		UNAVAILABLE			-	-							
78994-XYX	UNAVAILABLE		UNAVAILABLE		UNAVAILABLE			-	-	NOTE 1,13						

mat'l. code
NOTE 2 & 3

ltr ecn no dr date

DH

surface
ISO 1302

tolerances unless otherwise specified

angles

0'±2"

dr T.BREWBAKER 12/21/94

engr T.HANNA 12/21/94

chr J.MURPHY 12/21/94

appd T.HANNA 12/21/94

sheet index

revision sheet

tolerance
ISO 406
ISO 1101

linear
XX±01/XX±3
XXX±0.005/XX±.13
XXX±0020/XXX±.051

projection
INCH/MM

scale 2:1

FCI

product family
BERGSTIK

title
BERGSTIK II HEADER D/R
.100/2.54cc STRAIGHT

dwg no 67996

sheet 5 of 8

size A3

type Product Customer Drawing

1

2

3

4

5

6

PRODUCT NUMBER	TOT. PIN LGTH.	TAIL LENGTH	MATING LENGTH					BERGSTRIPTM	LF OPTION		
	DIM F	DIM F	DIM G	DIM G	DIM H	DIM H	PACKAGING	NOTES			AVAILABLE
	ENGLISH	METRIC	ENGLISH	METRIC	ENGLISH	METRIC					
78995-YYY	UNAVAILABLE		UNAVAILABLE		UNAVAILABLE		UNAVAILABLE		NOTE 1,13		
78996-YYY	UNAVAILABLE		UNAVAILABLE		UNAVAILABLE		UNAVAILABLE				
79242-YYY	0.930	23.62	0.340	8.64	0.490	12.45	POLY BAGS	NO	OB		
79243-YYY	1.230	31.24	0.390	9.91	0.740	18.80	POLY BAGS	NO	OB		
79244-YYY	UNAVAILABLE		UNAVAILABLE		UNAVAILABLE		UNAVAILABLE				
79268-YYY	1.020	25.91	0.120	3.05	0.800	20.32	POLY BAGS	NO	OB		
79271-YYY	1.100	27.94	0.500	12.70	0.500	12.70	POLY BAGS	NO	OB		
79425-YYY	0.410	10.41	0.120	3.05	0.190	4.83	POLY BAGS	NO			
79821-YYY	0.730	18.54	0.200	5.08	0.430	10.92	POLY BAGS	NO			
84610-YYYH	0.380	9.65	0.120	3.05	0.160	4.06	POLY BAGS	NO	OB		
84760-YYYH	0.870	22.09	0.150	3.81	0.620	15.74	POLY BAGS	NO	OB		
84784-YYYH	1.130	28.70	0.122	3.09	0.908	23.06	POLY BAGS	NO	OB		
84934-YYYH	1.375	34.93	0.625	15.88	0.650	16.51	POLY BAGS	NO	OB		
84976-YYYH	0.730	18.54	0.400	10.16	0.230	5.84	POLY BAGS	NO	OB		
86503-YYY	0.470	11.94	0.120	3.05	0.250	6.35	POLY BAGS	NO			
86581-YYY	0.450	11.43	0.120	3.05	0.230	5.84	POLY BAGS	NOTE 8	OB		
86817-YYY	0.925	23.50	0.120	3.05	0.705	17.91	POLY BAGS	NO	OB		
86827-YYY	0.700	17.78	0.120	3.05	0.480	12.19	POLY BAGS	NO	OB		
86832-YYY	0.525	13.34	0.100	2.54	0.325	8.26	POLY BAGS	NO			
86834-YYY	1.335	33.91	0.585	14.86	0.650	16.51	POLY BAGS	NO	OB		
86836-YYY	0.870	22.10	0.120	3.05	0.650	16.51	POLY BAGS	NO	OB		
86837-YYY	0.600	15.24	0.120	3.05	0.380	9.65	POLY BAGS	NO			
87037-YYY	1.240	31.50	0.120	3.05	1.020	25.91	POLY BAGS	NO	OB		
87052-YYY	0.990	25.15	0.120	3.05	0.770	19.56	POLY BAGS	NO			
87203-YYY	0.545	13.84	0.150	3.81	0.295	7.49	POLY BAGS	NO	OB		
87344-YYY	1.375	34.93	0.219	5.56	1.056	26.82	POLY BAGS	NO	OB	NOTE 1,13	

Copyright FCI

FCIconnect.com

mat'l. code				surface		tolerance		projection		product family	
NOTE 2 & 3				ISO 1302		ISO 406				BERGSTIK	
ltr	ecn	no	dr	date		tolerances unless otherwise specified		INCH/MM		title	
DH						linear				BERGSTIK II HEADER D/R	
						0°±2'		scale 2:1		.100/2.54cc STRAIGHT	
						dr		T.BREWBAKER 12/21/94		dwg no	
						enr		T.HANNA 12/21/94		sheet 6 of 8	
						chr		J.MURPHY 12/21/94		size	
						appd		T.HANNA 12/21/94		A3	
sheet index		revision sheet								type Product Customer Drawing	

form: A3

1

2

3

4

5

6

PDS: Rev :DH

STATUS: Released

Printed: Oct 29, 2013

PRODUCT NUMBER	TOT. PIN	LGTH.	TAIL LENGTH	MATING LENGTH					BERGSTRIPTM	
	DIM F	DIM F	DIM G	DIM G	DIM H	DIM H	PACKAGING	NOTES	AVAILABLE	LF OPTION
	ENGLISH	METRIC	ENGLISH	METRIC	ENGLISH	METRIC				
87345-XXX	1.218	30.94	0.406	10.31	0.712	18.08	POLY BAGS		NO	NOTE 1,13
87348-XXX	0.930	23.62	0.100	2.54	0.730	18.54	POLY BAGS		NO	
87349-XXX	0.890	22.61	0.110	2.79	0.680	17.27	POLY BAGS		NO	
87381-XXX	0.645	16.38	0.100	2.54	0.445	11.30	POLY BAGS		NO	
87382-XXX	0.675	17.15	0.100	2.54	0.475	12.07	POLY BAGS		NO	
87503-XXYH	0.630	16.00	0.110	2.79	0.420	10.67	POLY BAGS		NO	
87869-XXX	0.690	17.53	0.230	5.84	0.360	9.14	POLY BAGS		NO	
87894-XXX	0.588	14.94	0.170	4.32	0.318	8.08	POLY BAGS	-	NO	
87900-XXX	0.940	23.88	0.120	3.05	0.720	18.29	POLY BAGS	-	NO	
87901-XXX	1.040	26.42	0.120	3.05	0.820	20.83	POLY BAGS	-	NO	
87903-XXX	0.963	24.46	0.337	8.56	0.526	13.36	POLY BAGS		NO	OB
88797-XXX	0.950	24.13	0.320	8.13	0.530	13.46	POLY BAGS		NO	OB
88812-XXX	0.415	10.54	0.085	2.16	0.230	5.84	POLY BAGS/TUBES	NOTE 8	NO	OB
88886-XXX	1.306	33.17	0.276	7.01	0.930	23.62	POLY BAGS		NO	OB
89446-XXX	0.930	23.62	0.120	3.05	0.710	18.03	POLY BAGS		NO	OB
89540-XXX	0.760	19.30	0.280	7.11	0.380	9.65	POLY BAGS		NO	OB
89542-XXX	1.065	27.05	0.125	3.18	0.840	21.34	POLY BAGS		NO	OB
89639-XXX	1.260	32.00	0.118	3.00	1.042	26.47	POLY BAGS		NO	OB
91828-XXX	0.450	11.43	0.120	3.05	0.230	5.84	TUBES		NO	OB
92417-XXX	0.530	13.46	0.110	2.79	0.320	8.13	POLY BAGS	-	NO	
93216-XXYH	0.573	14.55	0.155	3.94	0.318	8.08	POLY BAGS/TUBES		NO	OB
93216-632HG	0.573	14.55	0.155	3.94	0.318	8.08	GPAX	NOTE 1	NO	OB
93217-XXYH	0.395	10.03	0.095	2.41	0.200	5.08	POLY BAGS		NO	OB
93254-XXX	0.563	14.30	0.110	2.79	0.353	8.97	POLY BAGS	-	NO	NOTE 1,13



Copyright FCI

form: A3

[illegible]

