



LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
AG	53		O	REL. PER NPR98-3	4-22-98	LM PS
			A	REV PER EC 0G3C-95-99	22SEP99	DH MZ
			A1	REVISED PER ECO-10-000445	09JAN10	KK AEG



1. MATERIAL:
HOUSING: GLASS-FILLED POLYESTER
CONTACT: PHOSPHOR BRONZE
2. CONNECTOR MATES WITH 0.64 [0.025] SQUARE POSTS.
3. PART DENOTES INDIVIDUAL TWO POSITION SHUNT WHICH IS PACKAGED ON BREAKAWAY COMBS OF TEN SHUNTS.
- 4 ASSEMBLIES ARE DELIVERED IN STICKS OF TEN PARTS.
- 5 FINISH: 1.27µm [0.000050] MIN NICKEL UNDERPLATE OVERALL.
- 6 FINISH: 0.76µm [0.000030] MIN GOLD IN CONTACT AREA.
- 7 FINISH: 0.38µm [0.000015] MIN GOLD IN CONTACT AREA.
- 8 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



8 OBSOLETE

YELLOW	30AU	390088-5	4	5	6
BLUE	15AU	390088-4	4	5	7
BLUE	30AU	390088-3	4	5	6
BLACK	15AU	390088-2	4	5	7
BLACK	30AU	390088-1	4	5	6
HOUSING COLOR	GOLD PLATING	PART NUMBER	NOTES		

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN D. WIEBKING CHK DGH APVD PPS	22-Sep-99 14-NOV-97 14-NOV-97	AMP Incorporated Harrisburg, PA 17105-3608	
DIMENSIONS: MM [INCH]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME SHUNT, DUAL BEAM .100 CL	
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ±.003 4 PLC ± ANGLES ± FINISH -		PRODUCT SPEC - APPLICATION SPEC - WEIGHT -		SIZE A2	CAGE CODE 00779
MATERIAL - SEE NOTE 1		FINISH - SEE NOTE 3		DRAWING NO 390088	SCALE SHT.
		CUSTOMER DRAWING		SHEET	OF
				REV	A1