



Search Results

Evaluate

- FAQ's

How to Buy

- Bill of Material

- Favorite Products List

- Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click to remove) Search Tips

Text Search: 'HSTT12-C5'

Your search criteria matched only one product, shown below

HSTT12-C5



Flexible Ployolefin DRY-SHRINKTMHeat Shrink Tubing

- General Purpose heat shrink tubing for dry locations
- Applications include insulating, protecting, harnessing and identifying wires.
- Material Type: Crosslinked Polyolefin
- Shrink Ratio: 2:1
- Temperature Range: -67°F to 275°F (-55°C to 135°C)
- Flammability Rating: Flame retardant EXCEPT clear
- Voltage: 600 V
- UL Recognized, CSA Certified
- Mil Spec: AMSDTL-23053/5 Class 1 (Colors) Class 2 (Clear)

▪ Part Number	HSTT12C5
▪ RoHS Compliancy Status	Compliant
▪ Part Description	Thin Wall Polyolefin Heat Shrink
▪ Material	Polyolefin cross-linked
▪ Color	Green
▪ CSA Certified	Yes
▪ Military Specification	AMS-DTL-23053/5 Class 1
▪ UL Recognized	E122770
▪ Length (m)	30.5
▪ CE Compliant	No
▪ CE Marking	No
▪ Flammability Rating	Flame Retardant
▪ Length Per Reel (ft.)	100
▪ Length Per Reel (m)	30.5
▪ Max. Recovered I.D. (In.)	.062
▪ Max. Recovered I.D. (mm)	1.6
▪ Min. Expanded I.D. (In.)	.125
▪ Min. Expanded I.D. (mm)	3.2
▪ Nominal Diameter / Size	.125
▪ Nominal Recovered Wall Thickness (In.)	.020
▪ Nominal Recovered Wall Thickness (mm)	.5
▪ Pricing Description	Heat Shrink Thin, .12"(3.2mm) Dia, Green
▪ Shrink Ratio	2:1
▪ Temperature Range	-67°F to 275°F (55°C to 135°C)
▪ Min. Order UOM	RL
▪ Min. Order Qty.	1
▪ BOM Qty. (# of Pkgs.)	0
▪ Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.