




- 1 0.38 μ m [$.000015$] MIN GOLD ON MATING AREA,
1.27 μ m [$.000050$] MIN BRIGHT TIN-LEAD ON CRIMP AREA, BOTH OVER
1.27 μ m [$.000050$] MIN NICKEL.
- 2 2.54 μ m [$.000100$] MIN BRIGHT TIN-LEAD, OVER
1.27 μ m [$.000050$] MIN NICKEL.
- 3 GOLD FLASH ON CRIMP AREA,
2.54 μ m [$.000100$] MIN TIN ON MATING AREA, BOTH OVER
1.27 μ m [$.000050$] MIN NICKEL.
- 4 0.38 μ m [$.000015$] MIN GOLD ON MATING AREA,
GOLD FLASH ON CRIMP AREA, BOTH OVER
1.27 μ m [$.000050$] MIN NICKEL.
- 5 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 6 GOLD PLATING MAY OR MAY NOT BE PRESENT ON THE BOTTOM OF THE CRIMP BARREL

5 OBSOLETE	4	487923-5-
3	6	487923-4
5 OBSOLETE	1	487923-3-
	2	487923-1
FINISH		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.OBERMAN 3-7-90	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK R.STONE 3-8-90				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME			
	0 PLC $\pm$ -		CONTACT, SOLDER TAB, .050 C/L			
	1 PLC $\pm$ -		-			
	2 PLC $\pm$ 0.13 [$.005$]		-			
MATERIAL		3 PLC $\pm$ -	SIZE		CAGE CODE	
PHOSPHOR BRONZE		4 PLC $\pm$ -	A2		00779	
FINISH		ANGLES $\pm$ -	DRAWING NO		RESTRICTED TO	
SEE TABLE		APVD -	C=487923		-	
		PRODUCT SPEC -	SCALE		SHEET	
		APPLICATION SPEC -	10:1		1 OF 1	
		WEIGHT -	CUSTOMER DRAWING		REV	
					D1	