


Data Sheet

Type Number 20379
Designation IEC SR521SW (SR63)
System Silver Oxide / Zinc /
NaOH - Electrolyte

Nominal Voltage 1,55 V
Typical Capacity C 15 mAh
Load 68,1 kOhm, at 20°C down to 1.2 V

Weight (approx.) 0,23 g
Volume 0,06 ccm
Coding..... Date of Manufacturing
Month/Year



Temperature Ranges min max.
Storage 0°C 60°C
Discharge 0°C 60°C*

Dimensions min max.
Diameter (A) 5,65 5,80
Height (B) 1,95 2,15
Shoulder Diameter[E]..... 2,60
Shoulder Height [C]..... 0,06

Typical Capacities (at 20°C)

Discharge Type	Load	End Voltage:	1.2 V
Continuous	68100 Ω	Time:	665 h
24h/d, 7d/w		Capacity [mAh]:	15
Current [μA]:		Energy [mWh]:	24

* Contact VARTA if the application is intended to be outside the range of 0°C to +60°C.

Information and contents in this data sheet are for reference purpose only.
They do not constitute any warranty or representation and are subject to change without notice.
For most current information and further details, please contact your VARTA representative.

VARTA Microbattery GmbH, Daimlerstr. 1, D-73479 Ellwangen/Jagst

Subject to change without prior notice!

Tel.: (+49) 7961/921-0, Telefax: (+49) 7961/921-553

Date of issue: 2014-12-12