




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		F	REVISED PER ECO-08-007327	05SEP08	BM	WM
			F1	REV PER ECO-09-021510	12SEP09	KK	AEG

1. THIS KIT SHIPPED NOT ASSEMBLED.

MATERIAL: SHIELDS – BRIGHT NICKEL PLATED CARBON STEEL.
PLUG HOUSING – POLYPHENYLENE OXIDE, SEE TABLE FOR COLOR.
TERMINAL – HIGH STRENGTH COPPER ALLOY PLATED WITH 0.76µm [.000030] MIN GOLD OR GOLD FLASH OVER PALLADIUM NICKEL PLATE, 0.76µm [.000030] MIN TOTAL ON MATING SURFACE. 1.27µm [.000050] MIN NICKEL UNDERPLATE OVER ENTIRE TERMINAL.

WIRE SIZE: 24 OR 26 AWG SOLID OR 24 AWG 7 STRANDS OF COPPER CONDUCTORS. MAXIMUM INSULATION DIAMETER OF 1.14 [.045] IS ACCEPTABLE FOR MOST APPLICATIONS.

CABLE RANGE: Ø8.89–15.88 [.350–.625].

CENTER-TO-CENTER SPACING OF TERMINALS 2.16 [.085] NOMINAL.

WIRE SIZE: 26–27–28 AWG 7 STRANDS OF COPPER CONDUCTORS. MAXIMUM INSULATION DIAMETER OF 1.14 [.045] IS ACCEPTABLE FOR MOST APPLICATIONS.


DIMENSIONS ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.

PACKAGED 1 KIT PER POLYBAG.

BULK PACKAGED 500 KITS PER CONTAINER.

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

OBSOLETE	COMPAQ-GRAY		E		5-554953-3
	BLACK		B		5-554953-2
	BLACK		E		5-554953-1
	BLACK		B		554953-2
	BLACK		E		554953-1
COLOR		PACKAGED	SLOT SIZE	WIRE SIZE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. SMITH 3-24-95		 Tyco Electronics Corporation Harrisburg, PA 17105-3608				
		CHK D.HUSSEY 4-04-95						
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME PLUG KIT, 50 POSITION, BAIL LOCK, SHIELDED CHAMP —				
		APVD M.HUGHES 4-04-95						
		PRODUCT SPEC —		SIZE CAGE CODE DRAWING NO RESTRICTED TO				
		APPLICATION SPEC —						A2 00779 C=554953 —
MATERIAL 		FINISH 		WEIGHT —				
CUSTOMER DRAWING				SCALE 2:1		SHEET 1 of 1		REV F1