



PRODUCT NUMBER
95000-XXXXLF

PLATING _____
RoHS COMPATIBLE, SEE NOTE 6
PACKAGING TYPE, NOTE 3
TOTAL NB OF POSITIONS, 3 TO 17




0 = 0.20µm GOLD/GXT ON CONTACT AREA
2.0µm MIN MATTE TIN ON TAILS
1 = 0.76µm GOLD/GXT ON CONTACT AREA
2.0µm MIN MATTE TIN ON TAILS
3 = 0.38µm GOLD/GXT ON CONTACT AREA
2.0µm MIN MATTE TIN ON TAILS
T = FULL MATTE TIN 2µm-5µm
1.27µm Ni MIN UNDERPLATING



NOTES:



- 1 - HOUSING MAT'L : HIGH TEMPERATURE THERMOPLASTIC. UL94V-0 COLOR: CREAM
- 2 - PIN MATERIAL : COPPER ALLOY
- 3 - PACKAGING :
= POLY BAGS
T = TUBE, FROM 04 POS UP TO 17 POS
TR = TAPE & REEL SEE TAB45 FOR PRODUCT AVAILIY
- 4 - 7N MIN RETENTION IN EITHER DIRECTION
- 5 - TO DETERMINE DIMENSIONS :
N = NUMBER OF POSITIONS
- 6 - RoHS COMPATIBLE PRODUCT SPECIFICATIONS

- a - MANUFACTURING PROCESS COMPATIBILITY
- THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 30 SECONDES MAX IN A CONVECTION, INFRA-RED OR VAPOR PHASE OR REFLOW OVEN.
 - b - LABELLING:
- MEETS PACKAGING SPECS AS PER GS-14-920
 - c - THIS PRODUCT MEETS EUROPEAN DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DISCRIBED IN GS-47-0004
- 7 - HOLE DIMENSION TO BE $\phi 1.60 \pm 0.07$ FOR INTERFERENCE FIT APPLICATIONS, SEE SHEET 2.
HOLE DIMENSION TO BE $\phi 1.95 \pm 0.07$ FOR NON INTERFERENCE FIT (LOCATIONAL) APPLICATIONS





mat'l. code				surface		tolerance		projection		product family			
				ISO 1302		ISO 406 ISO 1101				MINITEK			
ltr		ecn no		dr		date		tolerances unless otherwise specified		title			
S		B-19986		JCO		15.01.13				MINITEK SMT HDR SR POLARIZATION & LATCHING			
T		B-19995		JCO		15.01.15							
				angles		linear							
				±2°									
								xxx ±0.05		scale 7:1			
M		F11-0023		JCO		11.02.07		dr		J. FABRE		13.01.07	
P		B-15804		JCO		13.08.28		engr		J. FABRE		13.01.07	
N		B-16822		JCO		14.01.23		chr		JL CORDIER		13.01.07	
R		B-19187		LMU		14.10.24		appd		JMC		13.01.07	
sheet		revision		T		A							
index		sheet		1		2							

RECOMMENDATION TO PLACE THE CONNECTOR ONTO THE PCB



NO FORCE TO BE
APPLIED ON THIS AREA,
RISK TO BREAK THE
WALL

PLACE THE CONNECTOR
ON TO THE PCB BY HAND
OR WITH A TOOL BY
PUSHING ON THIS AREA



mat'l. code N/A				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection mm	product family MINITEK
ltr	ecn no	dr	date	tolerances unless otherwise specified		mm	title
A	B-19986	J.FA	15.01.13	angles	linear		MINITEK SMT HDR SR
				0°±x'	.00±.00x	scale 1:1	POLARIZATION & LATCHING
				dr	J.FABRE 15.01.07	FCI	dwg no
				enrg	L.MULIN 15.01.07		sheet 2 of 2
				chr	J.COMPAGNON 15.01.12		size
				appd	JCO 15.01.13		95000 A3
sheet	revision						
index	sheet						
						type Product Customer Drawing	