



Home > Search Tools > Part Number

Part Number Search

You Searched For: **2DB52S-F173-F0**

Note: Data provided here are offered in good faith and are as reliable and accurate as possible. However, they do not form part of any contract of supply or purchase unless specifically confirmed in writing by an authorized representative of ITT. All information and images shown are the property of ITT ICS and are not to be reproduced in any form without direct authorization from ITT ICS.

ITT ICS strongly recommends that you contact your local ITT Sales Office for confirmation of all the details you obtain through these Web pages. Please be aware that data may change at any time and without notice. For a listing of Sales Offices, local sales support, and authorized distributors please use the "Global Sales Locator" located either to the right of this data or at the top of every page.

[Sales Support](#)[Product Overview](#)[Stock Check](#)[Product Home](#)

Our Descriptive Part Number: 2DB52SF173F0

Our Global Manufacturing Part Number: 096448-0001

	CONSULT FACTORY	RoHS compliant =	material restrictions of lead, cadmium, hexavalent chromium, mercury, poly bromated biphenyl ether (PBB) and poly bromide diphenyl ether (PBDE) according to directive 2002/95/EC
	CONSULT FACTORY	RoHS compatible =	Compatible with lead free soldering process

Export Compliance

	Country of Compliance	United States
	Export Compliance Notes	Classification "P" Pending factory review.

Product Datasheet	
Product Group	Microminiature
Product Sub-Family	2D
Shell Size	B
Contact Type	Socket
Contact Arrangement	52
Float Mounts	Without
Hardware	Jackscrew - Low Profile (factory installed)
Alternate Finish Modification Code	None
Contacts For Assembly	Without
Shell Material	Steel, Yellow Chromate over Cadmium.
Mounting Hardware and Float Mounts	Stainless Steel
Insulator Material	Glass-filled nylon
Contacts Material and Finish	Copper alloy, gold plate
Contact Retention	Thermoplastic internal shoulder snaps into a locking groove in the contact.
Retention Force	4 lbs. min. axial load
Twist Pin Contacts	Seven outer wiping surfaces assure electrical continuity even under severe shock and vibration.
Positive Contact Alignment	Flexible pin is recessed in insulator cavity and rugged socket is exposed.
Keys	Guide-in Keys and Keyways assure alignment during mating
Polarization	Keystone-shaped shells
Contact Spacing	.075 inch (1.91mm)
Contact Termination	Crimp snap-in