

D2FL40

400V 1.3A


FEATURES

- Small SMT
- Low noise
- trr50ns

APPLICATION

- Switching power supply
- DC/DC converter
- Free Wheel
- Home Appliances, Office Equipment
- Telecommunication, Factory Automation

OUTLINE DIMENSIONS



RATINGS

● Absolute Maximum Ratings (If not specified Tl=25°C)


Item	Symbol	Conditions	Ratings	Unit
Storage Temperature	Tstg		-40~150	°C
Operating Junction Temperature	Tj		150	°C
Maximum Reverse Voltage	VRM		400	V
Average Rectified Forward Current	IO	50Hz sine wave, R-load, Ta=25°C On alumina substrate	1.3	A
		50Hz sine wave, R-load, Ta=25°C On glass-epoxy substrate	1.05	
Peak Surge Forward Current	IFSM	50Hz sine wave, Non-repetitive 1 cycle peak value, Tj=25°C	40	A

● Electrical Characteristics (If not specified Tl=25°C)

Item	Symbol	Conditions	Ratings	Unit
Forward Voltage	VF	IF=1.3A, Pulse measurement	Max.1.3	V
Reverse Current	IR	VR=VRM, Pulse measurement	Max.10	μA
Reverse Recovery Time	trr	IF=0.5A, IR=1A	Max.50	ns
Thermal Resistance	θjl	junction to lead	Max.24	°C/W
	θja	junction to ambient, On alumina substrate	Max.90	
		junction to ambient, On glass-epoxy substrate	Max.120	


D2FL40

Forward Voltage




D2FL40

Forward Power Dissipation




$T_j = T_{jmax}$




D2FL40

Derating Curve




$$V_R = V_{RM}$$




D2FL40

Derating Curve




$$V_R = V_{RM}$$



D2FL40

Peak Surge Forward Capability



D2FL40 Junction Capacitance

