

9730 Multi-Conductor - Multi-Pair Snake Cable

 For more Information
 please call

1-800-Belden1

**Description:**

24 AWG stranded (7x32) tinned copper conductors, Datalene® insulation, twisted pairs, individually shielded w/Beldfoil® (100% coverage), 24 AWG stranded tinned copper drain wire, overall PVC jacket.

Physical Characteristics (Overall)**Conductor****AWG:**

# Pairs	AWG	Stranding	Conductor Material	Dia. (mm)
3	24	7x32	TC - Tinned Copper	0.6096

Insulation**Insulation Material:**

Insulation Trade Name	Insulation Material	Dia. (mm)
Datalene®	FPE - Foam Polyethylene	1.5494

Inner Shield**Inner Shield Material:**

Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)
Beldfoil® (Z-Fold®)	Tape	Aluminum Foil-Polyester Tape	100

Inner Shield Drain Wire AWG:

AWG
24

Inner Shield Drain Wire Stranding: 7x32

Inner Shield Drain Wire Conductor Material: TC - Tinned Copper

Outer Shield**Outer Shield Material:**

Outer Shield Material
Unshielded

Outer Jacket**Outer Jacket Material:**

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cabling

Overall Nominal Diameter: 8.484 mm

Pair**Pair Color Code Chart:**

Number	Color
1	Black & Red
2	Black & White
3	Black & Green

Pair Lay Length & Direction:

Lay Length (mm)	Twists/ft. (twist/m)
44.449825	22.475

Mechanical Characteristics (Overall)

9730 Multi-Conductor - Multi-Pair Snake Cable

Operating Temperature Range:	-20°C To +80°C
UL Temperature Rating:	60°C (UL AWM Style 2493)
Bulk Cable Weight:	68.457 Kg/Km
Max. Recommended Pulling Tension:	226.858 N
Min. Bend Radius (Install)/Minor Axis:	88.900 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CM
CEC/C(UL) Specification:	CM
AWM Specification:	UL Style 2493 (300 V 60°C)
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	UL1685 UL Loading
----------------	-------------------

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	89730

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)
100

Nom. Inductance:

Inductance (µH/m)
0.75463

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)
41.0125

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/m)
76.1192

Nom. Mutual Capacitance:

Capacitance (pF/m)
127.959

Nominal Velocity of Propagation:

VP (%)
76

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
78.744

9730 Multi-Conductor - Multi-Pair Snake Cable

Ind. Pair Nominal Shield DC Resistance @ 20 Deg. C: 49.215 Ohm/km

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100m)
.384	2.42794
.7056	2.85447
.768	2.88728
1.024	3.08414
1.4112	3.31381
1.536	3.37943
2.048	3.70753
2.8224	4.23249
3.072	4.42935
4.096	5.15117
5.6448	5.84018
6.144	6.03704
8.192	6.98853
11.2896	8.03845
12.288	8.43217
24.576	11.7132

Max. Operating Voltage - UL:

Voltage
300 V RMS (UL AWM Style 2493)

Max. Recommended Current:

Current
2.5 Amps per conductor @ 25°C

Notes (Overall)

Notes: Datalene® insulation features include low dielectric constant and a dissipation factor for high-speed, low-distortion data handling. Physical properties include good crush resistance and light weight.

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9730 060100	30 MT	2.313 KG	CHROME		3 FS PR #24 FHDPE PVC
9730 0601000	305 MT	20.865 KG	CHROME	C	3 FS PR #24 FHDPE PVC
9730 06010000	3,048 MT	235.869 KG	CHROME	C Y	3 FSPR #24 FHDPE PVC
9730 060500	152 MT	11.113 KG	CHROME	C	3 FS PR #24 FHDPE PVC

Notes:

C = CRATE REEL PUT-UP.

Y = FINAL PUT-UP LENGTH MAY VARY -10% TO +20% FROM LENGTH SHOWN.MAY CONTAIN 2 PIECES. MINIMUM LENGTH OF ANY ONE PIECE IS 1500'.

Revision Number: 1 Revision Date: 04-17-2008

© 2011 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not

9730 Multi-Conductor - Multi-Pair Snake Cable

to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.
Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.