

## Voltage Regulator Diodes

### FEATURES

- Silicon zener diodes
- Low profile surface-mount package
- Zener and surge current specification
- Low leakage current
- Excellent stability
- Moisture sensitivity level: level 1, per J-STD-020
- Compliant to RoHS Directive 2011/65/EU and in accordance to WEEE 2002/96/EC
- Halogen-free according to IEC 61249-2-21 definition



### MECHANICAL DATA

**Case:** Sub SMA

Molding compound, UL flammability classification rating 94V-0

Base P/N with suffix "G" on packing code - green compound (halogen-free)

Base P/N with prefix "H" on packing code - AEC-Q101 qualified

**Terminal:** Matte tin plated leads, solderable per JESD22-B102

Meet JESD 201 class 1A whisker test

with prefix "H" on packing code meet JESD 201 class 2 whisker test

**Polarity:** Indicated by cathode band

**Weight:** 0.019g (approximately)

**Sub SMA**

| MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS (T <sub>A</sub> =25°C unless otherwise noted)             |                                   |             |       |
|----------------------------------------------------------------------------------------------------------|-----------------------------------|-------------|-------|
| PARAMETER                                                                                                | SYMBOL                            | VALUE       | UNIT  |
| Forward voltage @ I <sub>F</sub> =0.2A                                                                   | V <sub>F</sub>                    | 1.2         | Volts |
| Power dissipation at T <sub>L</sub> =80°C<br>T <sub>A</sub> =25°C (Note 1)                               | P <sub>tot</sub>                  | 2.3<br>1.0  | Watts |
| Non-repetitive peak pulse power dissipation<br>100µs square pulse (Note 2)                               | P <sub>ZSM</sub>                  | 300         | Watts |
| Non-repetitive peak pulse power dissipation<br>10/1000µs waveform (BZD27C6V8P to BZD27C100P)<br>(Note 2) | P <sub>RSM</sub>                  | 150         | Watts |
| Non-repetitive peak pulse power dissipation<br>10/1000µs waveform (BZD27C110P to BZD27C220P)<br>(Note 2) | P <sub>RSM</sub>                  | 100         | Watts |
| Thermal resistance junction to ambient (Note 1)                                                          | R <sub>θJA</sub>                  | 180         | °C/W  |
| Thermal resistance junction to lead                                                                      | R <sub>θJL</sub>                  | 30          | °C/W  |
| Operating and storage temperature range                                                                  | T <sub>J</sub> , T <sub>STG</sub> | -55 to +175 | °C    |

Note 1: Mounted on Cu-Pad size 5mm x 5mm

Note 2: T<sub>J</sub>=25°C prior to surge

| ORDERING INFORMATION  |                    |              |                     |         |                                       |
|-----------------------|--------------------|--------------|---------------------|---------|---------------------------------------|
| PART NO.              | AEC-Q101 QUALIFIED | PACKING CODE | GREEN COMPOUND CODE | PACKAGE | PACKING                               |
| BZD27CxxP<br>(Note 1) | Prefix "H"         | RU           | Suffix "G"          | Sub SMA | 1,800 / 7" Plastic reel (8mm tape)    |
|                       |                    | RV           |                     | Sub SMA | 3,000 / 7" Plastic reel (8mm tape)    |
|                       |                    | RT           |                     | Sub SMA | 7,500 / 13" Paper reel (8mm tape)     |
|                       |                    | MT           |                     | Sub SMA | 7,500 / 13" Plastic reel (8mm tape)   |
|                       |                    | RQ           |                     | Sub SMA | 10,000 / 13" Paper reel (8mm tape)    |
|                       |                    | MQ           |                     | Sub SMA | 10,000 / 13" Plastic reel (8mm tape)  |
|                       |                    | R3           |                     | Sub SMA | 1,800 / 7" Plastic reel (12mm tape)   |
|                       |                    | RF           |                     | Sub SMA | 3,000 / 7" Plastic reel (12mm tape)   |
|                       |                    | R2           |                     | Sub SMA | 7,500 / 13" Paper reel (12mm tape)    |
|                       |                    | M2           |                     | Sub SMA | 7,500 / 13" Plastic reel (12mm tape)  |
|                       |                    | RH           |                     | Sub SMA | 10,000 / 13" Paper reel (12mm tape)   |
|                       |                    | MH           |                     | Sub SMA | 10,000 / 13" Plastic reel (12mm tape) |

Note 1: "xx" defines voltage from 6.8V (BZD27C6V8P) to 220V (BZD27C220P)

| EXAMPLE       |           |                    |              |                     |                    |
|---------------|-----------|--------------------|--------------|---------------------|--------------------|
| PREFERRED P/N | PART NO.  | AEC-Q101 QUALIFIED | PACKING CODE | GREEN COMPOUND CODE | DESCRIPTION        |
| BZD27C10P RU  | BZD27C10P |                    | RU           |                     |                    |
| BZD27C10P RUG | BZD27C10P |                    | RU           | G                   | Green compound     |
| BZD27C10PHRU  | BZD27C10P | H                  | RU           |                     | AEC-Q101 qualified |

## RATINGS AND CHARACTERISTICS CURVES

(TA=25°C unless otherwise noted)

FIG. 1 TYPICAL FORWARD CHARACTERISTICS




FIG. 2 TYP. DIODE CAPACITANCE vs REVERSE VOLTAGE




FIG. 3 POWER DISSIPATION vs AMBIENT TEMPERATURE





FIG. 4 MAXIMUM PULSE POWER DISSIPATION vs ZENER VOLTAGE




| Device     | Device<br>Marking<br>Code | Working Voltage<br>(Note 1) |      | Differential<br>Resistance |      | Temperature<br>Coefficient |      | Test<br>Current | Reverse Current@<br>Reverse Voltage |       |
|------------|---------------------------|-----------------------------|------|----------------------------|------|----------------------------|------|-----------------|-------------------------------------|-------|
|            |                           | $V_Z @ I_{ZT}$              |      | $r_{dif} @ I_Z$            |      | $ALPH_Z @ I_Z$             |      | $I_{ZT}$        | $I_R$                               | $V_R$ |
|            |                           | V                           |      | $\Omega$                   |      | $\%/^{\circ}C$             |      | mA              | $\mu A$                             | V     |
|            |                           | Min.                        | Max. | Typ.                       | Max. | Min.                       | Max. |                 | Max.                                |       |
| BZD27C6V8P | D7                        | 6.4                         | 7.2  | 1                          | 3    | 0                          | 0.07 | 100             | 10                                  | 3     |
| BZD27C7V5P | D8                        | 7.0                         | 7.9  | 1                          | 2    | 0                          | 0.07 | 100             | 50                                  | 3     |
| BZD27C8V2P | D9                        | 7.7                         | 8.7  | 1                          | 2    | 0.03                       | 0.08 | 100             | 10                                  | 3     |
| BZD27C9V1P | E0                        | 8.5                         | 9.6  | 2                          | 4    | 0.03                       | 0.08 | 50              | 10                                  | 5     |
| BZD27C10P  | E1                        | 9.4                         | 10.6 | 2                          | 4    | 0.05                       | 0.09 | 50              | 7                                   | 7.5   |
| BZD27C11P  | E2                        | 10.4                        | 11.6 | 4                          | 7    | 0.05                       | 0.10 | 50              | 4                                   | 8.2   |
| BZD27C12P  | E3                        | 11.4                        | 12.7 | 4                          | 7    | 0.05                       | 0.10 | 50              | 3                                   | 9.1   |
| BZD27C13P  | E4                        | 12.4                        | 14.1 | 5                          | 10   | 0.05                       | 0.10 | 50              | 2                                   | 10    |
| BZD27C15P  | E5                        | 13.8                        | 15.6 | 5                          | 10   | 0.05                       | 0.10 | 25              | 1                                   | 11    |
| BZD27C16P  | E6                        | 15.3                        | 17.1 | 6                          | 15   | 0.06                       | 0.11 | 25              | 1                                   | 12    |
| BZD27C18P  | E7                        | 16.8                        | 19.1 | 6                          | 15   | 0.06                       | 0.11 | 25              | 1                                   | 13    |
| BZD27C20P  | E8                        | 18.8                        | 21.2 | 6                          | 15   | 0.06                       | 0.11 | 25              | 1                                   | 15    |
| BZD27C22P  | E9                        | 20.8                        | 23.3 | 6                          | 15   | 0.06                       | 0.11 | 25              | 1                                   | 16    |
| BZD27C24P  | F0                        | 22.8                        | 25.6 | 7                          | 15   | 0.06                       | 0.11 | 25              | 1                                   | 18    |
| BZD27C27P  | F1                        | 25.1                        | 28.9 | 7                          | 15   | 0.06                       | 0.11 | 25              | 1                                   | 20    |
| BZD27C30P  | F2                        | 28                          | 32   | 8                          | 15   | 0.06                       | 0.11 | 25              | 1                                   | 22    |
| BZD27C33P  | F3                        | 31                          | 35   | 8                          | 15   | 0.06                       | 0.11 | 25              | 1                                   | 24    |
| BZD27C36P  | F4                        | 34                          | 38   | 21                         | 40   | 0.06                       | 0.11 | 10              | 1                                   | 27    |
| BZD27C39P  | F5                        | 37                          | 41   | 21                         | 40   | 0.06                       | 0.11 | 10              | 1                                   | 30    |
| BZD27C43P  | F6                        | 40                          | 46   | 24                         | 45   | 0.07                       | 0.12 | 10              | 1                                   | 33    |
| BZD27C47P  | F7                        | 44                          | 50   | 24                         | 45   | 0.07                       | 0.12 | 10              | 1                                   | 36    |
| BZD27C51P  | F8                        | 48                          | 54   | 25                         | 60   | 0.07                       | 0.12 | 10              | 1                                   | 39    |
| BZD27C56P  | F9                        | 52                          | 56   | 25                         | 60   | 0.07                       | 0.12 | 10              | 1                                   | 43    |
| BZD27C62P  | G0                        | 58                          | 66   | 25                         | 80   | 0.08                       | 0.13 | 10              | 1                                   | 47    |
| BZD27C68P  | G1                        | 64                          | 72   | 25                         | 80   | 0.08                       | 0.13 | 10              | 1                                   | 51    |
| BZD27C75P  | G2                        | 70                          | 79   | 30                         | 100  | 0.08                       | 0.13 | 10              | 1                                   | 56    |
| BZD27C82P  | G3                        | 77                          | 82   | 60                         | 200  | 0.08                       | 0.13 | 10              | 1                                   | 62    |
| BZD27C91P  | G4                        | 85                          | 91   | 60                         | 200  | 0.08                       | 0.13 | 5               | 1                                   | 68    |
| BZD27C100P | G5                        | 94                          | 106  | 60                         | 200  | 0.09                       | 0.13 | 5               | 1                                   | 75    |
| BZD27C110P | G6                        | 104                         | 116  | 80                         | 250  | 0.09                       | 0.13 | 5               | 1                                   | 82    |
| BZD27C120P | G7                        | 114                         | 127  | 150                        | 300  | 0.09                       | 0.13 | 5               | 1                                   | 91    |
| BZD27C130P | G                         | 124                         | 141  | 150                        | 300  | 0.09                       | 0.13 | 5               | 1                                   | 100   |
| BZD27C150P | G9                        | 138                         | 156  | 150                        | 300  | 0.09                       | 0.13 | 5               | 1                                   | 110   |
| BZD27C160P | H0                        | 153                         | 171  | 150                        | 350  | 0.09                       | 0.13 | 5               | 1                                   | 120   |
| BZD27C180P | H1                        | 168                         | 191  | 280                        | 450  | 0.09                       | 0.13 | 5               | 1                                   | 130   |
| BZD27C200P | H2                        | 188                         | 212  | 350                        | 750  | 0.09                       | 0.13 | 5               | 1                                   | 150   |
| BZD27C220P | H3                        | 208                         | 233  | 430                        | 900  | 0.09                       | 0.13 | 5               | 1                                   | 160   |

 Notes: 1. Pulse test:  $t_p \leq 5ms$ .

| Device     | Rev.<br>Breakdown<br>Voltage | Test<br>Current | Temperature<br>Coefficient |      | Clamping Voltage |                     | Reverse Current@<br>Stand-Off Voltage |           |
|------------|------------------------------|-----------------|----------------------------|------|------------------|---------------------|---------------------------------------|-----------|
|            | $V_{(BR)}@I_{test}$          | $I_{test}$      | $ALPHz@I_{test}$           |      | $V_c$            | $@I_{RSM}$ (Note 1) | $I_R$                                 | $@V_{WM}$ |
|            | V                            | mA              | %/ $^{\circ}C$             |      | V                | A                   | $\mu A$                               | V         |
|            | Min.                         |                 | Min.                       | Max  | Max.             |                     | Max.                                  |           |
| BZD27C7V5P | 7                            | 100             | 0                          | 0.07 | 11.3             | 13.3                | 1500                                  | 6.2       |
| BZD27C8V2P | 7.7                          | 100             | 0.03                       | 0.08 | 12.3             | 12.2                | 1200                                  | 6.8       |
| BZD27C9V1P | 8.5                          | 50              | 0.03                       | 0.08 | 13.3             | 11.3                | 100                                   | 7.5       |
| BZD27C10P  | 9.4                          | 50              | 0.05                       | 0.09 | 14.8             | 10.1                | 20                                    | 8.2       |
| BZD27C11P  | 10.4                         | 50              | 0.05                       | 0.10 | 15.7             | 9.6                 | 5                                     | 9.1       |
| BZD27C12P  | 11.4                         | 50              | 0.05                       | 0.10 | 17               | 8.8                 | 5                                     | 10        |
| BZD27C13P  | 12.4                         | 50              | 0.05                       | 0.10 | 18.9             | 7.9                 | 5                                     | 11        |
| BZD27C15P  | 13.8                         | 50              | 0.05                       | 0.10 | 20.9             | 7.2                 | 5                                     | 12        |
| BZD27C16P  | 15.3                         | 25              | 0.06                       | 0.11 | 22.9             | 6.6                 | 5                                     | 13        |
| BZD27C18P  | 16.8                         | 25              | 0.06                       | 0.11 | 25.6             | 5.9                 | 5                                     | 15        |
| BZD27C20P  | 18.8                         | 25              | 0.06                       | 0.11 | 28.4             | 5.3                 | 5                                     | 16        |
| BZD27C22P  | 20.8                         | 25              | 0.06                       | 0.11 | 31               | 4.8                 | 5                                     | 18        |
| BZD27C24P  | 22.8                         | 25              | 0.06                       | 0.11 | 33.8             | 4.4                 | 5                                     | 20        |
| BZD27C27P  | 25.1                         | 25              | 0.06                       | 0.11 | 38.1             | 3.9                 | 5                                     | 22        |
| BZD27C30P  | 28                           | 25              | 0.06                       | 0.11 | 42.2             | 3.6                 | 5                                     | 24        |
| BZD27C33P  | 31                           | 25              | 0.06                       | 0.11 | 46.2             | 3.2                 | 5                                     | 27        |
| BZD27C36P  | 34                           | 10              | 0.06                       | 0.11 | 50.1             | 3                   | 5                                     | 30        |
| BZD27C39P  | 37                           | 10              | 0.06                       | 0.11 | 54.1             | 2.8                 | 5                                     | 33        |
| BZD27C43P  | 40                           | 10              | 0.07                       | 0.12 | 60.7             | 2.5                 | 5                                     | 36        |
| BZD27C47P  | 44                           | 10              | 0.07                       | 0.12 | 65.5             | 2.3                 | 5                                     | 39        |
| BZD27C51P  | 48                           | 10              | 0.07                       | 0.12 | 70.8             | 2.1                 | 5                                     | 43        |
| BZD27C56P  | 52                           | 10              | 0.07                       | 0.12 | 78.6             | 1.9                 | 5                                     | 47        |
| BZD27C62P  | 58                           | 10              | 0.08                       | 0.13 | 86.5             | 1.7                 | 5                                     | 51        |
| BZD27C68P  | 64                           | 10              | 0.08                       | 0.13 | 94.4             | 1.6                 | 5                                     | 56        |
| BZD27C75P  | 70                           | 10              | 0.08                       | 0.13 | 103.5            | 1.5                 | 5                                     | 62        |
| BZD27C82P  | 77                           | 10              | 0.08                       | 0.13 | 114              | 1.3                 | 5                                     | 68        |
| BZD27C91P  | 85                           | 5               | 0.09                       | 0.13 | 126              | 1.2                 | 5                                     | 75        |
| BZD27C100P | 94                           | 5               | 0.09                       | 0.13 | 139              | 1.1                 | 5                                     | 82        |
| BZD27C110P | 104                          | 5               | 0.09                       | 0.13 | 150              | 1                   | 5                                     | 91        |
| BZD27C120P | 114                          | 5               | 0.09                       | 0.13 | 152              | 0.9                 | 5                                     | 100       |
| BZD27C130P | 124                          | 5               | 0.09                       | 0.13 | 185              | 0.81                | 5                                     | 110       |
| BZD27C150P | 138                          | 5               | 0.09                       | 0.13 | 205              | 0.73                | 5                                     | 120       |
| BZD27C160P | 153                          | 5               | 0.09                       | 0.13 | 224              | 0.67                | 5                                     | 130       |
| BZD27C180P | 168                          | 5               | 0.09                       | 0.13 | 229              | 0.6                 | 5                                     | 150       |
| BZD27C200P | 188                          | 5               | 0.09                       | 0.13 | 254              | 0.54                | 5                                     | 160       |
| BZD27C220P | 208                          | 5               | 0.09                       | 0.13 | 279              | 0.35                | 5                                     | 176       |


Notes: 1. Non-repetitive peak reverse current in accordance with "IEC 60-1, Section 8" (10/1000  $\mu s$  pulse)

PACKAGE OUTLINE DIMENSIONS



| DIM. | Unit (mm) |      | Unit (inch) |       |
|------|-----------|------|-------------|-------|
|      | Min       | Max  | Min         | Max   |
| B    | 1.70      | 1.90 | 0.067       | 0.075 |
| C    | 2.70      | 2.90 | 0.106       | 0.114 |
| D    | 0.16      | 0.30 | 0.006       | 0.012 |
| E    | 1.23      | 1.43 | 0.048       | 0.056 |
| F    | 0.80      | 1.20 | 0.031       | 0.047 |
| G    | 3.40      | 3.80 | 0.134       | 0.150 |
| H    | 2.45      | 2.60 | 0.096       | 0.102 |
| I    | 0.35      | 0.85 | 0.014       | 0.033 |
| J    | 0.00      | 0.10 | 0.000       | 0.004 |

SUGGESTED PAD LAYOUT



| Symbol | Unit (mm) | Unit (inch) |
|--------|-----------|-------------|
| A      | 1.4       | 0.055       |
| B      | 1.2       | 0.047       |
| C      | 3.1       | 0.122       |
| D      | 1.9       | 0.075       |
| E      | 4.3       | 0.169       |

MARKING DIAGRAM



P/N = Marking Code  
G = Green Compound  
YW = Date Code  
F = Factory Code

### Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors in accuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.