





| REV. | DATE     | DESCRIPTION           |
|------|----------|-----------------------|
| A    | 11/26/03 | UPDATE DRAWING FORMAT |



RECOMMENDED  
CABLE STRIPPING DIM'S



NOTES:

1. CRIMPED FERRULE  
HEX CRIMP SIZE .255"
2. CONTACT PIN TO SOLDER

|             |              |              |         |   |                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |           |        |                               |  |                            |                                                                         |  |         |        |          |
|-------------|--------------|--------------|---------|---|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------|--------|-------------------------------|--|----------------------------|-------------------------------------------------------------------------|--|---------|--------|----------|
|             |              |              |         |   | <div>UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [ ] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.</div> <div>UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:<br/>0.5 – 8mm ± 0.20mm<br/>8 – 30mm ± 0.40mm<br/>30 – 120mm ± 0.50mm</div> <div>UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:<br/>.020 – .315 = ± 0.007”<br/>.315 – 1.180 = ± 0.015”<br/>1.180 – 4.724 = ± 0.020”</div> <div>DO NOT SCALE DRAWING</div> | APPROVALS |        | DATE                          |  | <div>Amphenol Connex</div> |                                                                         |  |         |        |          |
| 8           |              |              |         |   |                                                                                                                                                                                                                                                                                                                                                                                                                                                                       | DRAWN     | G.R.S. | 11/26/03                      |  |                            |                                                                         |  |         |        |          |
| 7           |              |              |         |   |                                                                                                                                                                                                                                                                                                                                                                                                                                                                       | CHECKED   |        |                               |  |                            |                                                                         |  |         |        |          |
| 6           | FERRULE      | BRASS        | GOLD    | 1 |                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |           |        |                               |  |                            | PART DESCRIPTION<br><div>SMA CRIMP PLUG<br/>(FOR RG–8/X, LMR–240)</div> |  |         |        |          |
| 5           | HEX NUT      | BRASS        | GOLD    | 1 |                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |           |        |                               |  |                            |                                                                         |  |         |        |          |
| 4           | LOCK WASHER  | BRASS        | GOLD    | 1 |                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |           |        |                               |  |                            | PART NO.<br><div>132231</div>                                           |  |         |        |          |
| 3           | CONTACT PIN  | PHOS. BRONZE | GOLD    | 1 |                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |           |        |                               |  |                            |                                                                         |  |         |        |          |
| 2           | INSULATOR    | TEFLON       | NATURAL | 1 |                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |           |        |                               |  |                            |                                                                         |  |         |        |          |
| 1           | HOUSING/BODY | BRASS        | GOLD    | 1 |                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |           |        |                               |  |                            |                                                                         |  |         |        |          |
| DESCRIPTION |              |              |         |   | MATERIAL                                                                                                                                                                                                                                                                                                                                                                                                                                                              | FINISH    | QTY    | CAD FILE<br>C:/132/132231.DWG |  | DWG. NO. 132231.DWG        |                                                                         |  | REV. NC | SIZE A | SCALE NA |