




Directive 2002/95/EC
"RoHS"
Compliant

NOTES:

- METAL SHELLS: STEEL; min. 315µm TIN over 40-80µm NICKEL
- INSULATORS: PBT GF UL 94 V-0; BLACK
- SIGNAL CONTACTS: COPPER ALLOY; 7,5A nominal
PLATING MATING AREA: 30µm HARD GOLD over min. 50µm NICKEL
FEMALE CONTACTS WIRE BRIDGE FROM POS. 1 TO POS. 2
- CONNECTOR IS PART MARKED: 13-000201 CONEC ABC

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name
a	Origin		

tolerance	dim. in mm
date	name
drawn	20.06.07 Schmidt
appd.	20.06.07 Koch
norm	
d-old	

scale:	2:1
material:	see notes
title:	Micro TCA Single Port Female, Crimp Style with wire bridge
dwg no:	Inventor 10
	13K1A2076
part no:	13-000201

CONEC

DIN-A3
sh: 1