

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

74752-4101

Status:

Active

Overview:

SFP+ Passive Cable Assembly

Description:

SFP+ Passive Cable Assembly, 10Gbps, 24 AWG Cable, Pull-to-Release Plunger Style Latch, 1.0m Length



Series

image - Reference only

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E72548

General

Product Family

Series

Assembly Configuration

Comments

Connector to Connector

Overview

Product Name

UPC

Cable Assemblies

74752

Dual Ended Connectors

Meets customer requirements for speeds up to 10 Gbps. Passive cables may require host pre-emphasis and equalization to reach at the longer lengths.

SFP Plus-to-SFP Plus

SFP+ Passive Cable Assembly

SFP Plus

800756661292

Physical

Cable Length

Circuits (Loaded)

Gender

Lock to Mating Part

Material - Metal

Net Weight

Packaging Type

Single Ended

Waterproof / Dustproof

Wire Insulation Diameter

Wire Size AWG

Wire/Cable Type

1.0m

TWO DIFFERENTIAL PAIR

Male-Male

Yes

Beryllium Copper, Zinc Alloy

100.000/g

Bag

No

Yes

N/A

24

Twin-ax

Electrical

Impedance

Shield Type

Shielded

Voltage - Maximum

100#

Full Shield

Yes

3.3V

Material Info

Reference - Drawing Numbers

Sales Drawing

SD-74752-001

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

74752Series

Mates With

74441 SFP Plus (SFP+) Host Connector

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[74752-4101](#)