

SSM-120-S-DV

SSM-116-S-SV

Surface
SMT
Mount

.025"sq SMT SOCKET SSM SERIES

Mates with:

TSW, MTSW, TST,
TSS, ZST, ZSS, DW,
EW, ZW, TSM

SPECIFICATIONS

For complete specifications
and recommended PCB layouts
see www.samtec.com?SSM

Insulator Material:
Black Liquid
Crystal Polymer

Contact Material:
Phosphor Bronze

Plating: Au, PdNi or
Sn over 50µ" (1,27µm) Ni

Current Rating:
3A @ 80°C ambient (-DV/-SV
mated with TSM-DV)
4A @ 80°C ambient (-DH/-SH
mated with TSW-D)

Voltage Rating:
475 VAC (-SV/-DV mated
with TSW)
450 VAC (-SH/-DH mated
with TSM)

Operating Temp Range:
-55°C to +125°C with Gold
-55°C to +105°C with Tin

Contact Resistance:
10 mΩ max
Insertion Depth:
SV/DV is (4,34mm) .171" to
(7,24mm) .285" or pass-through
from top; (5,56mm) .219" plus
board thickness minimum from
bottom; SH/DH is (4,34mm)
.171" to (6,35mm) .250"

Insertion Force:
(Single contact only)
5oz (1,39N) average

Normal Force:
125 grams (1,21N) average

Withdrawal Force:
(Single contact only)
2oz (0,56N) average

RoHS Compliant:
Yes

Processing:

Max Processing Temp:
230°C for 60 seconds, or
260°C for 20 seconds 3x

Lead-Free Solderable:
Yes

-DH Coplanarity:
Less than 28 positions
(0,15mm) .006" max

More than 27 positions
(0,20mm) .008" max

-SH, -SV, -DV Coplanarity:
(0,15mm) .006" max

Note: Some lengths,
styles and options
are non-standard,
non-returnable.

SSM

1

NO. PINS
PER ROWPLATING
OPTIONROW
OPTIONOTHER
OPTION02 thru 36
(-SV, -SH, -DH)02 thru 40
(-DV)

APPLICATION SPECIFIC OPTION

Alignment Pin available.
Call Samtec.

APPLICATIONS




-L

= 10µ" (0,25µm) Gold on contact,
Matte Tin on tail

-S

= 30µ" (0,76µm) Gold on contact,
Matte Tin on tail

APPLICATION



-BE

= Bottom Entry
(-DV & -SV only)

-LC

= Locking Clip
(-DV & -SV only)
Contact Samtec for
-DH & -SH

-K

= (6,50mm) .256" DIA
Polyimide film
Pick & Place Pad
(5 positions min.)
-DV & -SV only

-“XXX”

= Polarized Position
(-BE not available)


-M

= Metal Pick &
Place Pad
(5 positions min.)
-DV only



-P

= Plastic Pick &
Place Pad
(-DV & -SV only)
(5 pos. minimum)




-TR

= Tape & Reel Packaging
(29 positions max.)


-SV

= Single Row Vertical Pin




-DV

= Double Row Vertical Pin




-SH

= Single Row Horizontal Pin



-DH

= Double Row Horizontal Pin



Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: 1-800-SAMTEC-9 or 812-944-6733 • Fax: 812-948-5047

SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0 • Fax: +49 (0) 89 / 89460-299

SAMTEC NORDIC/BALTIC • Tel: +46-84477280 • Fax: +46-87420413

SAMTEC JAPAN • Tel: 045-475-1385 • Fax: 045-475-1340

SAMTEC HONG KONG • Tel: 852-26904858 • Fax: 852-26904842

SAMTEC KOREA • Tel: 82-31-717-5685 • Fax: 82-31-717-5681

SAMTEC SILICON VALLEY • Tel: 408-395-5900 • Fax: 408-395-1520

SAMTEC FRANCE • Tel: 01 60 95 06 60 • Fax: 01 60 95 06 61

SAMTEC ISRAEL • Tel: 972-3-7526600 • Fax: 972-3-7526690

SAMTEC CHINA • Tel: 86-21-61103766 • Fax: 86-21-5423 4575

SAMTEC SOUTH AFRICA • Tel: 27 11 454 4317 • Fax: 27 86 6714432

SAMTEC UK • Tel: 01236 739292 • Fax: 01236 727113

SAMTEC ITALY • Tel: 39 039 6890337 • Fax: 39 039 6890315

SAMTEC INDIA • Tel: +91-80-3272 1612 • Fax: +91-80-4152 8187

SAMTEC TAIWAN • Tel: 886-2-2735-6109 • Fax: 886-2-2735-5036

SAMTEC ANZ • Tel: 613 9512 7747 • Fax: 613 9512 7745