

THIS DRAWING IS UNPUBLISHED.





RELEASED FOR PUBLICATION

© COPYRIGHT copyright_date BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A2	REDRAWN TO CREO	19APR2017	JJH	JP



1. DELIVERY STATE: WRAPPED UP ROLL WITH STEP BETWEEN TERMINALS = 11.9±0.2mm
STATO DI FORNITURA: AVVOLTI SU BOBINA CON PASSO TRA TERMINALI DI = 11.9±0.2mm

2. SUITABLE FOR SINGLE WIRE SEAL TE PN 281934
ADDETTO PER GOMMINO TE 281934

3. MAX. CURRENT CAPACITY: 14A

CUSTOMER DRAWING FOR INFORMATION ONLY
DISEGNO PER CLIENTE SOLO PER RIFERIMENTO

PRE-TIN
(PRE-STAGNATO)

BRASS
(OTTONE)

282465-1

FINISH/COLOUR
(FINITURE/COLORE)

MATERIAL
(MATERIALE)

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN BERTINI 12DEC1992

CHK A. BRUNI 12DEC1992

APVD -

PRODUCT SPEC

APPLICATION SPEC

114-20045

WEIGHT -

CUSTOMER DRAWING



TE Connectivity

NAME
MINI MIC RS TAB CONTACT

-

-

SIZE

A3

CAGE CODE

-

DRAWING NO

©-282465


RESTRICTED TO

-

SCALE 5:1

SHEET 1 OF 1

REV A2




INS. DIA. RANGE
(DIAM. ISOLANTE)

2

WIRE RANGE
(RANGO FILO)

1.5-2.5mm²

DIMENSIONS:
mm



MATERIAL

-

-

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±
2 PLC	±
3 PLC	±
4 PLC	±

±0.3

ANGLES

FINISH

±2°

-

-