

RF AMPLIFIER

MODEL *TM9064*

Available as: TM9064, 4 Pin 0.500" TO-8 (T4)
 TN9064, 4 Pin 0.450" Sq. Surface Mount (SM3)
 BX9064, SMA Connectorized Housing (H1L-Laser)
 BXP9064, SMA Connectorized Housing (HPak)

Features

- Ultra Broad Bandwidth 100-3000 MHz
- High Gain: 18.5 dB Typical
- Cross to the Cougar AC3064, our Model BX9064
- Cross to the Cougar ACP3064, our Model BXP9064
- Screening to the Tables of MIL-STD-883 Available

Specifications

CHARACTERISTIC	TYPICAL Ta= 25 °C	MIN/MAX Ta = -55 °C to +85 °C
Frequency	100 - 3000 MHz	100 - 3000 MHz
Gain	18.5 dB	16.5 dB Min.
Gain Flatness	+/- 0.3 dB	+/- 0.8 dB Max.
Noise Figure (dB) (400-3000 MHz)	3.3 dB	4.5 dB Max.
(100-400 MHz)	4.5 dB	5.5 dB Max.
VSWR In	1.5:1	2.0:1 Max.
Out	1.5:1	2.0:1 Max.
Power Output @ 1 dB Comp. (dBm)	+16.5 dBm	+15.0 dBm
Reverse Isolation (dB)	-36 dB	-
Power Vdc	+15	+15
mA	80	88 Max.

Typical Intermodulation Performance at 25 °C


Second Order Harmonic Intercept Point.....+52 dBm (Typ.)
 Second Order Two Tone Intercept Point.....+46 dBm (Typ.)
 Third Order Two Tone Intercept Point.....+27 dBm (Typ.)
 (Typical at 25°C under a +15 volt supply)

Maximum (No Damage) Ratings

Ambient Operating Temperature-55°C to +100 °C
 Storage Temperature-62°C to +125 °C
 Case Temperature+125 °C
 DC Voltage+17 Volts
 Continuous RF Input Power+13 dBm
 Short Term RF Input Power 100 Milliwatts (1 Minute Max.)
 Maximum Peak Power 0.5 Watt (3 µsec Max.)


Note: Care should always be taken to effectively ground the case of each unit.
 Revision 5/16/2012

Typical Performance Data



Spectrum Microwave · 1900 West College Ave. · State College, PA. 16801 · PH (888) 553-7531 · Fax (888) 553-7532

www.SpectrumMicrowave.com Spectrum Microwave · 2707 Black Lake Place · Philadelphia, PA. 19154 · PH (215) 618-3700 · Fax (215) 464-4001



DWG NO. 088-00304		SH 1 OF 1	REV P1	1	
REVISIONS					
ECN	REV.	DESCRIPTION		CHNG/DATE	APPVD/DATE
XXX	P1	PRELIMINARY RELEASE		2012/05/14	



CAUTION

THIS ASSEMBLY CONTAINS PARTS SENSITIVE TO DAMAGE BY ELECTROSTATIC DISCHARGE (ESD). USE ESD PRECAUTIONARY PROCEDURES WHEN TOUCHING, REMOVING OR INSERTING

SEE SEPARATE PARTS LIST IN ELECTRONIC STORAGE

SPECTRUM MICROWAVE PROPRIETARY INFORMATION
THIS DOCUMENT IS THE SOLE PROPERTY OF SPECTRUM MICROWAVE, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SPECTRUM MICROWAVE, INC ARE PROHIBITED.

UNLESS OTHERWISE SPECIFIED		3rd ANGLE PROJECTION		SPECTRUM MICROWAVE, INC	
ANSI		DRAWN WAR		2707 Black Lake Place	
CHECKED		DATE 2012/05/14		Philadelphia, PA 19154-1008 (USA)	
ENGRG H PHAM		2012/05/14		TITLE	
MFG				OUTLINE, HPAK	
QA				SIZE B	REV P1
DO NOT SCALE DRAWING		CAGE CODE 60979		DWG NO. 088-00304	
		SCALE: 1.5:1		SHEET 1 OF 1	