




Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.

MARKETING SALES DRAWING
DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []



NOTES:

1. SUPPLIED WITH SILVER PLATED
HEX NUT AND LOCKWASHER.
2. TUSONIX STANDARD PART NUMBER: 4201-000.
TUSONIX RoHS COMPLIANT PART NUMBER: 4201-000 LF.
CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
3. LEAD FINISH: STANDARD PART #: 60/40 SOLDER PLATED. RoHS PART #: SILVER PLATED.
4. PART MARKING: TRADEMARK AND VARIATION NUMBER ON HEX FLATS.
STANDARD PART: BLACK INK. RoHS PART: GREEN INK.

MIN. CAP. (pF)	WORKING VOLTAGE (WVdc)		CURRENT (Idc)	I.R. MIN.	DWV	MINIMUM NO LOAD INSERTION LOSS (dB) AT 25°C PER MIL-STD -220			
	10 MHz	100 MHz				1 GHz	10 GHz		
1500	85°C	125 °C	10 A	10 G	400 VDC 2 SEC.				
	200	100				5	45	65	70

X-2015 Rev-0	REVISION RECORD										--TOLERANCES-- Unless Otherwise Specified		Title BUSHING STYLE EMI FILTER			
	Original Release C.O.										DECIMAL ± .031 [0.79]					
	0										ANGLES ± 		Drawn S.M. 01-23-02		Scale 4 X	
	1	093 WAS .094. LE 12-9-83									TUSONIX TUCSON, ARIZONA		Approved T.C. 01-23-02		A	4201-000
	2	WAS SK6644-030-S. L.E. 1-13-84														
	3	DIM'S & TOL'S REV'D. RELEASED. L.E. 1-8-85														
	4	CURRENT UNIT "A" ADDED. L.E. 8-20-85									ADDED NOTES. S.M. 07-27-05					
5	2595 10 GHz WAS 60. E.C. 7-14-92									20050726-2-12						
6	6774 RDN TO COMP FMT & ADDED METRIC. S.M. 01-23-02															
7	20020123-1-01 DIM. .890 REMOVED TOL. S.M. 02-18-02															
8	20020215-6-01															

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix:](#)

[4201-000LF](#)