


HONEYWELL
PART NUMBER
1SM817-T
PRODUCT CODE
TWE8017

REV	DOCUMENT	CHANGED BY	CHECK
6	0034444	JA 16OCT07	PSR




NOTES

1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .375 ± .002 CENTERS

2 - TERMINALS ARE PLATED FOR SOLDERING

3 - SWITCH WILL WITHSTAND TEMPERATURE OF 250°F

RELEASE NO.:
PR-5692
REPLACES
X63948-SM

CHARACTERISTICS		ELECTRICAL DATA			DESIGN UNITS: INCH TOLERANCES UNLESS NOTED:		DRAWN	JA	16OCT07	Honeywell				
OPERATING FORCE-----3-5 OZ.		CONTACT ARRANGEMENT SPDT					CHECK	PSR	16OCT07					
RELEASE FORCE-----1 OZ. MIN.		30 VOLTS DC RATING			NO PLACE X ± 0.040		THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE				
					ONE PLACE .X ± 0.030									
DIFFERENTIAL TRAVEL-----.002 MAX.		SEA LEVEL 50,000 FT			TWO PLACE .XX ± 0.015					INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY				
					THREE PLACE .XXX ± 0.005									
OVERTRAVEL-----.005 MIN.		INDUCTIVE 3 AMP 2.5 AMP			FOUR PLACE .XXXX ± 0.0005		RASTER			SIZE	TYPE	DRAWING NAME		REV
		RESISTIVE 5 AMP 5 AMP								B	I	1SM817-T		6
		MAXIMUM INRUSH 24 AMP			ANGLES ± 2					SCALE -		SHEET 1 OF 1		
APPROVALS		KEMA, CE	5A, 250V ~ T85 1E4		THIRD ANGLE PROJECTION 									
		UL, CSA	5A, 250 VAC				BRAND L4							