

Sensor/Actuator cable - SAC-8P-MS/15,0-285 SH SCO - 1574564

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Sensor/Actuator cable, 8-position, PUR, gray RAL 7001, shielded, Plug straight M12 SPEEDCON, A-coded, on free cable end, Cable length: 15 m, Twisted pair cables

as in the figure, but with a gray conductor



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	50 pc
Weight per Piece (excluding packing)	222.22 g
Custom tariff number	85444290
Country of origin	Poland

Technical data

Dimensions

Length of cable	15 m
Stripping length of the free conductor end	50 mm

Ambient conditions

Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)
Degree of protection	IP65
	IP67

General

Rated current at 40°C	2 A
Rated voltage	30 V
Number of positions	8
Insulation resistance	≥ 100 MΩ
Coding	A - standard
Status display	No
Overvoltage category	II
Degree of pollution	3

Material

Sensor/Actuator cable - SAC-8P-MS/15,0-285 SH SCO - 1574564

Technical data

Material

Flammability rating according to UL 94	HB
Contact material	CuZn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material of grip body	TPU, hardly inflammable, self-extinguishing
Material, knurls	Zinc die-cast, nickel-plated
Sealing material	NBR

Standards and Regulations

Flammability rating according to UL 94	HB
--	----

Cable

Cable type	PUR, gray, shielded
Cable type (abbreviation)	285
Cable abbreviation	Li12YC11Y-HF
Conductor cross section	4x 2x 0.25 mm ² (Signal line)
	1x 0.25 mm ² (Drain wire)
AWG signal line	24
Conductor structure signal line	32x 0.10 mm
Wire colors	white-brown, green-yellow, gray-pink, blue-red
Twisted pairs	2 cores to the pair
Overall twist	4 pairs for core
Shielding	Tinned copper braided shield
Optical shield covering	85 %
External sheath, color	gray RAL 7001
External cable diameter D	7.6 mm ±0.2 mm
Minimum bending radius, flexible installation	7.5 x D
Number of bending cycles	3000000
Bending radius	100 mm
Traversing path	1.2 m
Traversing rate	1.4 m/s
Acceleration	2 m/s ²
Outer sheath, material	PUR
Material conductor insulation	PES
Conductor material	Bare Cu litz wires
Insulation resistance	≥ 100 MΩ*km
Nominal voltage, cable	350 V
Test voltage, cable	1200 V

Sensor/Actuator cable - SAC-8P-MS/15,0-285 SH SCO - 1574564

Technical data

Cable

Resistance to oil	very good oil and chemical resistance
Other resistance	ozone and UV resistant
	Low adhesion
	abrasion-resistant
	notch tough
Ambient temperature (operation)	-50 °C ... 80 °C (cable, fixed installation)
	-40 °C ... 80 °C (cable, flexible installation)

Classifications

eCl@ss

eCl@ss 4.0	27060306
eCl@ss 4.1	27060306
eCl@ss 5.0	27061801
eCl@ss 5.1	27061801
eCl@ss 6.0	27061801
eCl@ss 7.0	27061801

ETIM

ETIM 3.0	EC001855
ETIM 4.0	EC001855
ETIM 5.0	EC001855


UNSPSC

UNSPSC 6.01	31251501
UNSPSC 7.0901	31251501
UNSPSC 11	31251501
UNSPSC 12.01	31251501
UNSPSC 13.2	31251501

Drawings

Sensor/Actuator cable - SAC-8P-MS/15,0-285 SH SCO - 1574564

Schematic diagram




Pin assignment M12 plug, 8-pos., view plug side

Cable cross section



PUR, gray, shielded [285]

Dimensional drawing



Plug, M12 x 1, straight, shielded

Circuit diagram



Contact assignment of M12 connector/socket