

CR Series

CR6™ LED Downlight - 6"

Product Description

The CR6™ LED downlight delivers up to 800 lumens of exceptional 90+ CRI light while achieving up to 67 lumens per watt. This breakthrough performance is achieved by combining the high efficacy and high-quality light of Cree TrueWhite® Technology. The CR6 is available in warm and cool color temperatures, and has a variety of trim options. It easily installs into most standard six-inch recessed IC or non-IC housings.

Applications: New construction or upgrade for residential and commercial lighting

Performance Summary

Utilizes Cree TrueWhite® Technology

Initial Delivered Lumens: 625, 800 lumens

Input Power: 9.5, 12 watts

CRI: 90


CCT: 2700K, 3000K, 3500K, 4000K

Limited Warranty¹: 5 years

Lifetime: Designed to last 50,000 hours

Dimming: Dimmable to 5%*

¹See www.cree.com/lighting/products/warranty for warranty terms



Housings & Accessories

Reference Housing & Accessory documents for more details.

Trims & Reflectors	
CT6A	CT6AB
- Diffuse anodized finish reflector	- Black diffuse anodized finish reflector
CT6AW	
- Wheat diffuse anodized finish reflector	- Flat black reflector and trim
Housings	
Edison Base Housing	GU24 Base Surface Mount Housing
RC	SC6-GU24
- New Construction	- Textured white finish
RR6	SC6-GU24 US
- Retrofit	- Textured white finish, U.S. Manufactured
C6	SC6-BL-GU24
- Recessed "Pan" Conversion Kit	- Textured black finish
GU24 Base Housing	GU24 Base Ceiling Mount Housing
RC6-GU24	SC6-CM-GU24
- New Construction	- Textured white finish
H6-GU24	SC6-CM-GU24 US
- Architectural	- Textured white finish, U.S. Manufactured
RR6-GU24	SC6-CM-BL-GU24
- Retrofit	- Textured black finish
C6-GU24	GU24 Base Wall Mount Housing
- Recessed "Pan" Conversion Kit	SC6-WM-GU24
C6-120V-LSA	- Textured white finish
- Hard Wire Recessed "Pan" Conversion Kit	SC6-WM-BL-GU24
	- Textured black finish

Ordering Information

Example: CR6-625L-27K-12-E26

QUICKSHIP™

For full list of Cree Quick Ship products visit www.cree.com/lighting/quickship

CR	6			12	
Series	Size	Initial Delivered Lumens	CCT	Voltage	Base Type
CR	6 6" (152mm)	625L 9.5W, 625 Lumens - 66 LPW 800L 12W, 800 Lumens - 67 LPW	27K 2700K 30K 3000K 35K 3500K 40K 4000K	12 120 Volts	E26 Edison Base GU24 GU24 Base (Title 24 Compliant)

* Reference www.cree.com/Lighting/Products/Indoor/Downlights-US/CR-Series for recommended dimmers



Rev. Date: V3 10/28/2015

US: www.cree.com/lighting

T (800) 236-6800 F (262) 504-5415

Canada: www.cree.com/canada



T (800) 473-1234 F (800) 890-7507

CR6™ LED Downlight - 6"

Product Specifications

CREE TRUEWHITE® TECHNOLOGY

A revolutionary way to generate high-quality white light, Cree TrueWhite® Technology is a patented approach that delivers an exclusive combination of 90+ CRI, beautiful light characteristics, and lifelong color consistency, all while maintaining high luminous efficacy – a true no compromise solution.

CONSTRUCTION & MATERIALS

- Durable upper housing protects LEDs, driver and power supply. Adjustable flip clips resist heat while providing retention for flush ceiling fit
- Thermal management system uses both upper housing and lower reflector to conduct heat away from LEDs and transfer it to the plenum space for optimal performance. LED junction temperatures stay below specified maximum even when installed in insulated ceilings
- Suitable for insulated and non-insulated ceilings
- One-piece aluminum lower reflector redirects light while also conducting heat away from LEDs. It creates a comfortable visual transition from the lens to the ceiling plane and easily accommodates CT6 snap-in trims

OPTICAL SYSTEM

- Unique combination of reflective and refractive optical components achieves a uniform, comfortable appearance while eliminating pixelation and color fringing. This ensures smooth light patterns are projected with no hot spots and minimal striations
- Components work together to optimize distribution, balancing the delivery of high illuminance levels on horizontal surfaces with an ideal amount of light on walls and vertical surfaces. This increases the perception of spaciousness
- Diffusing polycarbonate lens shields direct view of LEDs while lower reflector balances brightness of lens with the ceiling to create a low-glare high angle appearance

ELECTRICAL SYSTEM

- Integral, high-efficiency driver and power supply
- Power Factor:** > 0.9
- Total Harmonic Distortion:** < 20%
- Input Voltage:** 120V, 60Hz
- Dimming:** Dimmable to 5% with most incandescent dimmers. Reference www.cree.com/Lighting/Products/Indoor/Downlights-US/CR-Series for recommended dimmers
- Operating Temperature Range:** 0°C - +35°C (32°F - +95°F)

REGULATORY & VOLUNTARY QUALIFICATIONS


- ENERGY STAR® qualified. Please refer to http://www.energystar.gov/certified-products/certified-products?c=products.pr_find_es_products&s=mega for most current information
- cULus Classified
- Suitable for wet locations for covered ceilings only
- Exceeds California Title-24 high efficacy luminaire requirements. Please refer to <http://www.appliances.energy.ca.gov/AdvancedSearch.aspx> for most current information
- Meets FCC Part 15 standards for conducted and radiated emissions

Photometry

CR6-800L-27K-12-E26 BASED ON ONSPEX REPORT #: 2444322

CR6-625L: MULTIPLY BY 0.78

Luminaire photometry has been conducted by a NVLAP accredited testing laboratory in accordance with IESNA LM-79-08. IESNA LM-79-08 specifies the entire luminaire as the source resulting in a luminaire efficiency of 100%.



Coefficients Of Utilization - Zonal Cavity Method					
RC %:	80				
RW %:	70	50	30	10	
RCR: 0	119	119	119	119	
1	111	107	104	101	
2	103	96	91	86	
3	96	87	80	75	
4	89	79	71	66	
5	83	72	64	59	
6	77	66	58	53	
7	72	60	53	47	
8	68	56	48	43	
9	64	52	44	39	
10	60	48	41	36	

Effective Floor Cavity Reflectance: 20%


Zonal Lumen Summary			
Zone	Lumens	% Lamp	Luminaire
0-30	335	N/A	42.5%
0-40	513	N/A	65.0%
0-60	716	N/A	90.8%
0-90	789	N/A	100.0%

Reference www.cree.com/Lighting/Products/Indoor/Downlights-US/CR-Series for detailed photometric data

Installation

- Designed to easily install in standard 6" (152mm) downlight housings with minimum housing height of 6.5" (165mm) and diameter of 5.75" - 6.5" (146mm - 165mm)
- Quick install system utilizes a unique retention feature. Simply attach socket to CR6. Move light to ready position and slide into housing

NOTE: Reference www.cree.com/Lighting/Products/Indoor/Downlights-US/CR-Series for detailed installation instructions



Application Reference

Open Space					
Spacing	Lumens	Wattage	LPW	w/ft²	Average FC
4 x 4	625	9.5	66	0.60	36
6 x 6				0.28	18
8 x 8				0.15	10
10 x 10				0.10	7
4 x 4	800	12	67	0.76	47
6 x 6				0.35	22
8 x 8				0.19	13
10 x 10				0.13	8

10' Ceiling, 80/50/20 Reflectances, 2.5 workplane. LLF: 1.0 Initial. Open Space: 50' x 40' x 10'

© 2015 Cree, Inc. and/or one of its subsidiaries. All rights reserved. For informational purposes only. Content is subject to change. Patent www.cree.com/patents. Cree®, TrueWhite®, and Cree TrueWhite® are registered trademarks, and the Cree logo, CR6™, the Cree TrueWhite Technology logo, and the Quick Ship logo are trademarks of Cree, Inc. ENERGY STAR® and the ENERGY STAR logo are registered trademarks of the U.S. Environmental Protection Agency. The UL logo is a registered trademark of UL LLC.

US: www.cree.com/lighting

T (800) 236-6800 F (262) 504-5415

Canada: www.cree.com/canada

Corridor					
Spacing	Lumens	Wattage	LPW	w/ft²	Average FC
4' on Center	625	9.5	66	0.40	13
6' on Center				0.27	9
8' on Center				0.20	7
10' on Center				0.17	6
4' on Center	800	12	67	0.51	17
6' on Center				0.34	11
8' on Center				0.25	8
10' on Center				0.21	7

10' Ceiling, 80/50/20 Reflectances, Light levels on the ground. LLF: 1.0 Initial. Corridor: 6' Wide x 100' Long

CREE

T (800) 473-1234 F (800) 890-7507