


CORE DIMENSIONS:

A	14.99 [.590]	+	0.23 [.009]
B	6.76 [.266]	+	0.25 [.010]
C	28.83 [1.135]	+	0.51 [.020]
D	7.49 [.295]	+	0.18 [.007]

**UNCONTROLLED
DOCUMENT**




CASE DIMENSIONS:

A	21.00 [.827]	+	Ref.
B	6.80 [.268]	+	Ref.
C	41.70 [1.642]	+	Ref.
D	21.00 [.827]	+	Ref.
E	4.85 [.191]	+	Ref.

IMPEDANCE (Z)

Frequency	25 MHz	100 MHz	300 MHz
Nominal (REF)	95 Ω	270 Ω	460 Ω
Minimum	- Ω	216 Ω	- Ω

Z vs. FREQUENCY
(REF. ONLY)



FREQUENCY (MHz)

AGILENT E4991A Impedance/Material Analyzer
HP 16092A-Test Fixture

NOTES:

1. ASSEMBLED PART #: 28A2026-0A2
2. CASE COLOR: BLACK - "0A2"
3. CASE FLAMMABILITY RATING: UL94 V-2.
4. CASE MATERIAL: Halogen Free Nylon

DIMENSIONS ARE IN mm [INCHES].				This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved.			
REV	DESCRIPTION	DATE	INT				
G	UPDATED NOTE 3	09/15/10	JUN	PROJECT/PART NUMBER: 28A2026-0A2 DATE: 06/29/04 CAD # 28A2026-0A2-G			
F	UPDATE COMPANY LOGO ADD NOTE 3&4	01/27/09	JRK				
E	UPDATE 100MHz MINIMUM VALUE	11/01/07	TMB				
D	UPDATE COMPANY LOGO	04/18/07	TMB				
C	CHANGE CASE DIMENSION TOLERANCES REVISE NOTE 1	03/05/07	TMB				
B	REVIS NOTES REV CASE DIMS&TOLS ADD E DIM TO CASE	05/16/06	TMB	SCALE: NTS TOOL # - MATERIAL: NiZn FERRITE			
A	ORIGINAL DRAFT	06/29/04	JRK				
REV	DESCRIPTION	DATE	INT				

Laird
TECHNOLOGIES®

REV: G PART TYPE: CASE ASSEMBLY DRAWN BY: JRK