



## FEATURES:

- Provides a larger working area than Model 6087
- This kit provides a static-safe 22" x 24" laminated red vinyl mat
- The mat includes a 10mm snap socket and two 8" x 11" pockets.
- Carry those often used tools right with the mat
- A common point ground connector with two Banana Plug Jacks and a 15' ground lead
- An adjustable elastic wrist strap and a resistive coil cord completes the kit
- Folds down to fit into your tool box

## MATERIALS:

### Anti-Static Ground Cord

Body: Plug – Brass, nickel plate, fits 4,2 (.17) standard Banana Jack

Insulation: Banana Plug – Thermoplastic elastomer, Black

Cord: Coiled Tinsel Cord, vinyl jacket, 2,5 (.10) O.D.

Body: Snap – Brass, nickel plate, fits 4,0 (.16) snap stud

Insulation: Snap – Thermoplastic elastomer, Black

### Wrist Strap

Body: Impact resistant plastic, Blue

All dimensions are in inches and metric. All specifications are to the latest revisions. Specifications are subject to change without notice.  
Registered trademarks are the property of their respective companies. Made in USA

Strap: Elastic fibers with silver plated Nylon, Yarn, Circumference: 64,0 (2.50) min., 330,0 (13.00) Max.

Snap and Cam: Stainless Steel, 4,0 (.16) snap stud

MAT, ESD: 0,46 (.018") thick, vinyl, Red

Common Point Ground Cord

Snap W/Banana Jacks End:

Body: Snap – Brass, Nickel Plate. 10,0 (.39), Male

Resistor: One Megohm resistor, insulated

Insulation: Snap – Thermoplastic elastomer, Black

Cord: 22 AWG, vinyl jacket, 2,5 (.10) O.D., Length: 46,0 (17.0)

Banana Jacks: Brass, Nickel plated. Fits 4,2 (.17) Standard Banana Plug

Large Alligator Clip End:

Body: Alligator Clip – Brass, Nickel Plate, fits 4,2 (.17) Standard Banana Plug

Insulation: PVC, Black

## RATINGS:

Surface Resistivity: 108 to 109 Ohm/Sq.

Volume Resistivity: 109 Ohm cm

Static Decay: 0.01 sec 5000V to 0V 12% RH

## ORDERING INFORMATION: Model 6088

Packaging: One Anti-Static ground cord, common point ground cord, Mat, Wrist strap, and two instruction sheets, per bag

All dimensions are in inches and metric. All specifications are to the latest revisions. Specifications are subject to change without notice.  
Registered trademarks are the property of their respective companies. Made in USA

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[6088](#)