

Features

- Hot molded carbon element
- One piece housing and bushing
- Stainless steel shaft
- Compact size
- Meets or exceeds specifications of MIL-R-94 — QPL Listed




PEC No.	NTE Part No.	Military No.	Value (Ohms)	Shaft Length	Diag No.
SLU1011S20	501-0105	RV6LAYSA101A	100	5/8"	P5
SLU5011S20	501-0106	RV6LAYSA501A	500	5/8"	P5
SLU1021S20	501-0107	RV6LAYSA102A	1K	5/8"	P5
SLU2521S20	501-0108	RV6LAYSA252A	2.5K	5/8"	P5
SLU5021S20	501-0109	RV6LAYSA502A	5K	5/8"	P5
SLU1031S20	501-0110	RV6LAYSA103A	10K	5/8"	P5
SLU2531S20	501-0111	RV6LAYSA253A	25K	5/8"	P5
SLU5031S20	501-0112	RV6LAYSA503A	50K	5/8"	P5
SLU1041S20	501-0113	RV6LAYSA104A	100K	5/8"	P5
SLU2541S20	501-0114	RV6LAYSA254A	250K	5/8"	P5
SLU5041S20	501-0115	RV6LAYSA504A	500K	5/8"	P5
SLU1051S20	501-0116	RV6LAYSA105A	1M	5/8"	P5

PEC SLU/RV6LAY Series

Potentiometer – 1/2 Watt, 1/8" dia. locking shaft

P5



Specifications

Electrical

Resistance Range – Linear Taper: 100Ω to 1 Meg Ω

Resistance Tolerance: ±10%

Power Rating: 1/2 Watt @ 70°C derated to 0 Watts @ 120°C

Insulation Resistance: 10K Meg Ω (Dry)

100K Meg Ω (Wet)

Dielectric Strength: 750V RMS at sea level

Operating Voltage: 350V subject to power rating

Mechanical

Mechanical Rotation: 295°

Operating Torque: 0.5 oz/in to 6 oz/in

Rotation Life: 25,000 cycles

Environmental

Operating Temperature: –65°C to +125°C

Resistance to Soldering Heat: 350°C for 5 seconds

Load Life: 1000 hr. at 70°C